

Universal Self-Service Station (EM)



New Features and Enhanced Performance

- Value Priced
- Enhanced User Interface
- Additional Software Features
- Service and Support Provided by 3M-Trained Technicians
- Lighter Weight



Patron Self-Checkout Station designed for libraries facing budget constraints

The Universal Self-Service Station is a flexible, reliable, cost-effective way to gain all the benefits that self-service has to offer. Productivity is enhanced by reducing the length of checkout lines and frees up staff to do other activities. Patrons can also enjoy more privacy while checking their items out themselves. Libraries can also take advantage of the service and support provided by 3M-Trained Technicians.

Features:

- **Small footprint for libraries with space constraints:** The USS Station is a small, self-contained, system that is easily put and/or moved into almost any area in your library for effective self-service
- **Works with 3M™ Tattle-Tape™ Security Strips:** To help secure your libraries materials, this system will work with Checkpoint EM or 3M Tattle-Tape Security Strips
- **Flexible design options allow a table-top or built-in unit:** The USS Station is a compact unit that can be put on top of tables, stands and counters or easily built in to cabinetry to meet your libraries design and decor needs

Universal Self-Service Station (EM)

Specifications:

Physical Specifications

Dimensions: 24" H x 15" W x 18.5" D
(610mm x 380mm x 470mm)

Weight: 57 lbs. (26 kg)

Electrical Requirements: 110/220VAC, 50/60Hz,
3/1.5 amp, 185 watt

Packaging: tabletop (standard) or built-in

Environmental

Operating temperature:

32°F to 104°F (0°C to 40°C)

Storage temperature:

-4°F to 140°F (-20°C to 60°C)

Storage/operating humidity:

10% to 90%, non-condensing

Communications

Network: TCP/IP

Library: SIP, SIP2

Peripherals

Monitor: 15" touch screen LCD flat panel
(1024x768 resolution)

Barcode Scanner: high-performance line scan
(left or right mount)

Printer: high-speed thermal direct receipt printer with
drop-in paper loading

Paper Supply: 3 1/8" wide x 3 1/4" diameter
(80mm wide x 83mm diameter) roll

Security Support

Electromagnetic (EM): Checkpoint EM Strips or
3M™ Tattle-Tape™ Security Strips

Software

Operating System: Windows XP Pro®

Languages: 2 languages shown on screen from a selection
of more than 13 available

Standard Features:

Patron authentication

Cardless sign-on

Checkout

Display account status

Graphical User Interface (GUI) for customization including:

Receipt format, Patron messages, Screen graphics

Certifications

US/Canada:

EMI, EMC – FCC part 15 subparts b and c

Safety – CUI (dual listing comprising of UL60950-1, and 22.2 60950-1)

Australia/New Zealand:

EMI – Australia-New Zealand 4268

EMC – Cispar 11

Safety – Australia-NZ 60950

Australia/New Zealand:

EMI – EN 300 330-2

EMC – EN 301 489

Safety – EN60950

Human Exposure – EN 50634

*Distributed
exclusively by*

3M

3M Library Systems

3M Center

Building 225-4N-14

St. Paul, MN 55144

1-800-328-0067

In Canada, 1-800-364-3577

www.3M.com/us/library