



# Commercial Ring Panel HVAC Filters

Filtrete™ Commercial Ring Panel HVAC filters are available in two grades (Dust and Performance) for your high traffic, large particle applications. Their sturdy ring panel construction provides a lightweight filter that is easy to handle and installs securely into front and side loading filter racks. These filters may be used as primary filters or as prefilters in certain applications. Please refer to your industry specific prefilter guidelines and 3M technical data sheets for detailed product attributes and performance.



Layered design  
Internal wire frame  
Link configuration

## ■ Performance Ring Panel HVAC Filters

Filtrete™ Commercial Performance Ring Panel HVAC Filters from 3M are for use in the high traffic areas of your facilities. They have a higher particle capture efficiency than Filtrete™ Commercial Dust Ring Panel HVAC Filters. Suggested uses could include hotel lobbies, convention centers, shopping malls, university hallways, rail and bus terminals. They offer a mid level filtration value from a company you trust.

## ■ Dust Ring Panel HVAC Filters

Areas with high levels of dust and airborne debris may benefit from using the Filtrete™ Commercial Dust Ring Panel HVAC Filter. Loading docks, cabinet shops, sports stadiums and parking facilities are good candidates for using these filters.

## ■ Construction/Build Out

Ring panel filters may be a good choice for use in the main air handler during remodeling and construction projects for large particle capture. However, these filters should not be used during remediation projects. Use of ring panel filters, on return air registers, during remodeling and construction projects may also assist in reducing large particle build up within your HVAC system.

## ■ Individual or Link Panels

Filtrete ring panel filters are available individually or linked.

Individual filter panels offer quick installation in 1" front loading and single filter racks.

Linked constructions are easy to install and remove from slide-in racks. They may also offer reduced air by-pass between filters.

Filtrete ring panel filters are just one part of the commercial filtration offering from 3M. Whether your needs include high airflow, high performance, utility or specialty filtration, we would encourage you to talk with your local sales representative regarding 3M air filtration products.




100% synthetic media

Refer to technical data sheet for detailed product attributes and performance.



IMPORTANT NOTICE: The information in this literature is based on tests 3M believes are reliable. It is not and should not be relied on as a product or technical specification. We do not guarantee the accuracy of this information. If any products described in this literature are defective, 3M will replace them at no charge. THERE ARE NO OTHER EXPRESS OR IMPLIED WARRANTIES FOR THESE PRODUCTS, INCLUDING, BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. You are responsible for determining whether products described in this literature are fit for a particular purpose and suitable for your application. Because there are many factors within your knowledge and control that might affect the use and performance of these products, you must evaluate these products to determine whether they are fit for a particular purpose, are suitable for your application, and meet your performance expectations. 3M IS NOT LIABLE FOR ANY LOSS OR DAMAGES, WHETHER DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL ARISING OUT OF THE USE OF OR INABILITY TO USE ANY OF THESE PRODUCTS.

 CAUTION: USED FILTERS MAY CONTAIN CONTAMINANTS FROM OPERATION OF THE HVAC SYSTEM. FOR PROPER HANDLING OF USED FILTERS, CONSULT APPLICABLE HEALTH AND SAFETY STANDARDS OR CONTACT AN INDUSTRIAL HYGIENIST. TO REDUCE RISK OF ILLNESS OR INJURY, ALWAYS USE APPROPRIATE RESPIRATORY PROTECTION AND PROTECTIVE CLOTHING WHEN REMOVING OR HANDLING USED FILTERS. DISPOSE OF USED FILTERS ONLY IN ACCORDANCE WITH FEDERAL, STATE AND LOCAL LAWS AND REGULATIONS.

IMPORTANT USE RESTRICTIONS: DO NOT EXPOSE THIS FILTER DIRECTLY TO UV RADIATION FROM A UV PURIFICATION SYSTEM. EXCESSIVE UV EXPOSURE MAY LEAD TO A REDUCTION IN THE MECHANICAL INTEGRITY AND PERFORMANCE OF THE FILTER. THIS FILTER MUST NOT BE USED FOR THE FOLLOWING UNAUTHORIZED USES: A) ASBESTOS, LEAD, OR MOLD REMEDIATION; B) BIOTERRORISM PROTECTION; OR C) APPLICATIONS IN BUILDINGS THAT REQUIRE OR ARE UNDERGOING AIR HANDLING SYSTEM REMEDIATION OF HAZARDOUS SUBSTANCES.



**Energy and Advanced  
Materials Division**

3M Center  
Building 223-6S-04  
St. Paul, MN 55144-1000  
1-800-648-3550

3M and Filtrete are  
trademarks of 3M Company.  
Please recycle. Printed in USA.  
© 3M 2007. All rights reserved.  
Issued: 2/07 5556HB  
70-0713-8957-4