

3M™ Detection System (Model 8900)

Enhanced security coverage with style and versatility

The 3M™ Detection System Model 8900 combines flexibility and style with state-of-the-art technology to provide excellent detection and reliable performance. The system is available in a variety of finishes to match your library's décor. Compliant with ADA requirements, the Model 8900 has a variety of flexible mounting options—direct mount or base plate to better meet your needs.

Excellent Detection Performance

- Utilizes the latest RFID technology to provide enhanced detection performance
- Available in one, two, three or four corridor systems

Features

- Adjustable audio and visual alarms
- Integrated patron counter to monitor your traffic patterns

Attractive Design

- Slim elegant pedestal design allows for excellent visibility of patron in corridor
- Available with the same wood laminate finishes as the 3M™ SelfCheck™ System products to enhance decor matching capabilities
- Neutral finish options also available

The following specifications are for the Model 8900 single-corridor with baseplate.

Dimensions

26" d x 79" h x 41" w
(1040 mm x 1780 mm x 660 mm)

Energy Profile

100-240 VAC
50-60 Hz
0.5 A

Weight (Approximate)

135 lbs (61Kg)

Available Options

3M™ Stats and Status Software for 3M Detection System Model 8900

Operate your library more efficiently with powerful new monitoring and reporting tools from 3M. Gain real-time access to statistics and aggregated customized reports including patron counting, ability to identify items that left the library that were not checked out properly*, and alarm counting to help optimize the use of your staff time.



*Consult your 3M Sales Consultant regarding system specifications.



3M Library Systems
3M Center, Bldg. 225-4N-14
St. Paul, MN 55144-1000
USA
1-800-328-0067
www.3M.com/us/library

Please recycle. Printed in USA.
© 3M 2009. All rights reserved.
3M, SelfCheck and Tattle-Tape
are trademarks of 3M.

