

C L A R I T Y™ | S L

SELF-LIGATING APPLIANCE SYSTEM

Order Guide



- Passive Self-Ligating Performance
- Patient Pleasing Aesthetics
- True Twin Edgewise Functionality
- Reliable Bonding
- Enhanced Leveling and Alignment
- Efficient Archwire Changes
- Reduced Friction
- Predictable Tooth Movement
- Consistent Debonding

U N C O M P R O M I S I N G

Performance

Passive self-ligating performance and aesthetics merge
for a uniquely rewarding treatment experience.

Clarity™ SL Self-Ligating Brackets incorporating SmartClip™ Self-Ligating System technology, are the only ceramic brackets that are self-ligating and feature an open slot, true twin edgewise design. You can feel confident that Clarity SL brackets will deliver difference-making advantages throughout every phase of treatment.

CLARITY™ | SL

SELF-LIGATING APPLIANCE SYSTEM

Clarity™ SL Brackets – Selection by Tooth – MBT™ Appliance System

							(MAXILLARY .018 IN.)			(MAXILLARY .022 IN.)		
MAX	TORQUE	ANG	IN/OUT		L/R	HOOK	APC™ II	APC™ PLUS	NON-COATED	APC II	APC PLUS	NON-COATED
			in.	mm								
Central	+17	+4	.044	1.12	L		3007-501	5007-501	007-501	3007-401	5007-401	007-401
Central	+17	+4	.044	1.12	R		3007-502	5007-502	007-502	3007-402	5007-402	007-402
Lateral	+10	+8	.058	1.47	L		3007-503	5007-503	007-503	3007-403	5007-403	007-403
Lateral	+10	+8	.058	1.47	R		3007-504	5007-504	007-504	3007-404	5007-404	007-404
Cuspid	0	+8	.030	0.76	L		3007-511	5007-511	007-511	3007-411	5007-411	007-411
Cuspid	0	+8	.030	0.76	R		3007-512	5007-512	007-512	3007-412	5007-412	007-412
Cuspid	0	+8	.030	0.76	L	Y	3007-505	5007-505	007-505	3007-405	5007-405	007-405
Cuspid	0	+8	.030	0.76	R	Y	3007-506	5007-506	007-506	3007-406	5007-406	007-406
Bicuspid	-7	0	.036	0.92	L	Y	3007-507	5007-507	007-507	3007-407	5007-407	007-407
Bicuspid	-7	0	.036	0.92	R	Y	3007-508	5007-508	007-508	3007-408	5007-408	007-408
Bicuspid	-7	0	.036	0.92	L/R		3007-509	5007-509	007-509	3007-409	5007-409	007-409

							(MANDIBULAR .018 IN.)			(MANDIBULAR .022 IN.)		
MAN	TORQUE	ANG	IN/OUT		L/R	HOOK	APC II	APC PLUS	NON-COATED	APC II	APC PLUS	NON-COATED
			in.	mm								
Anterior	-6	0	.060	1.52			3007-530	5007-530	007-530	3007-430	5007-430	007-430
Cuspid	0	+3	.029	0.74	L	Y	3007-531	5007-531	007-531	3007-431	5007-431	007-431
Cuspid	0	+3	.029	0.74	R	Y	3007-532	5007-532	007-532	3007-432	5007-432	007-432
1st Bicuspid	-12	+2	.029	0.74	L		3007-539	5007-539	007-539	3007-439	5007-439	007-439
1st Bicuspid	-12	+2	.029	0.74	R		3007-540	5007-540	007-540	3007-440	5007-440	007-440
2nd Bicuspid	-17	+2	.033	0.84	L		3007-541	5007-541	007-541	3007-441	5007-441	007-441
2nd Bicuspid	-17	+2	.033	0.84	R		3007-542	5007-542	007-542	3007-442	5007-442	007-442

Clarity SL Brackets – Selection by Tooth – Roth* Rx

							(MAXILLARY .018 IN.)			(MAXILLARY .022 IN.)		
MAX	TORQUE	ANG	IN/OUT		L/R	HOOK	APC II	APC PLUS	NON-COATED	APC II	APC PLUS	NON-COATED
			in.	mm								
Central	+12	+5	.044	1.12	L		3007-517	5007-517	007-517	3007-417	5007-417	007-417
Central	+12	+5	.044	1.12	R		3007-518	5007-518	007-518	3007-418	5007-418	007-418
Lateral	+8	+9	.058	1.47	L		3007-519	5007-519	007-519	3007-419	5007-419	007-419
Lateral	+8	+9	.058	1.47	R		3007-520	5007-520	007-520	3007-420	5007-420	007-420
Cuspid	-2	+9	.030	0.76	L	Y	3007-521	5007-521	007-521	3007-421	5007-421	007-421
Cuspid	-2	+9	.030	0.76	R	Y	3007-522	5007-522	007-522	3007-422	5007-422	007-422
Bicuspid	-7	0	.036	0.92	L	Y	3007-523	5007-523	007-523	3007-423	5007-423	007-423
Bicuspid	-7	0	.036	0.92	R	Y	3007-524	5007-524	007-524	3007-424	5007-424	007-424
Bicuspid	-7	0	.036	0.92	L/R		3007-509	5007-509	007-509	3007-409	5007-409	007-409

*3M Unitek version of this prescription. No endorsement by the doctor is implied.



Clarity™ SL Brackets – One Patient Kits – MBT™ Appliance System

	.018 IN.			.022 IN.		
	APC™ II	APC™ PLUS	NON-COATED	APC II	APC PLUS	NON-COATED
U 5x5 Clarity™ SL Brackets Hks L 5x5 SmartClip™ SL3 Self-Ligating Brackets Hks	3007-103	5007-103	007-103	3007-113	5007-113	007-113
U 5x5 Clarity SL Brackets Only	3007-106	5007-106	007-106	3007-116	5007-116	007-116
U 5x5 Clarity SL Brackets Only Cuspid Hk	3007-122	5007-122	007-122	3007-132	5007-132	007-132
U 5x5 Clarity SL Brackets Only Hks	3007-107	5007-107	007-107	3007-117	5007-117	007-117
U 3x3 Clarity SL Brackets Only Cuspid Hk	3007-123	5007-123	007-123	3007-133	5007-133	007-133
U/L 5x5 Clarity SL Brackets Cuspid Hk	3007-100	5007-100	007-100	3007-110	5007-110	007-110
U/L 3x3 Clarity SL Brackets Cuspid Hk	3007-126	5007-126	007-126	3007-136	5007-136	007-136

Clarity SL Brackets – One Patient Kits – Roth* Rx

	.018 IN.			.022 IN.		
	APC II	APC PLUS	NON-COATED	APC II	APC PLUS	NON-COATED
U 5x5 Clarity SL Brackets Hks L 5x5 SmartClip SL3 Self-Ligating Brackets Hks	3007-121	5007-121	007-121	3007-131	5007-131	007-131
U 5x5 Clarity SL Brackets Only Cuspid Hk	3007-124	5007-124	007-124	3007-134	5007-134	007-134
U 5x5 Clarity SL Brackets Only Hks	3007-120	5007-120	007-120	3007-130	5007-130	007-130
U 3x3 Clarity SL Brackets Only Cuspid Hk	3007-125	5007-125	007-125	3007-135	5007-135	007-135



Accessories

	Part No.
Clarity™ SL Appliance System Chairside Starter Kit (.018 slot)	5007-998
Clarity SL Appliance System Chairside Starter Kit (.022 slot)	5007-999
Unitek™ Self-Ligating Bracket Debonding Instrument	804-170
Unitek™ Bracket Placement Instrument	804-171
SmartClip™ Appliance Wire Insertion Hand Instrument (.018 slot)	804-153
SmartClip Appliance Wire Insertion Hand Instrument (.022 slot)	804-152
SmartClip Appliance Disengagement Hand Instrument	804-160
SmartClip Appliance Disengagement Hand Instrument Replacement Slides	804-161
SmartClip Appliance Disengagement Hand Instrument Replacement Hooks with Allen Wrench and Set Screws	804-162

Practice Enhancement Materials

	Part No.
Clarity SL Appliance System Practice Enhancement Kit	5007-997
Clarity SL Appliance System Patient Information Brochure	014-498
Literature Holder for Patient Brochure	453-014
Clarity SL Appliance System Lenticular Card	012-178
Clarity SL Appliance System Presentation Typodont U/L	600-235
Clarity SL Appliance System Presentation Typodont with SmartClip Bracket Lowers	600-229
Clarity SL Appliance System 15x Demonstration Model	600-230
Clarity SL Appliance System Poster – Dark Hair Woman – Desk Size Mounted	014-499
Clarity SL Appliance System Poster – Dark Hair Woman #2 – Desk Size Mounted	014-500
Clarity SL Appliance System Poster – Blonde Hair Woman – Desk Size Mounted	014-501
Clarity SL Appliance System Poster – Man – Desk Size Mounted	014-502
Clarity SL Appliance System Poster – Dark Hair Woman – 20" x 30", Rolled	014-504
Clarity SL Appliance System Poster – Dark Hair Woman #2 – 20" x 30", Rolled	014-505
Clarity SL Appliance System Poster – Blonde Hair Woman – 20" x 30", Rolled	014-506
Clarity SL Appliance System Poster – Man – 20" x 30", Rolled	014-507




Clarity™ SL Appliance System
Poster – Dark Hair Woman



Clarity SL Appliance System
Poster – Dark Hair Woman #2



Clarity SL Appliance System
Poster – Blonde Hair Woman



Clarity SL Appliance System
Poster – Man



**3M Unitek
Orthodontic Products**
2724 South Peck Road
Monrovia, CA 91016 USA
www.3MUnitek.com

In U.S. and Puerto Rico: 1-800-423-4588 • 626-574-4000
In Canada: 1-800-443-1661
Technical Helpline: 1-800-265-1943 • 626-574-4577
CE Hotline: 1-800-852-1990 x4649 • 626-574-4649
Outside these areas, contact your local representative.

Clarity, MBT, SmartClip and Unitek
are trademarks of 3M.
Please recycle.
© 3M 2009. All rights reserved.
016-956-7 0909