





















Specifications for Vinyl Electrical Tapes

	Product Number	Product Description	Tape Thickness	U.V. Resistance	Temperature Rating	Typical Applications	Specifications/Certifications and Listings
	Scotch® Super 33+ Professional Use Premium Vinyl Electrical Tape	Highly conformable, super stretchy in all weather applications; resists UV rays, abrasion, corrosion, alkalies & acids. Flame retardant.	7 mil	Exceeds UL510 requirements	220°F 105°C	Primary insulation for splices up to 600V. Protective jacketing.	A-A-55809 ASTM D-3005 Type I   LISTED 539H LR48769
	Scotch 35 Professional Use Vinyl Electrical Tape for Color Coding	Nine fade-resistant colors, super stretchy & conformable, excellent insulating properties. Resist UV rays, abrasion, corrosion, alkalies & acid.	7 mil	Exceeds UL510 requirements	220°F 105°C	Phase identification & marking. Harnessing	A-A-55809   LISTED 539H LR48769
	Scotch Super 88 Professional Use Premium Vinyl Electrical Tape	All weather; heavy duty, professional use, abrasion resistant, fast build up.	8.5 mil	Exceeds UL510 requirements	220°F 105°C	Primary insulation for splices up to 600V. Protective jacketing.	MIL-I-24391C ASTM D-3005 Type II   LISTED 539H LR48769
	Scotch 22 Heavy Duty Vinyl Electrical Tape	Thicker for increased mechanical strength and abrasion resistance. Electrical insulating.	10 mil	Exceeds UL510 requirements	176°F 80°C	Bus bar insulation. Cable jacket repair.	ASTM D-2301 Type II   LISTED 539H LR48769
	Scotch 66R Vinyl Electrical Tape	Excellent mechanical strength, abrasion resistance and electrical insulating properties.	10 mil	Exceeds UL510 requirements	220°F 105°C	Primary insulation for 600V bus bar. Protective jacketing.	 File E 17385
	Highland™ Commercial Grade Electrical Tape	Flexible, stretchy, conformable, commercial grade vinyl. Flame retardant.	7 mil	Meets UL510 requirements	194°F 90°C	Protective jacketing. Harnessing.	ASTM D-2301 Type I   LISTED 539H LR48769
	Temflex™ 1700 General Purpose Vinyl Electrical Tape	Economical, flexible, general purpose tape.	7 mil	Meets UL510 requirements	176°F 80°C	Protective jacketing. Harnessing.	ASTM D-2301 Type I   LISTED 539H LR48769