



Pretreatment Cleaner

Product No. 10

Technical Data

May 2004

Description:

3M Pretreatment Cleaner is a concentrated product to be diluted and dispensed using the 3M Twist 'n Fill™ Cleaning Chemical Management System.

Pretreatment Cleaner loosens and suspends soil so it can be rinsed from the carpet during extraction.

Special Features:

- Automatic dispensing eliminates measuring and mixing and ensures accurate dilutions
- Neutral pH makes this product ideal for use on wool carpet
- No sticky residue to cause re-soiling problems

Applications:

- Commercial and residential carpets
- Most carpet fibers (nylon, olefin, wool & blends)
- Most carpet styles (loop or cut pile)
- Safe for use on stain resistant nylon fibers

Packaging:

2- liter bottle
6 bottles per case

Each 2-liter bottle yields
81 ready-to-use gallons

General Use Directions:

Refer to ready-to-use MSDS for personal protective equipment (PPE) recommendations.

1. Vacuum carpet thoroughly before cleaning.
2. Remove gum and tough stains before applying pretreatment.
3. Use a 3M All Purpose Sprayer (Model AP-1) or a bulk pressure sprayer to apply the pretreatment cleaner.
4. Dispense cleaner using the Twist 'n Fill dispenser directly into the solution tank of the sprayer.
5. Fill carpet extractor with warm water.
6. Apply the pretreatment cleaner to the carpet area at a rate of 200 ft² per diluted gallon.
7. Allow 3-5 minutes dwell time.
8. Provide agitation to heavily soiled areas using a brush or 3M Carpet Bonnet Pad (optional).
9. Extract the carpet using overlapping passes of the extraction wand.
10. Move the extractor slowly over the carpet making two passes.
11. Dispense rinse water throughout the 1st pass.
12. On the 2nd pass, vacuum only – do not apply additional water.
13. Apply Scotchgard™ Carpet Protector to damp carpet immediately following extraction cleaning.
14. Use fans or blowers to accelerate drying.
15. Allow carpet to fully dry before opening room for traffic.

Product Specifications:

(Typical Values)

Concentrate:

1. pH: 6-8
2. Flash Point: 102°F
3. Solubility in Water: Complete
4. Specific Gravity: 1.0
5. Viscosity: <100 cps
6. Appearance: Clear colorless liquid
7. Fragrance: Mild

Ready-to-Use:

1. pH: 6-7
2. Flash Point: N/A
3. Solubility in Water: Complete
4. Specific Gravity: 1.0
5. Viscosity: <100 cps
6. Appearance: Colorless liquid
7. Fragrance: Mild

Precautionary Summary:

Concentrate:

Eye Contact: Severe eye irritant
Skin Contact: Moderate skin irritant
Inhalation: May cause upper respiratory irritation

Ready-to-Use:

Eye Contact: Mild eye irritant
Skin Contact: Mild skin irritant after prolonged or repeated contact
Inhalation: May cause upper respiratory irritation

Note:

Refer to product Material Safety Data Sheet (MSDS: 06-2712-5, 06-2713-3) for specific health hazard, first aid and precautionary information

3M Branch Sales Offices

ANCHORAGE

11151 Calaska Circle
Anchorage, AK 99515
Telephone: 907/522-5200
Facsimile 907/522-1645

CONTINENTAL UNITED STATES

Customer Service Department
3M Center Building 223-5S-07
St. Paul, MN 55144-1000
Order Entry 1-800-852-9722
Facsimile 1-800-447-0408

HONOLULU

4443 Malaai Street
Honolulu, HI 96818
Mail to: P.O. Box 30048
Honolulu, HI 96820
Telephone: 808/422-2721
Facsimile 808/422-9557

CANADA

1840 Oxford Street East
London, Ontario, Canada
N5V 3G2
Mail to: P.O. Box 5757
London, Ontario, Canada
N6A 4T1
Telephone: 800/364-3577
Facsimile: 800/479-4453

Important:

The information provided in this report is believed to be reliable; however, due to the wide variety of intervening factors, 3M does not warrant that the results will necessarily be obtained. All details concerning product specifications and terms of sale are available from 3M.

3M Building and Commercial Services Division

St. Paul, MN 55144-1000
1-800-852-9722
www.3M.com/commcare

3M and Twist n' Fill are trademarks of 3M Company.

Copyright © 2004, 3M IPC. All rights reserved.