

3M

ScotchPad™

Custom Carry Handle

8329

Technical Data

May, 2009

Product Description 3M™ ScotchPad™ Carry Handle 8329 is made of durable plastic strips with adhesive at each end and is available in white or with custom printed or colored carry portion material. It is easy to create a convenient looped handle when the ends are attached to both sides of a box or package.

Product Construction	Backing:	Available in custom backing.
	Adhesive:	Pressure-sensitive rubber resin. Requires no heat, moisture or solvent activation prior to use.
	Carry Portion Material (CPM):	White or colored paper. Available custom printed.

Typical Physical Properties **Note: The following technical information and data should be considered representative or typical only, and should not be used for specification purposes.**


		ASTM Test Method
Adhesion to Steel:	60-100 oz./in. width*	D-3330
Tensile Strength:		
Longitudinal	150-270 lbs./in. width*	D-3759
Elongation at Break:	10-30%*	D-3759
Thickness:		D-3652
Tape	Various*	
Carry Portion Material	"	
Total	"	

*Based on custom construction.

- | | | |
|-----------------|---|---|
| Features | <ul style="list-style-type: none"> • Adhesive handle. • High-performance carrying tape. • Custom colors and graphics. • Compact size. • Easy to carry bulky packages. • Excellent adhesion. • Easy to apply. • Easy package identification. • Captures customers attention. • Promotion/communications vehicle. | <ul style="list-style-type: none"> • Customer convenience. • Carry more items. • Adheres to a variety of surfaces. • Speeds up customer traffic through checkout lines. • In-store security. • Stores easily at checkout counter. • Reduces packaging/waste. • Increases brand awareness. |
|-----------------|---|---|

3M™ ScotchPad™ Custom Carry Handle 8329

Handle Dimensions



A Handle Width	B Total Handle Length	C Adhesive Length	Max Load Per Handle
1 ³ / ₈ in. (35 mm)	23 in. (584 mm)	6 in. (152 mm)	Up to 50 lbs.

Application Ideas

- Carrying bulky products up to 50 lbs. (small appliances, small electronics, toys, lawn, garden, heavy houseware and hardware items) some industrial products and bulk-packaged items.
- Combining products while using a handle (shrink wrapped multipacks).
- Providing special promotional messages or UPC codes on the handle.

Storage Conditions

Storage of handles at 70°F (21°C) and 40-50% relative humidity is recommended.

Shelf Life

To obtain best performance, use this product within 18 months from date of manufacture.

Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2000

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.

3M

Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (Fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

3M and ScotchPad are trademarks
of 3M Company.
Printed in U.S.A.
©3M 2009 70-0710-0343-1 (5/09)