



# Insta-Lok™ II Blue Driving Assembly

---

**Description:**

This product is used to drive floor pads, bonnets and 3M brushes. It is a one piece molded driving assembly utilizing the unique pad holding 3M™ Insta-Lok™ material in combination with special pyramid driving points.

The assembly is predrilled to accept the proper 3M clutch plate\*. Clutch plates are available for a wide variety of standard floor machines.

**Intended Use:**

The assembly is designed for use with standard buffers that typically operate at or below 600 rpm and do not require special vibration dampening devices.

The assembly is designed to drive pads, bonnets and special 3M brushes for a wide range of cleaning jobs.

**Color:**

Blue

\* Clutch plate not included as part of driving assembly.

**Special Features:**

- One piece injection molded riser/plate
- High strength ABS polymer construction
- Unique 3M Insta-Lok material
- Pyramid drive points
- Showerfeed
- 3M clutch plate compatible

**How to Use:**

1. Select the proper size driving assembly for your machine. Follow the machine manufacturer's recommendation or select a driving assembly diameter one inch smaller than the outside diameter of the machine.
2. Select the proper clutch plate for your machine. (Refer to the 3M Clutch Plate Selection Guide as required.)
3. Install clutch plate using screws enclosed with the driving assembly.
4. The assembly is now ready for use. Simply attach to the floor machine and select the appropriate pad, bonnet or special 3M brush.

**Standard Sizes:**

15" to 20" diameter in one inch increments

**Packaging and Marking:****Packaging:**

One assembly per box

**Marking:**

Each box is marked with product name and size



**3M Branch Sales Offices**

**ANCHORAGE**

11151 Calaska Circle  
Anchorage, AK 99515  
Area Code 907 Tel. 522-5200  
Facsimile 907-522-1645

**CONTINENTAL UNITED STATES**

Customer Service Department  
3M Center Building 223-3E-04  
St. Paul, MN 55144-1000  
Order Entry 1-800-698-4595  
Facsimile 1-800-447-0408

**HONOLULU**

4443 Malaai Street  
Honolulu, HI 96818  
Mail to: P.O. Box 30048  
Honolulu, HI 96820  
Area Code 808 Tel. 422-2721  
Facsimile 808-422-9557

**3M CANADA**

1840 Oxford Street East  
London, Ontario, Canada  
N5V 3G2  
Mail to: P. O. Box 5757  
London, Ontario, Canada  
N6A 4T1  
519-451-2500  
Fax: 519-452-6262

"3M" and "Insta-Lok" are trademarks of 3M.

**Important Notice:**

This flyer is intended to be an introductory summary. The information provided is based upon typical conditions and is believed to be reliable; however, due to the wide variety of intervening factors, 3M does not warrant that the results will necessarily be obtained. All details concerning product specifications and terms of sale are available from 3M.