



3M™ MCS™ Warranty

OKI Data Infotech ColorPainter™ H-74s, H-104s, H2-74s and H2-104s, W-54s and W-64s Printers Using 3M™ GX Ink Series from OKI

IMPORTANT! Only graphics manufacturers having a current Certificate of 3M™ MCS™ Warranty are eligible to extend this Warranty to their customers. Finished Graphics Warranty Period is stated in years for Vertical Graphics made with 3M Film, Inks and Graphic Protection using Approved Printers. Refer to the film's Product Bulletin for details and full trademark names, which can be viewed online by clicking the blue film number links. Also review the notes at the end of the matrix.

Film	Notes	Graphic Protection	VEH	OUT	W/R	IN
2 MIL						
IJ170Cv3	G	8518, 8519, 8520, 8915	7	4	2	8
	D	8528	7/3	4	2	8
		8548G, 8549L	7/2	4	2	8
		8900	3/1	—	—	—
		1920DR	3	3	2	5
		9740i	5	4	2	8
		8530	—	—	—	—
		none	—	2	—	2
IJ180	G	8518, 8519, 8520, 8915	7	4	2	8
IJ180C	D	8528	7/3	4	2	8
IJ180Cv3		8548G, 8549L	7/2	4	2	8
IJ180mC-10		8900	3/1	—	—	—
IJ180mC-114		1920DR	3	3	2	5
IJ180mC-120		9740i	5	4	2	8
IJ180C-10LSE		8530	—	—	—	—
IJ180-10SLS		none	—	2	—	2
IJ380Cv3	A, D	8548G, 8549L	5/2	—	2	—
		1920DR	3	—	2	—
SV480Cv3	G	8518, 8519, 8520, 8915	7	4	2	8
SV480mC	D	8528	7/3	4	2	8
		8548G, 8549L	7/2	4	2	8
		1920DR	3	3	2	5
IJ8150	G	8518, 8519, 8520, 8915, 8914	3	3	—	8
	D	8528	3/3	3	—	8
		1920DR	3	3	—	5
		9740i	3	3	—	8
		none	—	—	—	2

Film	Notes	Graphic Protection	VEH	OUT	W/R	IN
IJ180mC-10UR	B, G	8518, 8519, 8520, 8915	2	2	—	2
IJ3552C		1920DR	2	2	—	2
		9740i	2	2	—	2
IJ3690LF-10	G	8518, 8519, 8520, 8915	—	4	—	8
IJ3690LF-114		1920DR	—	3	—	5
		9740i	—	4	—	8
		none	—	2	—	2
IJ3650-10		3619, 3620, 3658G, 3660M	—	6	—	8
IJ3650-114	G	8518, 8519, 8520, 8915	—	4	—	8
		1920DR	—	3	—	5
		9740i	—	4	—	8
		none	—	2	—	2
4 MIL						
IJ160-10	G	8518, 8519, 8520, 8915	3	3	—	5
IJ160C-10		8528	3	3	—	5
		1920DR	3	3	—	5
		9740i	3	3	—	5
		8530	—	—	—	—
		none	—	2	—	2
IJ160-10		3645	—	—	—	1
IJ3555	G	8518, 8519, 8520, 8915	2	2	—	2
		1920DR	2	2	—	2
		9740i	2	2	—	2
		8530	—	—	—	—
		none	—	2	—	2
8170-P40/P50		8914, 8518	1	2	—	5
ILLUMINATED						
3635-210		3619, 3620, 3658G, 3660M	—	5	—	5

Film	Notes	Graphic Protection	VEH	OUT	W/R	IN
IJ3630-20	C	3619, 3620, 3658G, 3660M	—	6	—	8
	G	8518, 8519, 8520, 8915	—	4	—	8
		1920DR	—	3	—	5
		9740i	—	4	—	8
		none	—	2	—	2
IJ3730-50	C	3619, 3620, 3658G, 3660M	—	6	—	8
IJ3730-60	G	8518, 8519, 8520, 8915	—	4	—	8
		1920DR	—	3	—	5
		9740i	—	4	—	8
		none	—	2	—	2
Panagraphics III	H	3619, 3620, 3658G, 3660M	—	6	—	8
	G	8518, 8519, 8520, 8915	—	4	—	8
		None	—	—	—	—
FS-1	H	3619, 3620, 3658G, 3660M	—	6	—	8
	G	8518, 8519, 8520, 8915	—	4	—	8
		none	—	—	—	—
REFLECTIVE						
780mC-10R	D	8518, 8519	7	4	4	8
		8548G, 8549L	7/2	4	4	8
		1920DR	3	3	3	5
		9740i	5	4	4	8
		None	—	2	—	2
IJ680-10		8518, 8519	7	4	4	8
IJ680CR-10		1920DR	3	3	3	5
		9740i	5	4	4	8
		None	—	2	—	2
IJ5000		8518, 8519	1.5	1.5	—	1.5
		1920DR	1.5	1.5	—	1.5
		9740i	1.5	1.5	—	1.5

- NOTES A Film IJ380Cv3 with overlamine 8548G or 8549L is for auto and watercraft wraps only.
 B Films IJ3552C/IJ180mC-10UR have 2 years durability when applied to flat and simple curved surfaces; 1 year durability when applied to compound curved surfaces, heated and stretched to conform.
 C Film IJ3630 or IJ3730 may be applied to 3M™ Panagraphics III Wide-Width Flexible Substrates or 3M™ Flexible Substrate FS-1.
 D For overlamine 8528 or 8548G or 8549L or 8900, the first number represents the vertical durability and the second number the horizontal/non-vertical durability on vehicle graphics.
 G Overlamine 8915 is not approved for or warranted for use with 3M™ GX Ink Series from OKI.
 H Be sure your printer is capable of supporting the width, weight and roll diameter of the flexible substrate to avoid damaging the printer.
 IMPORTANT NOTE: Unless you are using 3M horizontal/non-vertical warranty overlaminates (8528, 8548G, 8549L, and 8900), you will only be eligible for a vertical warranty. See the 3M Graphics Warranty Bulletin for more detail.

- VEH = Commercial Vehicle, Fleet Truck and Trailer, Bus, Personal Vehicles
 OUT = Outdoor Signs, OEM
 W/R = Watercraft or Railroad (Note: for most films, this refers to Watercraft. For Reflective films, it refers to Railroad).
 IN = Indoor signs

Warranty and Limited Liability. The following is made in lieu of all other express or implied warranties, including any implied warranty of merchantability or fitness for a particular purpose. All 3M products are warranted to be free of defects in materials and manufacture at the time of shipment and to meet the specifications stated in the film or media's Product Bulletin. Also see 3M Graphics Warranties Brochure, which gives the terms, additional limitations of the warranty, if any, and limitations of liability. Trademarks: 3M and MCS are trademarks of 3M Company. All other trademarks are the property of their rightful owners.

DISCLAIMER: With the exception of 3M branded products, 3M does not represent that any printer or printer accessory recommended in 3M literature will meet customer requirements, any federal, state or local regulations, or any applicable safety standards. Such determination is the responsibility of the printer owner.

Film	Notes	Graphic Protection	VEH	OUT	W/R	IN
IJ5100-10		8518, 8519	4	3	—	4
IJ5100R-10		1920DR	3	3	—	3
		9740i	4	3	—	4

Film	Notes	Graphic Protection	VEH	OUT	W/R	IN
------	-------	--------------------	-----	-----	-----	----

Film	Notes	Graphic Protection	VEH	OUT	W/R	IN
------	-------	--------------------	-----	-----	-----	----

- NOTES
- A Film IJ380Cv3 with overlaminate 8548G or 8549L is for auto and watercraft wraps only.
 - B Films IJ3552C/IJ180mC-10UR have 2 years durability when applied to flat and simple curved surfaces; 1 year durability when applied to compound curved surfaces, heated and stretched to conform.
 - C Film IJ3630 or IJ3730 may be applied to 3M™ Panagraphics III Wide-Width Flexible Substrates or 3M™ Flexible Substrate FS-1.
 - D For overlaminate 8528 or 8548G or 8549L or 8900, the first number represents the vertical durability and the second number the horizontal/non-vertical durability on vehicle graphics.
 - G Overlaminate 8915 is not approved for or warranted for use with 3M™ GX Ink Series from OKI.
 - H Be sure your printer is capable of supporting the width, weight and roll diameter of the flexible substrate to avoid damaging the printer.
- IMPORTANT NOTE: Unless you are using 3M horizontal/non-vertical warranty overlaminates (8528, 8548G, 8549L, and 8900), you will only be eligible for a vertical warranty. See the 3M Graphics Warranty Bulletin for more detail.

DISCLAIMER: With the exception of 3M branded products, 3M does not represent that any printer or printer accessory recommended in 3M literature will meet customer requirements, any federal, state or local regulations, or any applicable safety standards. Such determination is the responsibility of the printer owner.

- VEH = Commercial Vehicle, Fleet Truck and Trailer, Bus, Personal Vehicles
- OUT = Outdoor Signs, OEM
- W/R = Watercraft or Railroad (Note: for most films, this refers to Watercraft. For Reflective films, it refers to Railroad).
- IN = Indoor signs

Warranty and Limited Liability. The following is made in lieu of all other express or implied warranties, including any implied warranty of merchantability or fitness for a particular purpose. All 3M products are warranted to be free of defects in materials and manufacture at the time of shipment and to meet the specifications stated in the film or media's Product Bulletin. Also see 3M Graphics Warranties Brochure, which gives the terms, additional limitations of the warranty, if any, and limitations of liability. Trademarks: 3M and MCS are trademarks of 3M Company. All other trademarks are the property of their rightful owners.