

3

Interam™ T-49 Tape

Product Description

3M Interam Tape is an adhesive backed aluminum foil tape which is designed to seal in cooling vapors in the event of fire. It also serves as an additional environmental seal for the item being fire protected.

Applications

Used to seal seams and provide physical protection.

Data

Tape Thickness:	0.005 in. (0,127mm)
Roll Length:	180 ft. (54,8 mm)
Roll Width:	4 in. (101 mm)
Weight/Unit Area:	0.052 lbs./ft. ² (0,254 Kg/m ²)
Tensile Strength:	30 lbs./in. width (525N/100mm)
Color:	Silver

Specifications

T-49 Tape is constructed using a dead soft aluminum foil 3 mils (0,076mm) thick and an acrylic adhesive 2 mils (0,050mm) thick. The adhesive contains less than 22 ppm leachable chlorides.

Characteristics and Test Data

T-49 Tape has undergone fire test qualification as an integral part of the Interam Structural Steel and Electrical Wrap Systems. No other tape should be substituted.

Installation Techniques

Apply tape to seam and rub down the tape with a small rubber roller or squeegee.

Maintenance/Storage

Warehouse in dry location.

Important Notice to Purchaser:

LIMITATION OF REMEDIES AND LIABILITY: If the 3M product is proved to be defective, THE EXCLUSIVE REMEDY, AT 3M'S OPTION, SHALL BE TO REFUND THE PURCHASE PRICE OF OR TO REPAIR OR REPLACE THE DEFECTIVE 3M PRODUCT. 3M SHALL NOT OTHERWISE BE LIABLE FOR LOSS OR DAMAGES, WHETHER DIRECT, INDIRECT, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL (INCLUDING, BUT NOT LIMITED TO, LOSS OF PROFITS, INVESTMENT, GOODWILL OR BUSINESS OPPORTUNITY), REGARDLESS OF THE LEGAL THEORY ASSERTED, INCLUDING NEGLIGENCE, CONTRACT, WARRANTY, OR STRICT LIABILITY.

3

Fire Protection Products

3M Center, Building 207-1S-02
St. Paul, MN 55144-1000
800 328 1687



Recycled paper
40% pre-consumer
10% post-consumer

Litho in USA with 3M films,
Proofing systems and offset plates

© 3M 1997

98-0400-0888-4