

NEW PRODUCT

Brighter nights ahead!

With the 3M™ Lens Renewal Kit 39014, your lenses will look as good as new

Hazy lenses are a thing of the past with the 3M™ Lens Renewal Kit. Designed to provide increased brightness to plastic lenses, this kit comes with everything you need to do the job - just add a drill! It will remove the hazy, yellow layer from lenses on trailers, snowmobiles, headlights/taillights, emergency vehicle light bars, plastic motorcycle lights and more. Increase your nighttime visibility and the appearance of your vehicle using the 3M Lens Renewal Kit.

Simple to use:



Before



1. Mask

Requires only basic household items like masking tape and a drill



2. Sand

Easily sand away the outer layer to restore headlight lenses



3. Refine

Refine and reduce scratches



4. Polish

Polish lenses for clarity and shine



To see this product in action, watch our YouTube video. Search for "3M Headlights."



After



For more information on 3M Car Care products, visit www.3MCarCare.com or call (877) MMM-CARS

Made in the U.S.A.
60-4401-0370-7




Requester: Jo Twite
Creator: deZinnia.1
File Name: 60-4401-0370-7.indd
Structure #: N/A
Date: 10/27/09

Printed Colors – Front:



Printed Colors – Back:

Match Colors:

Scale:  1 Inch

This artwork has been created as requested by 3M. 3M is responsible for the artwork AS APPROVED and assumes full responsibility for its correctness.