

# Scotch® Flatback Masking Tape 250



## Technical Data

March, 2013

**Product Description** Scotch® Flatback Masking Tape 250 is used for bundling and holding applications where a stronger paper backing is needed.

Product Construction	Backing	Adhesive	Color	Standard Roll Length
	Flat Stock Paper	Rubber	Tan	60 yds. (54.8 m)

**Typical Physical Properties** **Note: The following technical information and data should be considered representative or typical only, and should not be used for specification purposes.**

		ASTM Test Method
Adhesion to Steel:	78 oz./in. width (85 N/100 mm)	D-3330
Tensile Strength:	59 lbs./in. width (1033 N/100 mm)	D-3759
Elongation at Break:	4%	D-3759
Tape Thickness:	6.0 mils (0.15 mm)	D-3652
Temperature Use Range:	Up to 125°F (52°C) for up to 30 minutes. Removes cleanly.	

## Features

- Aggressive rubber adhesive provides instant adhesion to a wide variety of surfaces.
- The treated flat stock backing has good tensile strength to resist breakage.
- Special backsize treatment provides easy to use controlled unwind.
- Not recommended for outdoor exposure as it may become difficult to remove.

## Application Ideas

- Holding, bundling and wrapping applications for a wide variety of materials where a stronger paper backing is needed.
- Scotch® Flatback Masking Tape 250 can be certified to meet ASTM D 6123 / D 6123M-97.
- PPP-T42C Type II and CID-A-A-883B are obsolete standards which have been replaced by ASTM D 6123 / D 6123M-97.
- 3M no longer qualifies Scotch® Flatback Masking Tape 250 to meet the inactive specification MIL-F-18264D.
- Scotch® Flatback Masking Tape 250 has been used to conduct testing according to ASTM D-3359; however, this test method does not endorse or suggest that any particular tape must be used.

# Scotch® Flatback Masking Tape

250

---

**Storage** Store under normal conditions of 70°F (21°C) and 50% R.H. in the original carton.

---

**Shelf Life** To obtain best performance, use this product within 18 months from date of manufacture.

---

**Technical Information** The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

---

**Product Use** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

---

**Warranty, Limited Remedy, and Disclaimer** Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

---

**Limitation of Liability** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

---

**ISO 9001**

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

**3M**

**Industrial Adhesives and Tapes Division**

3M Center, Building 225-3S-06  
St. Paul, MN 55144-1000  
800-362-3550 • 877-369-2923 (Fax)  
www.3M.com/industrial



*Recycled Paper*  
40% pre-consumer  
10% post-consumer

Scotch is a registered trademark of 3M.  
Printed in U.S.A.  
©3M 2013 70070945442 (3/13)