



# Automotive Masking Tape 2308

06545 • 06547 • 06548

Technical Data

July 2025

3M Part Numbers	3M Part Descriptor
06545	¾ in. x 60 yds. (18 mm x 55 m), 48 rolls per case
06547	1 ½ in. x 60 yds. (36 mm x 55 m), 24 rolls per case
06548	2 in. x 60 yds. (48 mm x 55 m), 24 rolls per case

## Product Description

3M™ Automotive Masking Tape is a natural-colored crepe paper masking tape designed specifically for general masking applications in the collision repair industry. It is a cost-effective masking tape good for everyday use.

## Features, Advantages, Benefits

Feature	Advantage	Benefit
Proprietary rubber-based adhesive	Instant adhesion and good holding power	Allows for fast and efficient application
Special backsize treatment	Good solvent & moisture resistance and controlled unwind	Easy to handle tape reduces clean-up time and need for rework
Semi-smooth crepe paper backing	Thin, conformable backing	Produces clean, quality paint jobs
Balanced construction	Sticks, stays, and removes cleanly	Efficient masking tool helps save time & money

## Product Uses

Designed for use in the collision repair industry (cars, trucks, other specialty vehicles) for general paint masking.

# 3M™ Automotive Masking Tape 2308

06545 • 06547 • 06548

## Performance Properties



NOTE: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

<b>Adhesion to Steel</b>	32 oz/in (ASTM D-3330)
<b>Tensile Strength</b>	21 lbs/in (ASTM D-3759)
<b>Elongation at Break</b>	9% (ASTM D-3759)
<b>Temperature Use Range</b>	Up to 250°F (121.1°C) for 30 mins
<b>Tape Thickness</b>	5.3 mils (0.13 mm) (ASTM D-3652)

## Directions for Use

Tape is designed for indoor use – exposure to sun and heat may cause tape to become more difficult to remove.

- Make sure surfaces are thoroughly clean and dry before applying masking tape.
- Some surfaces, such as rubber gaskets and moldings, should be cleaned with a solvent to remove residual release agents from the manufacturing process before applying masking tape.
- For best adhesion, surface temperatures should range from 60°F to 90°F when tape is applied.
- For easier application and removal, apply long continuous strips of tape in flat, straight areas and break the tape often when going around contours or curves such as wheel arches. The objective when back masking and over-taping is to keep the tape lying flat and rolled back, away from the paint edge in order to produce the cleanest look.
- Tape removal:
  - For *general applications*, tape should be removed back over itself at a 45° angle.
  - For removal on *delicate surfaces* (such as old weathered paint), tape should be removed as close to a 180° angle as possible.



# 3M™ Automotive Masking Tape 2308

06545 • 06547 • 06548

---

**Applications** General masking applications, including use on apron tapers & other masking machines.

---

**Storage and Handling** Store product in the original carton under normal conditions of 70°F and 50% relative humidity. When stored at the recommended conditions in original, unopened containers, this product has a shelf life of 18 months.

---

**Precautionary Information** Before using this product, please reference Product Label and/or Safety Data Sheet for Health and Safety Information. Note: Laws controlling the acceptable amounts of Volatile Organic Compounds (VOCs) vary by state, and in some cases by locality. For surface preparation and clean-up activities, consult federal, state and local regulations regarding use of products containing VOCs in your area.

---

**Technical Information** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

---

**Product Selection and Use** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

---

**Warranty, Limited Remedy and Disclaimer** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price. Warranty claims must be made within one (1) year from the date of 3M's shipment.

---

**Limitation of Liability** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

# 3M™ Automotive Masking Tape 2308

06545 • 06547 • 06548

---

## Disclaimer

3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and other limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, death, or property damage. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).



Automotive Aftermarket Division  
3M Center, Building 0223-4S-04  
St. Paul, MN 55144-1000  
1-877-666-2277 (1-877-MMM-CARS)  
3MCollision.com

3M is a trademark of 3M Company.  
Printed in U.S.A. © 3M 2025 All rights reserved (07/25)