



Fire Protection Products

3M™ Fire Barrier Sealant IC 15WB+

Technical Data Sheet

January / 2026

Product Description

3M™ Fire Barrier Sealant IC 15WB+ is a cost-effective, one-part, gun-grade, latex-based, intumescent firestop sealant that dries to form a monolithic firestop seal that also acts as a barrier to airborne sound transmission. 3M™ Fire Barrier Sealant IC 15WB+ firestops through penetrations passing through fire-rated floor, floor/ceiling or wall assemblies, as well as other fire-rated interior building partitions and assemblies (e.g. static construction joints or blank openings). In addition, the unique intumescent property of this material allows 3M™ Fire Barrier Sealant IC 15WB+ to expand and help maintain a firestop penetration seal for up to 3 hours as penetrants are exposed to fire. 3M™ Fire Barrier Sealant IC 15WB+ bonds to most construction substrates, including: gypsum wallboard, concrete, metals, wood, plastic (including CPVC) and cable jacketing. No mixing is required.

Product Features

- Firestop tested up to 3 hours in accordance with ASTM E 814 (UL 1479), UL 2079 (ASTM E 1966) and CAN/ULC-S115
- Expanded fire protection systems
- Helps minimize sound transfer —STC-Rating of 54 when tested in STC 54-rated wall assembly
- Sag-resistant
- Excellent adhesion
- Re-enterable/repairable
- Excellent caulk rate
- Paintable
- Water clean up
- Halogen-free, low VOC — *Complies with the intent of LEED® NC-EQ Credit 4.1 for Low-Emitting Materials: Adhesives and Sealants, contains <250 g/L VOC contents (less H2O and exempt solvents per SCAQMD Rule 1168)*

Applications

3M™ Fire Barrier Sealant IC 15WB+ is a general-purpose intumescent firestop ideal for sealing single or multiple through penetrations in fire-rated construction. 3M™ Fire Barrier Sealant IC 15WB+ is typically used in mechanical, electrical and plumbing applications to firestop openings created by the following penetrations in fire-rated floors, floor/ceilings or walls: metallic pipe, plastic pipe, conduit, power and communication cable, cable trays, busways, combos, insulated pipe and HVAC duct penetrations. 3M™ Fire Barrier Sealant IC 15WB+ is also used to firestop blank openings and static construction joints.

3M Fire Protection Products

3M™ Fire Barrier Sealant IC 15WB+

Specifications

3M™ Fire Barrier Sealant IC 15WB+ shall be a one component, ready-to-use, gun-grade, latex-based, intumescent firestop sealant capable of expanding a minimum of 3 times at 1000°F. The material shall be thixotropic and be applicable to overhead, vertical and horizontal firestops. The sealant shall be listed by independent test agencies such as UL, ULC, Intertek or FM. 3M™ Fire Barrier Sealant IC 15WB+ shall be tested to and pass the criteria of ASTM E 814 (UL 1479) Standard Test Method for Fire Tests of Penetration Firestop Systems, ASTM E 1966 (UL 2079) Standard Test Method for Fire Resistive Joint Systems and CAN/ULC-S115 Standard Method of Fire Tests of Firestop Systems. 3M™ Fire Barrier Sealant IC 15WB+ meets the requirements of the IBC, IRC, NBCC, IFC, IPC, IMC, NFPA 5000, NEC (NFPA 70) and NFPA 101.

For technical support relating to 3M™ Fire Protection Products and Systems, call: 1-800-328-1687.

For more information on 3M™ Fire Protection Products, visit: www.3M.com/firestop

Performance and Typical Physical Properties

Color	Yellow
Application Temperature Range (ASTM C 1299)	40° to 122°F (4° to 50°C)
Service Temperature Range	-20° to 180°F (-28° to 82°C)
STC Acoustic Barrier: (ASTM E 90 and ASTM E 413)	54 when tested in STC 54 rated wall assembly
Surface Burning (ASTM E 84)	Flame Spread 5 Smoke Development 50
Hardness (ASTM D240 Shore A)	70
Tensile Strength	85 psi (0.59 MPa)
Volume Shrinkage (ASTM C 1241)	28%
VOC Less H ₂ O and Exempt Solvents*	<2 g/L

Dry: Under typical conditions of 75°F (23°C) and 50% R.H., sealant becomes tack-free in about ten minutes and dry-to-touch in 30 to 60 minutes. Full dry depends upon ambient conditions and volume of sealant. Typical dry rate is approximately 1/8 inch (3 mm) per day.

**Meets the intent of LEED® VOC environmental quality requirements*

Unit Volume: 10.1 fl. oz. tube (300mL), 20 fl. oz. sausage (591 mL), 4.5-gallon pail (17 L)

3M Fire Protection Products

3M™ Fire Barrier Sealant IC 15WB+

Installation Techniques

Consult a 3M Authorized Fire Protection Products Distributor or Sales Representative for applicable UL, ULC, Intertek or other third-party drawings and system details.

Preparatory Work: The surface of the opening and any penetrating items should be cleaned to allow for the proper adhesion of the 3M™ Fire Barrier Sealant IC 15WB+. Ensure that the surface of the substrates is dry and frost free. Sealant can be installed with a standard caulking gun, pneumatic pumping equipment or it can be easily applied with a putty knife or trowel.

Installation Details: Install the applicable depth of backing material, if required, as detailed within the applicable UL, cUL, ULC, Intertek, FM or other third-party listed system. Cut the end of the 3M™ Fire Barrier Sealant IC 15WB+ tube spout to achieve the desired bead width when applying. Install the applicable depth of 3M™ Fire Barrier Sealant IC 15WB+ into the opening flush with the surface of the substrate, or as detailed within the applicable listed system, at the depth for the assembly and rating that is required. Tool within 5 minutes. Clean all tools immediately after use with water.

Limitations: Do not apply 3M™ Fire Barrier Sealant IC 15WB+ when surrounding temperature is than less 40°F (4°C) and in conditions where seals may be exposed to rain or water spray within 18 hours of application. Do not apply 3M™ Fire Barrier Sealant IC 15WB+ to building materials that bleed oil, plasticizers or solvent (e.g. impregnated wood, oil-based sealants, or green or partially vulcanized rubber). Do not apply 3M™ Fire Barrier Sealant IC 15WB+ to wet or frost-coated surfaces or to areas that are continuously damp or immersed in water.

NOTICE: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, the customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for the customer's application, including chemical compatibility with CPVC piping. Before applying any 3M Fire Protection Products or to a system which consists of CPVC pipes or materials, please check CPVC manufacturers' compatibility list.

Maintenance

No maintenance is expected to be required when installed in accordance with the applicable UL, cUL, ULC, Intertek, FM or other third-party listed system. Once installed, if any section of the 3M™ Fire Barrier Sealant IC 15WB+ is damaged, the following procedure will apply: remove and reinstall the damaged section in accordance with the applicable listed system, with a minimum 1/2 in. (12.7 mm) overlap onto the adjacent material.

Storage and Shelf Life

Product packaged in cartridge or pail is enclosed in HDPE plastic containers, sausage is packaged in aluminum foil wrap.

3M™ Fire Barrier Sealant IC 15WB+ should be stored indoors in dry conditions between 40°F and 90°F (4°C and 32°C). Avoid repeated freeze / thaw exposures of the 3M™ Fire Barrier Sealant IC 15WB+ while still in the packaging.

3M Fire Protection Products

3M™ Fire Barrier Sealant IC 15WB+

3M™ Fire Barrier Sealant IC 15WB+ shelf life is 12 months in original unopened containers from date of packaging when stored above 68°F (20°C).

Lot numbering (e.g. 5120Y): First digit = Last digit of year manufactured, second to fourth digit = Julian date, letter = random to distinguish between lot numbers.

Availability

Available from 3M Authorized Fire Protection Products Distributors.
For additional technical and purchasing information, call 1-800-328-1687 or visit 3M.com/firestop.

Safe Handling

Consult Safety Data Sheet prior to handling and disposing of 3M™ Fire Barrier Sealant IC 15WB+

Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Warranty, Limited Remedy and Disclaimer

Warranty: 3M warrants that the Product will be free from defects in material and manufacture during the Extended Warranty Period. If the Product does not conform to this warranty during the Extended Warranty Period, then 3M will, as the sole and exclusive remedy, provide replacement Product (or, if replacement material is unavailable, refund the Product purchase price) for the Project. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE.

This warranty is void if the Product is not installed: (1) in accordance with the applicable UL or Intertek listings; (2) in accordance with the applicable Product data sheet and installation instructions; (3) in accordance with the specifications for the Project; and (4) by a 3M trained Installer. This warranty does not cover damage or failure caused by Product misuse, improper Product storage, improper Product installation, Product or Project abuse, natural disasters, or other force majeure events.

Limitation of Liability

EXCEPT FOR THE LIMITED EXTENDED WARRANTY AND REMEDY STATED ABOVE, AND EXCEPT TO THE EXTENT PROHIBITED BY LAW, 3M WILL NOT BE LIABLE FOR ANY LOSS OR DAMAGE ARISING FROM OR RELATING TO THE PRODUCT, WHETHER DIRECT, INDIRECT, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL, (INCLUDING, BUT NOT LIMITED TO, LOST PROFITS OR BUSINESS OPPORTUNITY), REGARDLESS OF THE LEGAL OR EQUITABLE THEORY ASSERTED, INCLUDING, BUT NOT LIMITED TO, WARRANTY, CONTRACT, NEGLIGENCE, OR STRICT LIABILITY.

Product Selection and Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the 3M product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.



Industrial Specialties Division
3M Center
St. Paul, MN 55144-1000

Phone 800-328-1687
Web 3M.com/firestop

3M and 3M Science. Applied to Life. are trademarks of 3M Company © 3M
2026. All rights reserved.