
Scotchlok[™] Terminals

MV18BC, MV14BC, MV10BC Butt Connector, Vinyl Insulated, Seamless



Data Sheet

Product Number	Wire Range (AWG)	L (in.)	Thickness	Barrel Length	Barrel I.D.	Maximum Insulation Diameter
MV18BC	22-18	1.02	0.031	0.28	0.062	0.125
MV14BC	16-14	1.02	0.031	0.30	0.095	0.155
MV10BC	12-10	1.20	0.038	0.38	0.142	0.218



UNDERWRITERS LABORATORIES STANDARD NO. UL 486C 3M FILE NO. E23438



CANADIAN STANDARDS ASSOCIATION STANDARD NO. 22.2 NO. 0, 65 3M FILE NO. LR22190

Installation Information

riangle warning

Turn power off before installing or removing terminal. All electrical work should be done according to appropriate electrical codes.

UL Listed and CSA Certified for use on stranded copper (AWG) wire only.

Strip away the end 3/8 inch of wire insulation.

Make the crimp in the proper station of a recommended 3M crimp tool: TH-440, TH-450 (scissor style) or TR-490 (ratchet style) hand tools.

Specifications

Wire Size: Barrel Seam:

Insulator Max. Volt. Rating:

Maximum Operating Temp: Maximum Current: Insulator Material: Terminal Material: Terminal Plating:

See Table Above Seamless 600 V Building Wire 1000 V Signs or Fixtures (Luminaires) 221°F (105°C) Same as Wire Vinyl ETP Copper

Tin

Barrel Crimp (Electrical)

Engineering Specification

Crimp-type connectors shall, electrically and mechanically, connect permanently to the pre-stripped ends of two stranded copper wires.

The connector line shall offer barrel variations in wire (AWG) size (22-18, 16-14, 12-10). and construction (non-insulated brazed seam, vinyl insulated butted seam, nylon insulated seamless, etc...). The connector line shall have regulatory agency coverage (UL Listing, CSA Certification). The connectors shall be marked with the wire range and manufacturer's symbol (\uparrow).

The Vinyl Insulated, Seamless Butt Connector shall be tin-plated, annealed copper, having a double-length, round seamless barrel, with a center stop and a close fitting vinyl tube covering, color coded and sized for a specified (AWG) wire range (22-18, 16-14, 12-10).

Insulated connectors shall be UL Listed and CSA Certified for 600 volts maximum, building wire: 1000 volts maximum, signs or fixtures and temperature rated 221°F (105°C) maximum.

3M and Scotchlok are trademarks of 3M.



is a trademark of Underwriters Laboratories.



is a trademark of Canadian Standards Association.

IMPORTANT NOTICE

Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

Warranty; Limited Remedy; Limited Liability. This product will be free from defects in material and manufacture as of the date of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.



Electrical Products Division

6801 River Place Blvd. Austin, TX 78726-9000 http://www.3M.com/elpd