



Control-Flow Seam Sealer

08329

Technical Data Sheet

June 2020

3M Part No.(s)	3M Part Descriptor(s)
08329	3M™ Control-Flow Seam Sealer

Product Description 3M™ Control-Flow Seam Sealer uses two-part urethane technology to provide a tough flexible material for the sealing of joints on primed or painted substrates such as steel or aluminum enclosures. 3M™ Control-Flow Seam Sealer works particularly well in areas where a flowable self-leveling type seam sealer is required, it is designed to flow one to two inches then begins to cure preventing further flow out of the material, this feature allows the user to control application preventing excessive waste while maintaining a uniform film thickness even on surfaces that are not level.

- Features**
- Two-Part Urethane Technology
 - 200 mL Dual - Syringe Cartridge
 - Metered Static Mixing

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Container	200 mL Dual-Syringe Cartridge
Base	Urethane
Density lbs/Gallon (Appx.)	8.6 / 8.7
Color	Black / Amber
Viscosity (CPS) Brookfield Viscometer	Base 1,100 - 1,700 cps
Consistency	Paste
Solvent	N/A
Service Temperature - °F	-20°F to 180°F

3M™ Control-Flow Seam Sealer

08329

Product Uses Typical product uses include automotive “roof ditch” applications where a flow grade sealer is required.

3M™ Control-Flow Seam Sealer flows one to two inches then begins to cure, this feature allows the user to control application preventing excessive waste while maintaining a uniform film thickness even on surfaces that are not level.

Use with the following applicators: PN 08117 (manual), PN 08571 (manual), and PN 09930 (pneumatic).

3M™ Mix Nozzle: PN 08193 (6/bag), PN 8194 (50/box).

For professional use only. Not intended for retail sale.

Typical Performance Properties The following times have been determined with ambient air temperature and substrate temperature @ 70°F (21°C) and are considered typical values.

WORK TIME:

3 minutes

MIX NOZZLE DWELL TIME:

1 minute

CURE TIME:

2 hours

PAINT TIME:

40 minutes

TENSILE STRENGTH:

2490 PSI

ELONGATION:

400%

Directions for Use **NOTE:** 3M Best Practice is that all sealers, unless designated specifically for use on bare metal be applied to properly prepared automotive paint or primer.

SURFACE PREPARATION:

NOTE: Apply only to surfaces primed with a 2K urethane, 2K epoxy primer, or clean, sanded paint. Acid etch primers should never be in direct contact with seam sealer.

1. Scuff primed surface with a Scotch-Brite™ General Purpose Hand Pad (Ultrafine), (PN 07448).
2. Blow off dust with clean, compressed air and wipe with an appropriate VOC compliant surface cleaner for the removal of surface contaminants.

3M™ Control-Flow Seam Sealer

08329

Directions for Use (continued)

PRODUCT PREPARATION:

1. Insert cartridge into applicator gun.
2. Remove retaining collar and plug from end of cartridge. Discard plug & save retaining collar.
3. Extrude a small amount of product until both parts A and B dispense equally.
4. Attach 3M™ Mixing Nozzle (PN 08193) to cartridge and lock in place with retaining collar.
5. Dispense a small amount of material and discard.

GENERAL REPAIR PROCESS:

Extrude sealer onto surface. Allow to cure a minimum of 15 minutes before beginning the painting process.

NOTE: If sealer is allowed to cure more than 24 hours, scuff the sealer prior to any painting steps.

APPLICATION WARNINGS:

Not to be used in direct contact with acid etch primers.

STORAGE:

After initial use, leave mix nozzle in place to seal the cartridge.

CLEAN-UP:

Unmixed material may be cleaned from most surfaces with an appropriate VOC compliant product.

Applications

Typical applications include automotive “roof ditch” and some “trunk rain gutter” seams where the use of a standard “self leveling” sealer is unacceptable due to flow characteristics.

Storage and Handling

HANDLING

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water. Keep out of the reach of children. Keep container closed when not in use. Avoid breathing of dust created by cutting, sanding, grinding or machining. For industrial or professional use only. Avoid eye contact with dust or airborne particles.

STORAGE

When stored at the recommended conditions in original, unopened containers, this product has a shelf life of 12 months from the date of manufacture. Store in a dry area at 72°F for optimal shelf life. Store away from acids and other oxidizing agents.

After use, leave mix nozzle in place to seal the cartridge.

3M™ Control-Flow Seam Sealer

08329

Precautionary Information

Before using this product, please reference Product Label and/or Safety Data Sheet for Health and Safety Information. Note: Laws controlling the acceptable amounts of Volatile Organic Compounds (VOC's) vary by state, and in some cases by locality. For surface preparation and clean-up activities, consult federal, state and local regulations regarding use of products containing VOCs in your area.

Technical Information

The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer

Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price. Warranty claims must be made within one (1) year from the date of 3M's shipment.

Limitation of Liability

Except for the limited remedy stated above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer

3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and other limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, death, or property damage. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.



Automotive Aftermarket Division

3M Center, Building 223-6S-07
St. Paul, MN 55144-1000
1-877-666-2277 (1-877-MMM-CARS)
www.3MCollision.com

3M and Scotch-Brite are trademarks of 3M Company.
Printed in U.S.A.
©3M 2020 P.N. 08329 (6/20)

This is the last page