



Commercial Graphics

Index of 3M Technical Bulletins April 2017



Bulletin No.	Description and URL link	Release Date		
Product Bulletins				
IJ20	3M™ Scotchcal™ Graphic Film Series 20	Feb-16		
IJ25	3M™ Scotchcal™ Graphic Film Series IJ25	Apr-17		
40	3M™ Controltac™ Graphic Film Series 40C & 3M™ Scotchcal™ Graphic Film Series 40	May-15		•
48 & 48C	3M™ Envision™ Print Film 48 & 48C	Jan-16		
50	3M™ Scotchcal™ Graphic Film Series 50	May-14		
80	3M™ Scotchcal™ Opaque Graphic Film Series 80	May-16		
160, 160C	3M™ Controltac™ Graphic Film Series 160; IJ160-10 & 3M™ Controltac™ Graphic Film with Comply™ adhesive 160C-30; IJ160C-10	Apr-17		•
100	3M™ Scotchcal™ Opaque Graphic Film Series 100	May-16		
IJ170Cv3	3M™ Scotchcal™ Graphic Film with Comply™ Version 3 Adhesive IJ170Cv3-10	Nov-15		
180, 180C, IJ180, IJ180C, IJ180Cv3	3M™ Controltac™ Graphic Films Series IJ180, IJ180C, IJ180Cv3	May-16		
IJ380	3M™ Controltac™ Graphic Film IJ380	Feb-15		
480	3M™ Envision™ Print Wrap Film 480Cv3	May-15		
680	3M™ Scotchlite™ Reflective Graphic Film Series 680	Jan-09		
IJ680	3M™ Scotchlite™ Flexible Reflective Graphic Film IJ680-10	Oct-04		
1080	3M™ Car Wrap Film Series 1080	Nov-15		
1380	3M™ Wrap Film Series 1380	Mar-16		
1500v2	3M™ Piezo Inkjet Ink Series 1500v2	May-05		
1900	3M™ Screen Printing Ink Series 1900	Jan-05		
1955	3M™ Overprint Clear & Edge Sealer 1955ABC	Mar-06		
2330	3M™ Scotchcal™ Translucent Graphic Film Series 2330	May-14		
VP1587	3M™ Scotchcal™ Photoluminescent Film VP1587	May-03		
2900	3M™ Scotchlite™ Transparent Screen Printing Ink Series 2900	Jan-05		
3470	3M™ Scotchcal™ Graphic Film Series 3470	Feb-05		
3480	3M™ Scotchcal™ Fluorescent Graphic Film Series 3480	May-05		
3545C	3M™ Controltac™ E-Film with Comply™ Adhesive 3545C	Sep-09		
3630	3M™ Scotchcal™ Translucent Graphic Film Series 3630	Aug-12		
IJ3630	3M™ Scotchcal™ Translucent Graphic Film IJ3630-20	Mar-05		
3635	3M™ Light Management Film Series 3635	Aug-11		
3635-100	3M™ Light Enhancement Film 3635-100	Mar-04		
3635-200	3M™ Dual-Color Film Series 3635-200	May-04		
3650	3M™ Scotchcal™ Graphic Film Series 3650	Feb-08		
VHR3650	3M™ Scotchcal™ Graphic Film Series VHR3650	May-06		
3662-10	3M™ Scotchcal™ Graphic Film for Pavement Graphics 3662-10	Nov-07		
3669	See 3650	Jun-04		
3670	3M™ Scotchcal™ Graphic Film Series 3670	Jun-04		
3700	3M™ Envision™ Translucent Film Series 3730	Feb-13		
IJ3730	3M™ Envision™ Translucent Films IJ3730-50 and IJ3730-60	Oct-12		
3735-50 & 3635-60	3M™ Envision™ Diffuser Films 3735-50, 3735-60	Oct-12		
3690	3M™ Scotchcal™ Graphic Film Series 3690	Jun-04		
3950	3M™ Edge Sealer 3950	Jun-01		
4000	3M™ Piezo Ink Jet Ink Series 4000	Jan-04		
4150S	3M™ Edge Sealer 4150S	Jun-01		

4600	3M™ Piezo Ink Jet Ink Series 4600	Jul-04		
5525SE	3M™ Scotchcal™ ElectroCut™ Graphic Film Series 5525SE-300	Jul-09		
6645C	3M™ Controltac™ Removable Graphic Film with Comply™ Adhesive 6645C	Oct-06		
6800	3M™ Piezo Ink Jet Ink Series 6800	Nov-03		
6900	3M™ Piezo Inkjet Ink Series 6900	Apr-13		
7725SE	3M™ Scotchcal™ ElectroCut™ Dusted/Frosted Graphic Film Series 7725SE-300 and 7725SE-400 Fluorescent Films	Jul-04		
7755SE-400	3M™ Scotchcal™ ElectroCut™ Mirror Graphic Film Series 7755SE-400	Aug-11		
7755SE-520	3M™ Scotchcal™ Translucent Mirror Film 7755SE-520	Oct-07		
8150	3M™ Scotchcal™ Clear View Graphic Film 8150	Jul-10		
8173	3M™ Scotchcal™ Perforated Window Graphic Film 8173 and RG8173	Oct-07		
8991	Scotchgard™ Graphic and Surface Protection Film 8991	Aug-11		
8993	Scotchgard™ Graphic and Surface Protection Film 8993	Feb-12		
8995	Scotchgard™ Graphic and Surface Protection Film 8995-124	Feb-12		
9730 UV Clear	3M™ Screen Print Matte Clear 9730UV	Mar-12		
9740i UV Clear	3M™ Screen Print UV Gloss Clear 9740i	Mar-12		
9800	3M™ Screen Printing Ink Series 9800UV	May-07		
VSC17848	3M™ Envision™ Print Film VSC17848	Apr-17		●
VSC17876	3M™ Envision™ Print Film VSC17876	Apr-17		●
Application Tapes	Application Tapes	Sep-11		
Cleaner	3M™ Cleaner for Matte Wrap Films – Product & Instruction Bulletin	Apr-16		
D1	3M™ DI-NOC™ Architectural Finishes	May-12		
Dichroic	3M™ Dichroic Glass Finishes DF-PA	Nov-13		
Fasara	3M™ Fasara™ Glass Decorative Films	Apr-15		
Graffiti Remover	3M™ Graffiti Remover System	Feb-01		
Graphic Remover	3M™ Graphic Remover System	Aug-98		
Overlaminates	3M UK Commercial Graphics Overlaminates	Aug-15		
QRG	Quick Reference Guide for all Commercial Graphics' Films	May-16		
Snitty	3M™ Snitty (Cutting Tool)	Feb-16		
Surface Preparation	Surface Preparation System	Feb-08		
Instruction Bulletins				
1.0 Theory				
1.1	Preparation for 4-Colour Screen Printing	Nov-02		
2.0 Design of Markings and Signs				
2.1	Design of Markings Featuring Films and Sheetings	Mar-94		
2.4	Design of Cabinets for Light Boxes and Channel Letters using 3M™ Light Enhancement Film 3635-100	Sep-01		
3.0 Screen Printing				
3.4	Screen printing with 3M™ Screen Printing Ink Series 9700UV (Line inks)	May-05		
3.11	Screen printing with 3M™ 4-Colour Screen Printing Ink Series 1900	Jul-00		
3.12	Screen Printing with 3M™ Screen Printing Ink Series 1900 (line inks)	Jul-00		
3.12.2	3M™ Overprint Clear & Edge Sealer Series 1955 ABC	Jul-00		
3.13	Screen Printing with 3M™ 9700 Series UV 4-Colour Inks	May-05		
3.18	Screen Printing with 3M™ Scotchlite™ Screen Printing Ink Series 2900 (line colour)	Jan-05		
3.19	Screen Printing with 3M™ Scotchlite™ Four Colour Screen Printing Ink Series 2900	Aug-01		
3.20	Screen printing with 3M™ Screen Printing UV Ink Series 9800	May-07		
3.21	Screen Printing with 3M™ 4-Colour UV Inks Series 9800	May-07		
4.0 Finishing Operations				
4.1	Scoring and Cutting of Films	May-02		
4.3	3M™ Application Tapes Premasking and Prespacing for Films	Mar-10		

4.22	Cold Roll Lamination for 3M™ Laminates	Aug-97		
4.22.1	Lamination Techniques for Convertors of Laminating Adhesives	Oct-06		
4.26	Making Backlit Signs with 3M Digitally –Printed Graphics (Replaces 5.17)	Feb-02		
4.27	Piezo Ink Jet Printing with 3M™ Piezo Ink Jet Ink Series 4000 for VUTEk UltraVu™ 3000/3300 and 5000/5300 Printers	Feb-04		
4.28	Ink Change-Over 3M™ Piezo Ink Jet Ink Series 4000 Used in VUTEk UltraVu™ 3000/3300 and 5000/5300 Printers	Jul-01		
4.35	Piezo Ink Jet Printing with 3M™ Piezo Ink Jet Series 2300 For VUTEk Ultra Vu™ 2360/3360 Printers	Mar-04		
4.38	Piezo Ink Jet Printing with 3M™ Piezo Ink Jet Ink Series 6700	Mar-04		
4.39	Piezo Ink Jet Printing with 3M™ Piezo Ink Jet Series 6000 for the Océ Arizona 30 Printer	Mar-04		
4.4	Piezo Ink Jet Printing with 3M™ Piezo Ink Jet Ink Series 6800	Nov-03		
4.43	Piezo Ink Jet Printing with 3M™ Piezo Ink Jet Ink Series 4600 For Scitex Pressjet-W™ Digital Press	Mar-05		
4.45	Piezo Ink Jet Printing with 3M™ Piezo Ink Jet Ink Series 1500 For VUTEk UltraVu™ 150 and 2360/3360/3300/5300 Printers	May-05		
5.1	Substrate Selection, Preparation and Substrate-specific Application Techniques	Mar-15		
5.1.1	Surface Preparation, Graphic Removal and Application of Replacement Graphics on Rail Transport Vehicles	Mar-17		●
5.4	Special Applications and Vehicles	Feb-15		
5.4.7	Application of 3M Di-Noc Films: A guide for indoor and outdoor applications	Mar-11		
5.5	General Procedures for Interior and Exterior Dry Applications	Apr-07		
5.7	Application Wet Method for Translucent Screen Printed, Thermal Mass Transfer, and Cut Graphics. Replaces Instruction Bulletins 5.8, 5.9, 5.10 and the previous version of Instruction Bulletin 5.7	May-05		
5.7.1	Application Wet Method for 3M™ Scotchcal™ Clear View Graphic Film 8150	Jul-10		
5.8.1	Applying 3M™ Scotchshield™ Glass Protection Film	undated		
5.8.2	Application & Removal of 3M™ Dichroic Glass Finish DF-PA	Nov-13		
5.16	Thermoforming With Selected 3M™ Films	Apr-02		
5.31	Applying 3M™ Graphic Films with Comply™ Adhesive	Jul-00		
5.33	Application and Maintenance of Scotchprint® Graphics for Pavements	Nov-00		
5.37	A Guide to Understanding and Applying Graphics to Common Wall Surfaces	May-04		
5.41	Application of 3M™ Controltac™ Graphic Film IJ380	Nov-07		
5.46	Application on Substrates with Recesses and Removal 3M™ Envision™ Print Wrap Film 480Cv3	May-15		
5.47	3M™ Wrap Film Series 1380 Application on Substrates with Recesses	Jun-16		
6.0 Installation, Maintenance, Repair and Removal				
6.4.2	How to Remove 3M™ Scotchlite™ Reflective Sheeting	Nov-99		
6.5	Storage, Handling, Maintenance and Removal of Films and Sheetings	Nov-09		
Additional Application Instructions				
A16	Inlay method for Applications to Recessed Panels and Recessed Areas	Aug-15		
A18	Application Instructions - Guidelines for Graphic Repair on Vehicular Transport	Jun-03		
Ink change-over	Cold Roll Lamination for 3M™ Laminates	Apr-13		
Warranty				
Warranty	3M™ MCS™ & Select Warranty	Apr-16		

NB: The bulletins contained in this document are subject to review, please check with your technical representative to ensure you have the most current bulletin.

Commercial Graphics
3M United Kingdom plc
3M Centre, Cain Road
Bracknell, Berkshire RG12 8HT
United Kingdom
Tel: 01344 858000
Email: commgraphics.uk@mmm.com

Commercial Graphics - Customer Service
4th Floor Building 8
Exchange Quay, Salford Quays
Manchester M15 3EJ
Tel: 01344 857000
commgraphics.uk@mmm.com

3M Ireland Limited
The Iveagh Building
The Park
Carrickmines
Dublin 18
Tel: 00 353 1 280
3555Email: commgraphics.uk@mmm.com

www.3m.co.uk/graphicsolutions
www.3m.co.uk/innovativefinishes
facebook.com/3MGraphicsUK
twitter.com/3MGraphicsUK