
3M

Cold Shrink[™] Jacket Kits

SJ-1A, SJ-2A & SJ-3A



Data Sheet

1. Product Description

3M™ SJ series Cold Shrink™ Splice Jacket Kits are a series of open ended, tubular, rubber sleeves that combined with Scotch™ 2228 Rubber Mastic Tape provide a sealed jacket over cable splices installed on Jacketed Concentric Neutral (JCN) and other types of jacketed power cable. The Scotch™ 2228 Rubber Mastic Tape provides for an assured sealing interface between the cable jacket and the Cold Shrink™ Jacket tube. It is also used to seal around a cable ground conductor. The Cold Shrink™ Jacket tube is provided in an expanded state, mounted on two inner supporting plastic cores. As supplied in this prestretched condition, the tube is ready for field installation. The jacketing tube is made of EPDM rubber which contains no chlorides or sulfurs. Three kit sizes cover an application range of 0.95″ (24 mm) to 4.0″ (101,6 mm).

Kit Contents:

Each kit contains sufficient quantity of the following materials to jacket one cable splice.

- 1 Cold ShrinkTM Jacketing Tube
- 1 Three Foot (914 mm) Roll Of Scotch™ 2228 Rubber Mastic Tape

Features:

Easy to install, requires only workman's hands. Simply center over splice area and unwind core from each end to shrink in place.

Versatile one-piece jacket that accommodates a wide range of cable sizes and splice diameters.

No torches or heat required.

Seals tight, retains its resiliency and pressure even after years of aging and exposure.

Tough rubber formulation to withstand rough back filling.

Water resistant. Meets the water seal requirements of ANSI C119.1.

Compatible with cable jackets and cable semi-conducting insulation shields.

Provides for a seal around cable ground conductor.

Resists fungus.

Resists acids and alkalies.

Resists ozone and ultraviolet light.

2. Applications

To jacket inline splices installed on Jacketed Concentric Neutral (JCN) Cables rated 15, 25 and 35 kV and operating temperature of 90°C and an emergency overload rating of 130°C.

Physical protection and moisture sealing inline splices installed on shielded power cables having solid dielectric insulation as follows: polyethylene (high and low density), cross-linked polyethylene (XLP) and ethylene propylene rubber (EPR).

For use at indoor and outdoor installations including direct burial, aerial and submersible applications.

Typical Value*

wt. gain

1.8%

A. Typical Physical and Electrical Properties EPDM Rubber

Physical Properties

Moisture Absorption

7 days 90°C (194°F) H₂O

Test Method

	<u> </u>
• Color	Black
 300% Modulus (ASTM D 412–75) 	480 psi (3,3 MPa)
 Ultimate Tensile (ASTM D 412–75) 	1400 psi (9,6 MPa)
 Ultimate Elongation (ASTM D 412–75) Original 	750%
 Die C Tear (ASTM D 624C-73) Original 	150 pli (26,3 KN/m)
 Fungus Resistance (ASTM G–21) 28 days exposure 	No Growth

Electrical Properties

Test Method	Typical Value*
Dielectric Strength	

(ASTM D 149-75) Original @ 1,78 mm

• 7 days in H₂O at 90°C (194°F)

365 V/mil (14,3 MV/m)

282 V/mil (11,1 MV/m)

Scotch™ 2228 Rubber Mastic Tape

Physical Properties

Test Method	Typical Value*
• Color	Black

Thickness (ASTM D-1000) — Overall

0.065" (1,65 mm) - EPR Backing 0.030''(0,76 mm)- Mastic Layer 0.035''(0.89 mm)

 Adhesion to steel 15 lbs/in. (ASTM D-1000) (0,17 MPa)

0.15%

 Water Absorption (ASTM D-570)

Electrical Properties

Test Method Typical Value*


 Dielectric Strength (ASTM D-1000

— Dry 500 V/mil (19,6 kV/mm)

- Wet 500 V/mil (19,6 kV/mm)

All values are averages and are not intended for specification purposes.

B. Typical Dimensions



Jacket	Approximate Core			Approximate Minimum	Approximate Maximum	
Kit	Length			Installed Length	Installed Length	
SJ-1A	26.5"	24.0"	2.85"	23.0"	27.0"	
	(673 mm)	((610 mm)	(72,4 mm)	(584 mm)	(686 mm)	
SJ-2A	31.0"	27.0"	3.87"	32.0"	35.0"	
	(787 mm)	(686 mm)	(98,3 mm)	(813 mm)	(889 mm)	
SJ-3A	J–3A 32.0" 28.0" (711 mm)		4.50" (114,3 mm)	33.0" (838 mm)	37.0" (940 mm)	

Table 1

C. Cold Shrink™ Jacket Kit Selection Table

Jacket Kit	Minimum Cable Jacket O.D.	Maximum Splice O.D.	Maximum Cable Jacket Opening	3M 15 kV Splice Number	3M 25 kV Splice Number	3M 35 kV Splice Number
SJ-1A	0.95" (24,1 mm)	2.4" (61,0 mm)	20" (508 mm)	5411 5411A 5412 5411R*	_	_
SJ–2A	1.15" (29,2 mm)	3.3" (83,8 mm)	28" (711 mm)	5403 5404 5405 5406	5420 5421 5422 5451 5452	5432 5461
SJ-3A	1.55" (39,4 mm)	4.0" (101,6 mm)	30" (762 mm)	5407 5408 5409	5423 5424 5425 5426	5433

^{*3}M 5411R QSII requires an additional 8428–12 Cold Shrink™ Tube to jacket splice. The procedure for jacketing the 5411R QSII is detailed in the SJ-1A kit installation instruction.

3. Maintenance

Components of the 3M SJ Series Cold Shrink™ Splice Jacket Kit are not impaired by freezing or overheating due to ambient temperatures found in storage or shipping. Normal

stock rotation procedures are recommended. 3M Cold ShrinkTM removable core material is polypropylene and recyclable with other $\frac{d}{dp}$ waste.

'3M', 'Cold Shrink' and 'Scotch' are trademarks of 3M.

Important Notice to Purchaser:

All statements, technical information and recommendations related to the Seller's products are based on information believed to be reliable, but the accuracy or completeness thereof is not guaranteed. Before utilizing the product, the user should determine the suitability of the product for its intended use. The user assumes all risks and liability whatsoever in connection with such use.

Any statements or recommendations of the Seller which are not contained in the Seller's current publications shall have no force or effect unless contained in an agreement signed by an authorized officer of the Seller. The statements contained herein are made in

lieu of all warranties expressed or implied, including but not limited to the implied warranties of merchantability and fitness for a particular purpose which warranties are hereby expressly disclaimed.

SELLER SHALL NOT BE LIABLE TO THE USER OR ANY OTHER PERSON UNDER ANY LEGAL THEORY, INCLUDING BUT NOT LIMITED TO NEGLIGENCE OR STRICT LIABILITY, FOR ANY INJURY OR FOR ANY DIRECT OR CONSEQUENTIAL DAMAGES SUSTAINED OR INCURRED BY REASON OF THE USE OF ANY OF THE SELLER'S PRODUCTS.



Electrical Products Division

6801 River Place Blvd. Austin, TX 78726-9000 800–245–3573