


# Scotchlok<sup>™</sup> Terminals

# MVU18-187DF, MVU14-187DF

Female Disconnect, Vinyl Insulated, Butted Seam



# **Data Sheet**

Product Number	Wire Range (AWG)	Mates with <u>Male Tab</u> Width (W´)  x Thickness	L	Barrel Length	Barrel I.D.	Maximum Insulation Diameter
MVU18-187DF	26-20	0.187 x 0.020	0.78	0.25	0.085	0.145
MVU14-187DF	16-14	0.187 x 0.020	0.78	0.25	0.085	0.145



UNDERWRITERS LABORATORIES STANDARD NO. UL 310 3M FILE NO. E70512



CANADIAN STANDARDS ASSOCIATION STANDARD NO. 22.2 NO. 0, 65 3M FILE NO. LR22190

### **Installation Information**

#### **△WARNING**

Turn power off before installing or removing terminal. All electrical work should be done according to appropriate electrical codes.

UL Listed and CSA Certified for use on stranded copper (AWG) wire only.

Strip away the end 3/8 inch of wire insulation.

Make the crimp in the proper station of a recommended 3M crimp tool: TH-440, TH-450 (scissor style), or TR-490 (ratchet style) hand tools.

### **Specifications**

Wire Size: See Table Above
Barrel Seam: Butted
Maximum Voltage Rating: 600V Building Wire

1000 V Signs or Fixtures (Luminaires)

Tin

Maximum Operating Temp: (105°C) 221°F Maximum Current: Same as Wire Insulator Material: Vinyl Terminal Material: Brass

Plating:



Barrel Crimp (Electrical)

Suitable for factory installation on steel or brass tabs, UL and CSA.

Suitable for field application on brass tabs, strain relief is required. UL only.

### **Engineering Specification**

Crimp-type female disconnects shall, electrically and mechanically, connect permanently to the prestripped end of a stranded copper wire: and have a tongue portion with fingers which grip a male disconnect in a separable, reusable manner, forming a quick connect wiring termination.

The connector line shall offer tongue variations (sized to grip male tabs: 0.250" x 0.032" or 0.187" x 0.020" per ANSI/NEMA CD-2), and barrel variations in wire (AWG) size: (22-18, 16-14, 12-10) and construction (non-insulated, vinyl insulated and nylon fully insulated insulated, etc.). The female disconnects shall have regulatory agency coverage (UL Listing, CSA Certified). The tongue portion shall be marked with the wire range and manufacturer's symbol (↑).

The vinyl insulated female disconnect, shall be tin plated 0.016" thick brass with a tongue for gripping a 0.187" x 0.020" male tab per ANSI/NEMA CD-2 and a 0.250" long barrel with a tin plated brass funnel entry insulation grip, covered by a molded vinyl sleeve, color coded and sized for a specified (AWG) wire range (Red, 22-18: Blue, 16-14).

Insulated connectors shall be UL Listed and CSA Certified for 600 volts minimum, building wire: 1000 volt maximum; signs or fixtures (luminaires) and temperature rated 221°F (105°C) maximum.

Female Disconnects shall be suitable for field or factory wiring, with a UL Recognized strain relief required.

3M and Scotchlok are trademarks of 3M.



(UL) is a trademark of Underwriters Laboratories.



is a trademark of Canadian Standards Association.

#### IMPORTANT NOTICE

Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

Warranty; Limited Remedy; Limited Liability. This product will be free from defects in material and manufacture as of the date of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.



**Electrical Products Division**