

3M Gripping Material Trial Bags

Adhesive backed

TB400	Firm
TB731	Firm/clear
TB614	Ultra Soft
TB631	Very Soft
TB641	Soft

Technical Data

October, 2011

Product Description

3M™ Gripping Materials are based on 3M's proprietary micro- replicated technology. 3M Gripping Materials consists of a high-friction surface developed to enhance grip and reduce slippage. These adhesive backed Gripping Materials utilize this high-friction surface with a thin flexible backing laminated with an acrylic pressure sensitive adhesive which is good for low surface energy surfaces. These gripping products are designed to be used alone, or as a two- part mated system. When used alone on a single surface, 3M soft gripping material provides a strong secure grip. When used as a two-part mated system, for example a glove and handle bar, grip strength is maximized. As firmly as 3M gripping material holds, it releases just as easily.

These Trial Bags are meant for sampling and setting up prototypes. These same materials can be purchased in larger quantities with the "GM" designation.

Converting and Application

3M™ Gripping Material TB400, TB731, TB614, TB631, and TB641

These Trail Bags are designed to give you enough product for testing and prototyping your application ideas.

These pressure sensitive adhesive backed products can be shear cut, die-cut, or converted by other application methods. When used as a handle wrap, material should be wrapped so edges overlap opposite the stress direction. If wrapped handle is to be used in a pushing mode, overlap the wraps from top to bottom. If handle is to be used in pulling mode, overlap wraps from bottom to top. The leading and ending edges of the wrap should be secured with end caps or tape designed for that purpose. Minimum tension should be used to avoid stretching and distortion of the product. Avoid direct contact with heated processing surfaces, in excess of 160°F (71°C), for prolonged periods of time.

3M™ Gripping Material Trial Bags

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Trial Bag Number (Corresponding "GM" number)	3M™ Gripping Material				
	TB400 (GM400)	TB731 (GM731)	TB614 (GM614)	TB631 (GM631)	TB641 (GM641)
	Typical Values		Typical Values		
Gripping Material Product Type	Thermoplastic Polyurethane 5 mil acrylic pressure sensitive adhesive		Thermoplastic Elastomer 5 mil acrylic pressure sensitive adhesive		
Carrier Type	Polyester mesh		Polyester knit		
Weight - oz/yd ² (g/m ²)	without liner	12.9 (440)	15.45 (524)		
	with liner	15.8 (535)	18.29 (620)		
Thickness - mils (mm)	without liner	33 (0.8)	42 (1.07)		
Stem Height - mils (mm)		20 (0.508)	20 (0.508)		
Stems Density (stems/in ²)		3000	3000		
Color	Black	Clear	Dark Grey	Dark Grey	Black
Texture	Firm	Firm	Ultra Soft	Very Soft	Soft
Hardness - Shore A	75	75	15	30	40
Durability	Very high	Very high	Low	Medium	High
Coefficient of Friction ASTMD-1894**:					
dry - kinetic coefficient of friction	1.1	1.1	2.8	3.3	3.5
wet - kinetic coefficient of friction	0.98	0.98	2.6	3.0	3.4
Taber Abrasion ASTM D3389 (CS-10 500g) 500 revolutions					
Stem damage	100%	100%	90%	75%	3%
Temperature Range - °F (°C)	-40 to 160 (-40 to 71)		-40 to 160 (-40 to 71)		
Optimum Usable					

**Coefficient of Friction is a property of the mechanical contact between two mating surfaces, in this case each material was tested against its mating part. For example 3M™ Gripping Material GM613 was tested against TB614, GM630 against TB631 and GM640 was tested against TB641.

3M™ Gripping Material Trial Bags

Care and Maintenance Instructions

3M™ Gripping Material TB400, TB731, TB614, TB631, and TB641

The gripping material can be hand washed with mild detergent in cool to warm water once it is affixed to a handle or part.

Surface contamination – lint or other debris – can be easily removed with a Scotch® Lint Roller and Scotch® Lint Sheets, or other lint removing mechanisms.

Do not bleach

Do not iron

Do not use in a dryer

Do not dry clean

Product Availability

3M™ Gripping Material TB400, TB614, TB631, TB641, TB731

Trial Bag sizes:	2 rolls;	1 inch (2.5 cm) x 15 feet (4.5 m)
	6 sheets;	6 inch (15.2 cm) x 7 inch (17.8 cm)

Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2008

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2008 standards.



Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (Fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

3M is a trademark of 3M Company.
Scotch is a registered trademark of 3M Company.
Printed in U.S.A.
©3M 2011 (10/11)