

3M Commercial Solutions

3M™ Window Graphic Film 8170-P50



For Striking Window Views

NEW & IMPROVED

Film 8170-P50 offers all the benefits of a high-performance cast vinyl film plus versatility for cross-platform printing. It's the window film you can count on for longer term appearance.

Conformability and great lifting resistance

As the only cast vinyl perforated film on the market, it provides better conformability (think rear windows) and greater lifting resistance than calendared vinyl films and yet easy to remove.

Great image and see-through capabilities

The 50% perforation pattern enhances light transmission, providing vibrant image quality balanced with excellent see-through capability. It is print compatible with UV, latex, solvent, and eco-solvent printers for ink jet and screen printing.

Durability for peace of mind

This premium film is backed by the 3M™ MCS™ Warranty and 3M Performance Guarantee.

3M Commercial Solutions

3M Center, Building 220-12E-04, St. Paul, MN 55144 USA
General and technical information 1-800-328-3908

NOTE: Use with 3M™ Scotchcal™ Optically Clear Overlaminate 8914 for the best optical clarity, protection and a high gloss finish.

KNOW IT:

Bookmark 3Mgraphics.com/windows Visit the website for complete product details including product and instruction bulletins and warranted applications.

BUY IT: Visit 3Mgraphics.com/wheretobuy or call 1-800-328-3908

TRY IT: Try [this sample](#) and see for yourself

