3M Precision Automotive Masking Tape 03491 • 03492

Technical Data Sheet

July, 2014

3M Part No.(s)	3M Part Descriptor(s)
03491	1/4 in. x 35 yd., 24 rolls per case
03492	1-1/2 in. x 35 yd., 24 rolls per case

Product Description 3MTM Precision Automotive Masking Tape is a specially designed ultra- thin & smooth flat masking tape that makes it ideal for achieving extremely sharp paint lines, and is compatible with both solvent and waterborne paint systems. The thin backing also allows for the adhesive to visibly wet out so it is easy to see the even adhesion that results in high holding power, crisp paint lines, and a low-profile paint edge. 3MTM Precision Automotive Masking Tape is a suitable option on all automotive surfaces, including metal, glass, rubber, and plastic and can be easily removed without tearing or adhesive transfer upon completion of a paint job.

Features	Advantages	Benefits
1. Proprietary acrylic adhesive	1. Excellent instant adhesion to all automotive surfaces - metal, glass, rubber and plastic	1. Allows for fast and efficient application
2. Ultra-thin, smooth backing	2. Good holding power yet removes easily without tearing or adhesive transfer	2. Produces sharp, low profile paint edges
3. Premium balanced construction	3. Can cut through layers of color and clear coat for easy removal after completing a job	3. Resists edge bleed with all paints, especially waterborne colors
4. Thin backing allows for visibility as adhesive wets out for assured evenness	4. Bonds completely and tears easily	4. Easy and clean removal for minimal cleanup labor time
	 Proprietary acrylic adhesive Ultra-thin, smooth backing Premium balanced construction Thin backing allows for visibility as adhesive wets 	1. Proprietary acrylic adhesive1. Excellent instant adhesion to all automotive surfaces - metal, glass, rubber and plastic2. Ultra-thin, smooth backing2. Good holding power yet removes easily without tearing or adhesive transfer3. Premium balanced construction3. Can cut through layers of color and clear coat for easy removal after completing a job4. Thin backing allows for visibility as adhesive wets4. Bonds completely and tears easily

Properties

ote: The following technical information and data should be considered representative o typical only and should not be used for specification purposes.

Adhesion to Steel	10.4 ounces/inch width	ASTM D-3330
Tensile Strength	15.5 lbs/inch width	ASTM D-3759
Elongation at Break	6%	ASTM D-3759
Tape Thickness	3.5 mils (0.09mm)	ASTM D-3652
Temperature Use Range	Up to 250°F (121°C) for up to 30 minutes	

3M[™] Precision Automotive Masking Tape

03491 • 03492

Product Uses	High performance masking tape for use in all automotive repair and painting applications.
Performance Properties	Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.
	• Crisp, sharp paint lines with no edge bleed
	Smooth and easy unwind
	• Good paint anchorage reduces the possibility of paint flaking
	• Translucent backing makes it easy to see what you are masking and when the tape is completely adhered
	Solvent and moisture resistant backing
	• Safe for taping on fresh base coats when applying multiple colors
	• Great for masking long, straight paint lines
	• Special acrylic adhesive resists UV degradation making it safe to place masked vehicle outside
Directions for Use	Make sure surfaces are thoroughly clean and dry before applying masking tapes. For best adhesion results, surface temperatures of 60-90°F (16-27°C) for application are recommended. Press the entire width of the tape down firmly to ensure good adhesion and avoid lifting. Designed for indoor and outdoor use with UV resistance for up to 3 weeks. Longer term exposure to sun and heat is not recommended as it may cause tape to become very difficult to remove. Should be removed by pulling up from surface at a 90 degree angle to avoid slivering or adhesive transfer to the surface.
Storage and Handling	For best performance use this product within 12 months from the date of manufacture. Store product in the original carton under normal conditions of 50 to 80°F (10 to 27°C) and 50% relative humidity.

3M[™] Precision Automotive Masking Tape 03491 • 03492

Precautionary Information	Refer to Product Label and Material Safety Data Sheet for Health and Safety Information before using this product. See link below: http://solutions.3m.com/wps/portal/3M/en_US/MSDS/Search/?gsaAction=msdsSRA&msdsLocate=en_US
Technical Information	The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.
Product Use	Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.
Warranty, Limited Remedy, and Disclaimer	Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.
Limitation of Liability	Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

For Additional Health and Safety Information



Automotive Aftermarket Division

3M Center, Building 223-6N-01 St. Paul, MN 55144-1000 1-877-666-2277 (1-877-MMM-CARS) www.3M.com/automotive

3M is trademark of 3M Company. Printed in U.S.A. ©3M 2014 All rights reserved. (7/14)