

Safety is at work

Protective eyewear with prescription lenses

Product Bulletin

3M™ Locking System

Patent Pending

NEW CONCEPT IN PERMANENT SIDESHIELD ATTACHMENT

Benefits:

- Made of nylon and 3M™ heat shrink tubing; no natural latex rubber
- Helps reduce issues from riveted sideshields
- Installed with frame warmer or heat gun
- Two sizes of heat shrink tubing to cover most temple sizes
 - 3/8" dia. fits most temple sizes; 1/2" dia. fits oversized temples
- Patent pending

Pricing:

- Single Pair Package (contains both regular and oversized heat shrink tubing): \$1.25



Locking bar placed in hole of sideshield



3M™ heat shrink tubing slipped over locking bar and temple



Heat from frame warmer or heat gun shrinks tubing and locks sideshield

Personal Safety Division
Occupational Prescription Eyewear
2925 Gary Drive, Plymouth, IN 46563 USA
Customer Service: 800.982.2828
www.3M.com/SafetyRx

