

## 3M™ Cross-Connect Cabinets

### Innovative technology

- 3M cabinets bring you cutting-edge, rigorously tested materials. Powder-base, anti-static paint.
- Heavy-gauge construction. Stainless steel hardware. Base isolation for moisture and pest protection.
- Long-term durability aimed at helping you keep costs down.

### A vast product offering

- A vast selection of cabinet lines — pad mount, pole mount and stake mount — means there's a product for almost every need. You also get one-stop convenience with a full line of accessories, all developed in-house to provide a fully integrated solution.



## 3M™ Quick Connect System (QCS) 2810

The 3M Quick Connect System 2810 is an easy-to-use, tool-less copper block designed specifically for high-capacity performance you can trust. This insulation displacement connector (IDC) termination system from 3M features convenient tool-less jumpering; high-integrity, gel-encapsulated connectivity; maximum jumper visibility; as well as low-force, pair-at-once termination for enhanced productivity.



3M is a trademark of 3M Company.

### Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

### Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of 12 months from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether indirect, special, incidental or consequential regardless of the legal theory asserted.**



### Communication Markets Division

6801 River Place Blvd.  
Austin, TX 78726-9000  
800/426 8688  
Fax 800/626 0329  
www.3M.com/Telecom

Please recycle. Printed in USA.  
© 3M 2014. All rights reserved.  
80-6114-9890-0

## 3M Cross-Connect Solutions





Reliable  
CROSS-Connect  
Solutions



## 1 3M™ Quick Connect System 2810

- Simple-to-use, tool-less block
- Gelled connection
- Ideal for outdoor applications
- Protects connection to help eliminate contamination
- **Modular:** Available for pre-terminated applications in a 50-pair block or field-terminated applications in a 10-pair strip



## 2 3M™ Quick Connect System 2811

- Simple-to-use, tool-less copper block
- Protects connection to help eliminate contamination
- Ideal for indoor applications
- **Modular:** Available for pre-terminated applications in a 50-pair block or field-terminated applications in a 10-pair strip



## 3M™ Building Entrance Terminals

- Utilize flame retardant 3M Quick Connect System blocks
- High-performance, compact solution to help deploy high-speed networks



## 3M™ Cross-Connect Cabinets

- Pad-, pole- and stake-mount cabinets available
- Easy to use, maintain and expand as your network grows
- Full range of parts and accessories for different applications



## Other Applications

- Frame solutions for 3M™ Quick Connect System that are easily mounted blocks in in-building premises applications
- Add-on terminals
- Expansion kits and sealants
- Cable terminals