



# Adhesive Transfer Tape with Adhesive 300MP 9772WL, 9773WL, 9774WL, 9775WL

## Product Data Sheet

September 2022  
Supersedes: March 2014

### Product Description

3M™ Transfer Adhesive 300MP provides an good bond to various fabricated foams, fabrics, substrates, and has good shear strength at elevated temperatures. These tapes also meet the highly variable needs of most gasket fabricators.

### Properties

- High adhesion to a variety of substrates.
- Good roll stability.
- Suitable for: Metal, plastics, paper, rubber, textile, felt, plywood, etc.

### Construction

Product	Adhesive thickness	Carrier	Liner, Colour, Thickness Weight
9772WL	0,051 mm	None	Polycoated Paper, White unprinted 0,172 mm, 161 g/qm
9773WL	0,076 mm		
9774WL	0,100 mm		
9775WL	0,128 mm		

### Performance Characteristics

Adhesion FINAT FTM 2, 90°, 300 mm/Min. 0,150 mm Alu. in N/25 mm		9772WL	9773WL	9774WL	9775WL
72 h at RT	Stainless Steel	23,4	21,0	39,6	28,8
	ABS	24,4	14,6	34,0	19,2
	Polypropylene	11,8	11,8	15,4	13,3
72 h at 70°C	Stainless Steel	29,5	38,4	58,1	48,5
72 h at 38°C 98% R.H.	Stainless Steel	28,1	29,8	30,9	36,9
24 h at 120°C	Stainless Steel	45,7	41,0	54,3	47,1
Shear strength FINAT FTM 8, 25 mm * 25 mm Alu. on steel		9772WL	9773WL	9774WL	9775WL
1000 g, RT		> 5000 Minutes			
250 g, 70°C		> 5000 Minutes			

---

<b>Temperature Resistance</b>	Long term (days, weeks): 70°C Short term (minutes, hours): 120°C
<b>Storage</b>	Store in cool and dry conditions at room temperature  Product retains its performance properties for two years from date of manufacture.
<b>For Additional Information</b>	To request additional product information or to arrange for sales assistance, call..... Address correspondence to: 3M
<b>Automotive Disclaimer</b>	<p>Automotive Applications: This product is an industrial product and has not been designed or tested for use in certain automotive applications, including, but not limited to, automotive electric powertrain battery or high voltage applications. This product does not fully adhere to typical automotive design or quality system requirements, such as IATF 16949 or VDA 6.3. This product may not be manufactured in an IATF certified facility and may not meet a Ppk of 1.33 for all properties. The product may not undergo an automotive production part approval process (PPAP). Customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's automotive application and for conducting incoming inspections before use of the product. Failure to do so may result in injury, death, and/or harm to property. No written or verbal statement, report, data or recommendation by 3M related to automotive use of the product shall have any force or effect unless in an agreement signed by the Technical Director of 3M's Automotive Division. Customer assumes all responsibility and risk if customer chooses to use this product in an automotive electric powertrain battery or high voltage application, and 3M will not be liable for any loss or damage arising from or related to the 3M product or customer's use of the product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity or recall costs), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability. In no event shall 3M be liable for any damages in excess of the purchase price paid for the product.</p> <p>NOTWITHSTANDING ANY OTHER STATEMENT TO THE CONTRARY, 3M MAKES NO REPRESENTATIONS, WARRANTIES OR CONDITIONS WHATSOEVER, EXPRESS OR IMPLIED, REGARDING THE PRODUCT IF USED IN AN AUTOMOTIVE ELECTRIC POWERTRAIN BATTERY OR HIGH VOLTAGE APPLICATION, INCLUDING, BUT NOT LIMITED TO, ANY WARRANTY ON PERFORMANCE, LONGEVITY, SUITABILITY, COMPATIBILITY, OR INTEROPERABILITY, OR ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE.</p>

---

## Important Notice

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law

---

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations

---

3M is a trademark of the 3M Company.

**3M United Kingdom PLC**  
2M Centre, Cain Road, Bracknell  
RG12 8HT  
United Kingdom

**3M Ireland Ltd**  
The Iveagh Building, 3rd Floor  
The Park, Carrickmines 18  
Ireland

**3M Belgium bvba/sprl**  
Hermeslaan 7  
1831 Diegem  
Belgium

**3M Nederland B.V.**  
Molengraaffsingel 29  
2629 JD Delft  
The Netherlands

**3M Svenska AB**  
Herrjärva torg 4  
170 67 Solna  
Sweden

**3M a/s**  
Hannemanns Allé 53  
DK-2300 Copenhagen S.  
Denmark

**3M Norge AS**  
Tærudgata 16  
2004 Lillestrøm  
Norway

**Suomen 3M Oy**  
Keilaranta 6  
02150 Espoo  
Finland

**3M Eesti OÜ**  
Pärnu mnt. 158  
11317 Tallinn  
Estonia

**3M Latvia SIA**  
K.Ulmaņa gatve 5  
Rīga, LV-1004  
Latvia

**3M Lietuva UAB**  
A.Goštauto g. 40  
Vilnius LT- 03163  
Lithuania