



3M™ Versaflo™ TR-600 Series

Parts and Accessories

TR-600 Series



Part Number/AAD	General Description	Description	Replace when maximum life is reached or when/if:	UPC Ordering #
System Kits				
TR-600-ECK/37375	Easy Clean PAPR Kit	Kit includes: S-433L Hood with Integrated Head Suspension, BT-30 Length Adjusting Breathing Tube, TR-6710N (HE) Filter, TR-641N Single Station Battery Charger, BT-922 Breathing Tube Cover, TR-602N PAPR Unit, TR-630 Standard Battery, TR-627 Easy Clean Belt, TR-6700 Filter Cover, TR-6600 Prefilter (x2), TR-662 Spark Arrestor (x2), TR-971 Airflow Indicator	replace component(s) in kit based on guidance in table below, and/or reference component user instructions	00051131373754
TR-600-HIK/37374	Heavy Industry PAPR Kit	Kit includes: M-307 Respiratory Hard Hat Assembly with Premium Visor and Faceseal, TR-602N PAPR Unit, TR-632 High Capacity Battery, BT-30 Length Adjusting Breathing Tube, TR-626 High Durability Belt, TR-6530N OV/AG/HE Cartridge, TR-6500 Filter Cover, TR-641N Single Station Battery Charger Kit, TR-971 Airflow Indicator, BT-926 High Temperature Breathing Tube Cover, TR-6600 Prefilter (x2), TR-662 Spark Arrestor (x2)	replace component(s) in kit based on guidance in table below, and/or reference component user instructions	00051131373747

TR-600-HKS/HKL	Head Cover PAPR Kit	Kit includes: S-133 Soft Headtop, TR-971 Airflow Indicator, TR-6710N Filter, TR-641N Single Station Battery Charger, TR-653 Cleaning and Storage Kit, TR-991 Carrying Bag, TR-602N PAPR Unit, TR-630 Standard Battery, BT-30 Length Adjusting Breathing Tube, TR-627 Easy Clean Belt, TR-6700FC Filter Cover	replace component(s) in kit based on guidance in table below, and/or reference component user instructions	HKS: 00051131274990 HKL: 00051131275010
Series Assemblies				
TR-613N/37339	PAPR Assembly	PAPR Assembly: includes blower unit (TR-602N), flow indicator (TR-971), high durability belt (TR-626), standard battery (TR-630), and length adjusting breathing tube (BT-30).	replace component(s) in assembly based on guidance in table below, and/or reference component user instructions	00051131373396
TR-614N/37340	PAPR Assembly	PAPR Assembly: includes blower unit (TR-602N), flow indicator (TR-971), Easy clean belt (TR-627), standard battery (TR-630), and length adjusting breathing tube (BT-30).	replace component(s) in assembly based on guidance in table below, and/or reference component user instructions	00051131373402
TR-616N/37341	PAPR Assembly	PAPR Assembly: includes blower unit (TR-602N), flow indicator (TR-971), high durability belt (TR-626), high capacity battery (TR-632), and length adjusting breathing tube (BT-30).	replace component(s) in assembly based on guidance in table below, and/or reference component user instructions	00051131373419
TR-617N/37342	PAPR Assembly	PAPR Assembly: includes blower unit (TR-602N), flow indicator (TR-971), Easy clean belt (TR-627), high capacity battery (TR-632), and length adjusting breathing tube (BT-30).	replace component(s) in assembly based on guidance in table below, and/or reference component user instructions	00051131373426
Component Parts				
TR-602N/37338	Blower	Replacement Blower for Versaflo™ TR-600	damaged or unable to resolve alarms	00051131373389
TR-626/37343	Belt	High Durability belt for Versaflo™ TR-600/ TR-800 PAPR	damaged	00051131373433
TR-626X/37344	Belt Extender	Belt extender for TR-626 High Durability Belt	damaged	00051131373440
TR-627/37345	Belt	Easy Clean belt for Versaflo™ TR-600/TR-800 PAPR	damaged	00051131373457
TR-627X/37346	Belt Extender	Belt extender for TR-627 Easy Clean Belt	damaged	00051131373464
TR-630/37347	Battery	Standard battery for Versaflo™ TR-600 PAPR	damaged or no longer achieving desired run-time	00051131373471
TR-632/37348	Battery	High capacity battery for Versaflo™ TR-600 PAPR	damaged or no longer achieving desired run-time	00051131373488
TR-642N	Charger	3M™ Versaflo™ Single Station Battery Charger Kit TR-642N	damaged, broken, or unable to charge battery	

TR-642-3	Charger add-on	3M™ Versaflo™ 3-Station Battery Charger Pack Only TR-642-3, (cable not included)	damaged, broken, or unable to charge battery	
TR-6600/37354	Prefilter	Prefilter for Versaflo™ TR-600/TR-800 PAPR	damaged or clogged	00051131373549
TR-662/37355	Spark Arrester/ Prefilter	Spark arrester/Prefilter for Versaflo™ TR-600/ TR-800 PAPR	damaged or unable to clean	00051131373556
TR-6710N-5/37357 TR-6710N-40/37358	Filter	HE Filter for Versaflo™ TR-600/TR-800 PAPR	damaged or when change is indicated by the PAPR low flow alarm	00051131373575 00051131373582
TR-6320N/37363	Filter/ Cartridge	Acid Gas/HEPA Cartridge for Versaflo™ TR-600/TR-800 PAPR	damaged, when change is indicated by the PAPR low flow alarm, when indicated by service life software, or if breakthrough is detected	00051131373636
TR-6350N/37365	Filter/ Cartridge	Formaldehyde/HEPA Cartridge for Versaflo™ TR-600/TR-800 PAPR	damaged, when change is indicated by the PAPR low flow alarm, when indicated by service life software, or if breakthrough is detected	00051131373650
TR-6360N/37364	Filter/ Cartridge	Ammonia/Methylamine/HEPA Cartridge for Versaflo™ TR-600/TR-800 PAPR	damaged, when change is indicated by the PAPR low flow alarm, when indicated by service life software, or if breakthrough is detected	00051131373643
TR-6510N/37361	Filter/ Cartridge	Organic Vapor/HEPA Cartridge for Versaflo™ TR-600/TR-800 PAPR	damaged, when change is indicated by the PAPR low flow alarm, when indicated by service life software, or if breakthrough is detected	50051131373612
TR-6530N/37362	Filter/ Cartridge	Organic Vapor/Acid Gas/HEPA Cartridge for Versaflo™ TR-600/TR-800 PAPR	damaged, when change is indicated by the PAPR low flow alarm, when indicated by service life software, or if breakthrough is detected	00051131373629

TR-6590N	Filter/ Cartridge	Multi-Gas/HEPA Cartridge for Versaflo™ TR-600 PAPR	damaged, when change is indicated by the PAPR low flow alarm, when indicated by service life software, or if breakthrough is detected	50051131373667
TR-6700FC/37356	Filter Cover	Filter cover for 6700 series filters for Versaflo™ TR-600/TR-800 PAPR	damaged or broken. No longer securely attaches to filter/ cartridge	00051131373563
TR-6300FC/37380	Filter Cover	Filter cover for 6300 series filter/cartridge for Versaflo™ TR-600/TR-800 PAPR	damaged or broken. No longer securely attaches to filter/ cartridge	00051131373808
TR-6500FC/37381	Filter Cover	Filter cover for 6500 series filter/cartridge for Versaflo™ TR-600/TR-800 PAPR	damaged or broken. No longer securely attaches to filter/ cartridge	00051131373815
TR-971/56707	Flow Indicator	Flow indicator for Versaflo™ TR-600/TR-800 PAPR (for loose fitting headgear)	damaged	00051141567075
TR-973	Flow Indicator	Flow indicator for Versaflo™ TR-600/TR-800 PAPR (for tight fitting facepieces)	damaged	
TR-651/37382	Filter Latch	Replacement filter latch assembly for TR-602N blower	damaged	00051131373822
TR-653/37373	Cleaning/ Storage Kit	Cleaning and Storage Kit for TR-602N/ TR-802N PAPR, and TR-630/TR-632/TR-830 batteries	damaged, broken, gaskets changed after 30 washings	00051131373730
TR-654/37384	Cleaning/ Storage Kit	Replacement gaskets for TR-653 cleaning and storage kit	damaged, broken, gaskets changed after 30 washings	00051131373846
BT-953	Cleaning/ Storage Kit	3M™ Versaflo™ Cleaning and Storage Kit BT-953	damaged	
BT-20S	Breathing Tube	3M™ Versaflo™ Breathing Tube, BT-20S/ 37309(AAD), Small/Medium	damaged, broken, holes, cuts or tears	
BT-20L	Breathing Tube	3M™ Versaflo™ Breathing Tube BT-20L, Medium/Large	damaged, broken, holes, cuts or tears	
BT-30	Breathing Tube	3M™ Versaflo™ Length Adjusting Breathing Tube, BT-30	damaged, broken, holes, cuts or tears	
BT-40	Breathing Tube	3M™ Versaflo™ Neoprene Breathing Tube, BT-40	damaged, broken, holes, cuts or tears	
BT-63	Breathing Tube	3M™ Versaflo™ Length Adjusting Tight Fitting Breathing Tube BT-63	damaged, broken, holes, cuts or tears	
BT-64	Breathing Tube	3M™ Versaflo™ Heavy-Duty Tight-Fitting Breathing Tube, BT-64	damaged, broken, holes, cuts or tears	
BT-957	Breathing tube Storage Plug	3M™ Versaflo™ Storage Plugs BT-957	damaged	
TR-681	PAPR Cover	3M™ Versaflo™ PAPR Cover TR-681	damaged	

BT-922	Breathing tube cover	3M™ Versaflo™ Breathing Tube Cover BT-922	damaged	
BT-926	Breathing tube cover	3M™ Speedglas™ Breathing Tube Cover BT-926 (high temperature)	damaged	
TR-927	Backpack	3M™ Versaflo™ Easy Clean Backpack, TR-927	damaged	
BPK-HD	Backpack	3M™ Speedglas™ Heavy Duty Backpack BPK-HD	damaged	
TR-655/37385	Backpack Adapter	Backpack Adaptor to connect TR-602N to BPK-01 or alternate belts TR-325, TR-326 or TR-327 (not shown)	damaged	00051131373853

 **WARNING**



These respirators help protect against certain airborne contaminants. Before use, the wearer must read and understand the User Instructions provided as a part of the product packaging. A written respiratory protection program must be implemented meeting all the requirements of OSHA 1910.134 including training, fit testing and medical evaluation. In Canada, CSA standards Z94.4 requirements must be met and/or requirements of the applicable jurisdiction, as appropriate. **Improper use may result in injury, sickness or death.** For correct use, see supervisor and *User Instructions*, or call 3M PSD Technical Service in USA at 1-800-243-4630 and in Canada at 1-800-267-4414.

For More Information

In U.S.

Technical Assistance: 1-800-243-4630, Hours of Operation: 8:00 a.m. – 4:30 p.m. CST

Customer Care Center: 1-800-328-1667, Hours of Operation: 7:00 a.m. – 5:00 p.m. CST

Internet: 3M.com/PPESafety, 3M.com/Versaflo



Personal Safety Division

3M Center, Building 235-2W-70
St. Paul, MN 55144-1000

3M Canada

P.O. Box 5757
London, Ontario
N6A 4T1

In United States of America

Technical Service: 1-800-243-4630
Customer Service: 1-800-328-1667
3M.com/workersafety

3M is a trademark of 3M. Used under license in Canada. © 2026, 3M. All rights reserved. Please recycle.

3M PSD products are occupational use only.

In Canada:

Technical Service: 1-800-267-4414
Customer Service: 1-800-6880
3M.ca/Safety