


3M Industrial Adhesives and Tapes

3M™ Dual Lock™ Reclosable Fasteners



# Unlock simplicity

Hundreds of  
reattachments in a snap



# Strong and simple to use

## 3M™ Dual Lock™ Reclosable Fasteners

Not all design requirements are easily satisfied, but you can simplify your attachments. When you need a strong, reliable, yet removable closure or attachment, 3M™ Dual Lock™ Reclosable Fasteners are the easy alternative to traditional fastening methods such as screws, nuts or bolts.

- Strong, interlocking mushroom-shaped heads close with a snap to assure your design is securely fastened.
- The many adhesive options help to reduce concerns of material damage and deformation, fastener placement, contamination and corrosion, and the challenges of joining dissimilar materials.
- Works behind the scenes as an invisible fastener to create a snug fit and smooth lines for improved aesthetics and sleek appearances.
- Provides the application ease of tape and the durability of a traditional fastener.

## Experience the simplicity

- Durable — up to 1,000 openings and closings before losing 50% of original tensile strength
- Helps reduce vibration
- Temperature, moisture and UV resistant
- Strong pressure sensitive adhesive bonds on contact
- Application and maintenance ease
- Low profile option available — approximately half the thickness of the standard fastener



### Reliable Performance

Strong, interlocking mushroom-shaped heads connect with an audible “snap”; Peel apart to open; Easily attach and detach multiple times

### Customize for Your Application

Mix and match stem densities for the ideal closure strength; Choose from a variety of widths and adhesive options

### Quick and Easy to Install

Adhesive sticks on contact to a variety of materials without special tools (no drilling, screwing, sewing); Non-adhesive product also available

### Design Flexibility

Lightweight and low profile; Fastener is hidden beneath the surface and does not interfere with the integrity of the design; No holes or traditional fastener marks



# Select the right 3M™ Dual Lock™ Reclosable Fastener for the job



Product	Stem Density (per sq/in)	Adhesive	Color	3M Liner	Engaged Thickness	Temperature Resistance	Substrates					Use	Applications						
							Metals (Al, SS)	Glass	Plastics (Acrylic, PC, ABS)	Powder Coated Paints	Low Surface Energy (PP, PE)		Interior Panels (Walls, doors, headliner, storage)	Accessory Attachment	Curtain Rails	Seats			
<b>Specialty Vehicle</b>												Indoor/Outdoor							
<b>SJ3550</b>	250	White Acrylic	Black	Clear, 4mil (0.10mm) Polyolefin	0.23 in (5.7mm)	200°F (93°C)	■	●	■	▲	▲	Indoor/Outdoor	■	■	■	■			
<b>SJ3551</b>	400																		
<b>SJ3552</b>	170																		
<b>SJ3560</b>	250	Clear Acrylic	Clear	Clear, 4mil (0.10mm) Polyolefin	0.23 in (5.7mm)	220°F (104°C)	●	■	●	▲	▲	Indoor/Outdoor	●	●	●	●			
<b>SJ4570</b>	Low Profile	Low Surface Energy Acrylic	Clear	Brown, 83# Polykraft	0.098 in (2.489mm)	158°F (70°C)	●	●	●	■	■	Indoor	●	●	●	●			



<b>General Industrial</b>							Metals (Al, SS)	Glass	Plastics (Acrylic, PC, ABS)	Powder Coated Paints	Low Surface Energy (PP, PE)	Indoor/Outdoor	Panel Assembly	Accessory Attachment	General Attachment	Floor Attachment			
<b>SJ3550</b>	250	White Acrylic	Black	Clear, 4mil (0.10mm) Polyolefin	0.23 in (5.7mm)	200°F (93°C)	■	●	■	▲	▲	Indoor/Outdoor	■	■	■	■			
<b>SJ3551</b>	400																		
<b>SJ3552</b>	170																		
<b>SJ3560</b>	250	Clear Acrylic	Clear	Clear, 4mil (0.10mm) Polyolefin	0.23 in (5.7mm)	220°F (104°C)	●	■	●	▲	▲	Indoor/Outdoor	●	●	●	●			
<b>SJ4570</b>	Low Profile	Low Surface Energy Acrylic	Clear	Brown, 83# Polykraft	0.098 in (2.489mm)	158°F (70°C)	●	●	●	■	■	Indoor	●	●	●	●			



<b>POP, Display and Signage</b>							Metals (Al, SS)	Glass	Plastics (Acrylic, PC, ABS)	Powder Coated Paints	Low Surface Energy (PP, PE)	Indoor/Outdoor	Trade Shows and Exhibits	Point of Purchase Displays	General Signage	Interior Design			
<b>SJ3550</b>	250	White Acrylic	Black	Clear, 4mil (0.10mm) Polyolefin	0.23 in (5.7mm)	200°F (93°C)	●	●	●	▲	▲	Indoor/Outdoor	●	●	●	●			
<b>SJ3551</b>	400																		
<b>SJ3552</b>	170																		
<b>SJ3560</b>	250	Clear Acrylic	Clear	Clear, 4mil (0.10mm) Polyolefin	0.23 in (5.7mm)	220°F (104°C)	●	●	●	▲	▲	Indoor/Outdoor	●	●	●	●			
<b>SJ4570</b>	Low Profile	Low Surface Energy Acrylic	Clear	Brown, 83# Polykraft	0.098 in (2.489mm)	158°F (70°C)	■	■	■	■	■	Indoor	■	■	■	■			

## Meet the environmental and strength requirements for the application

Temperature Performance	
<b>Best</b>	SJ3560
<b>Better</b>	SJ3550
<b>Good</b>	SJ4570

Stem Density (per sq/in) Combinations	
<b>Strongest</b>	250:400
<b>Stronger</b>	250:250
<b>Strong</b>	170:250
<b>Not Recommended</b>	170:170 or 400:400

Interchangeable Strength Combinations		
Type 400	Type 250	Type 170

Self-Mating
Low Profile

KEY
■ Best Suggested Product
● Alternate Suggested Product
▲ Alternate Product — Must Use Primer

# Solve attachment challenges in an instant

Choosing 3M™ Dual Lock™ Reclosable Fasteners can solve attachment challenges in an instant with the confidence that you've made the best decision for how your project will look when it's unveiled. Plus with the super strong bonds of 3M™ VHB™ Tape and powerful, interlocking mushroom-shaped heads, it also means you've chosen strength and easy to use reliable performance for the long run.

## Ordering Information

Product	Stem Density (per sq/in)	Adhesive	3M Liner	Color	Description
<b>SJ3550</b>	250	Acrylic		Black	3M™ Dual Lock™ Reclosable Fasteners, Black, Type 250, 45.7m in length
<b>SJ3551</b>	400	Acrylic	Clear, 4mil (0.10mm) Polyolefin	Black	3M™ Dual Lock™ Reclosable Fasteners, Black, Type 400, 45.7m in length
<b>SJ3552</b>	170	Acrylic		Black	3M™ Dual Lock™ Reclosable Fasteners, Black, Type 170, 45.7m in length
<b>SJ3560</b>	250	Clear Acrylic	Clear, 4mil (0.10mm) Polyolefin	Clear	3M™ Dual Lock™ Reclosable Fasteners, Clear, Type 250, 45.7m in length
<b>SJ4570</b>	LP	Low Surface Energy Acrylic	Brown, 83# Polykraft	Clear	3M™ Dual Lock™ Reclosable Fasteners, Low Profile, Clear, 45.7m in length
<b>Industrial Trial Bags - Australia</b>					
<b>TB3550</b>	250	Acrylic	Clear, 4mil (0.10mm) Polyolefin	Black	3M™ Dual Lock™ Reclosable Fastener, 250/250, Black, 25.4mm x 3.05m, 1 Mated Strip/Bag
<b>TB3560</b>	250	Clear Acrylic	Clear, 4mil (0.10mm) Polyolefin	Clear	3M™ Dual Lock™ Reclosable Fastener, 250/250, Clear, 25.4mm x 3.05m, 1 Mated Strip/Bag
<b>TB4570</b>	LP	Low Surface Energy Acrylic	Brown, 83# Polykraft	Clear	3M™ Dual Lock™ Reclosable Fastener, Low Profile, Clear, 25.4mm x 3.05m, 1 Mated Strip/Bag
<b>Industrial Small Packs - New Zealand</b>					
<b>MP3541/42</b>	170/400	Rubber	White, 5mil (0.13mm) Polyolefin	Black	3M™ Dual Lock™ Reclosable Fastener, 170/400, Black, 25.4mm x 4.5m, 1 Mated Strip/Bag
<b>MP3551/52</b>	170/400	Acrylic	Clear, 4mil (0.10mm) Polyolefin	Black	3M™ Dual Lock™ Reclosable Fastener, 170/400, Black, 25.4mm x 4.5m, 1 Mated Strip/Bag
<b>MP3560</b>	250/250	Clear Acrylic	Clear, 4mil (0.10mm) Polyolefin	Clear	3M™ Dual Lock™ Reclosable Fastener, 250/250, Clear, 25.4mm x 4.5m, 1 Mated Strip/Bag

For more information visit: [3Mfasteners.com.au](http://3Mfasteners.com.au) or call 136 136 in Australia  
[fastening.co.nz](http://fastening.co.nz) or call 0800 362 880 in New Zealand



**3M Australia Pty Ltd  
 Industrial Adhesives &  
 Tapes Division**  
 Bldg A, 1 Rivett Road  
 North Ryde NSW 2113  
 Australia  
 Phone: 136 136  
[www.3Mfasteners.com.au](http://www.3Mfasteners.com.au)

**3M New Zealand Ltd  
 Industrial Adhesives &  
 Tapes Division**  
 94 Apollo Drive, Albany  
 Auckland, New Zealand  
 Phone: 0800 362 886  
[www.fastening.co.nz](http://www.fastening.co.nz)

**Product Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application.

**Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

3M, Dual Lock and VHB are trademarks of 3M Company. All rights reserved.  
 Please recycle. Printed in Australia. © 3M 2015. All rights reserved. AV011442355



Secure plastic signs to window glass



Attach cushioning panels in an ambulance or bus



Secure vehicle accessories to dashboard



Attach access panels to industrial, electronic, and electrical equipment



Attach elevator control panel to interior wall



Fasten ceiling panels to interior for future access