

**3M** Science.  
Applied to Life.™

## Increase your brand visibility.

### 3M™ Perforated Window Graphic Film 8170-P50

3M's perforated window film can turn your vehicle into valuable advertising space without obstructing driving visibility. Compared to calendered vinyl film, this high-performance cast vinyl film offers better conformability and excellent lifting resistance for a longer lasting appearance. Plus the durability of this film is backed by the industry-leading 3M™ MCS™ Warranty and 3M Performance Guarantee. So you can use your vehicle to build your brand with eye-catching graphics that will leave a lasting impression.

Meet your new go-to film at  
[3M.com/windowwraps](http://3M.com/windowwraps).

This product is 50% film with 50% perforation and features 3M™ Scotchcal™ Optically Clear Overlaminate 8914 that provides true optical clarity for graphics.

3M and MCS are a trademarks of 3M. Used under license in Canada. © 3M 2017. All rights reserved.  
75-5100-3934-2

