Scotch[®] High Temperature Fine Line Tape

3M

4737S • 4737T

Product Description	Scotch® High Temperature Fine Line Tape 4737 is a vinyl paint masking tape for fascia, rocker panels, two-tone and other multiple color applications where critical paint break lines are required.				
Product Construction	Backing Adhesiv		ve Color	Standard Roll Lengtl	
	Vinyl	Rubber	Scotch® Tape 4737S - Blue (Solid)	36 yds. (32.9 m)	
			Scotch® Tape 4737T - Blue (Translucent)		
Typical Physical Properties			ical information and data should l should not be used for specification	n purposes.	
	or typic Adhesion to Ste	al only and s	should not be used for specification 10.5 oz./in. width (11.5 N/100 mm	n purposes. ASTM Test Method	
	or typic	al only and seel:	should not be used for specification	ASTM Test Method D-3330	
Properties	Adhesion to Ste	al only and seel: h: reak:	should not be used for specification 10.5 oz./in. width (11.5 N/100 mm) 16 lbs./in.width (280 N/100 mm)	ASTM Test Method D-3330 D-3759	
	Adhesion to Ste Tensile Strengt Elongation at B	al only and seel: h: reak:	10.5 oz./in. width (11.5 N/100 mm 16 lbs./in.width (280 N/100 mm) 115%	ASTM Test Metho D-3330 D-3759 D-3652	
	Adhesion to Ste Tensile Strengt Elongation at B Tape Thickness Temperature Us *Has been laborate up to 300°F (149) given application	eel: h: reak: se Range: ory tested on sta PC) for 30 minu and can vary de	10.5 oz./in. width (11.5 N/100 mm) 16 lbs./in.width (280 N/100 mm) 115% 5.4 mils (0.137 mm)	ASTM Test Methor D-3330 D-3759 D-3759 D-3652 minutes:* hesive residue at bake temperatures on ance may be higher or lower for a itions (i.e. multiple bake cycles and the	

- Outstanding fine line color separation.
- Smooth trimmed edges create a continuous straight paint line.
- Designed for indoor use.
- Vinyl backing is heat resistant for one piece removal.
- Functions with high temperature paint bake cycles.
- Minimal neck down when stretched for accurate paint lines.
- Scotch® Tape 4737S Solid backing aids in seeing contrast with substrate color.
- Scotch® Tape 4737T Translucent backing allows visual confirmation of adhesive wet out on substrate.
- Conformable to allow ease of application in areas of tight radii and depressions.

Scotch® High Temperature Fine Line Tape

4737S • 4737T

Application Ideas	Ideal for the transportation OEM industry for paint masking of metal and plastic surfaces.			
Storage	Store under normal conditions of 70°F (21°C) and 50% R.H. in the original carton.			
Shelf Life	To obtain best performance, use this product within one year from date of manufacture.			
Technical Information	The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.			
Product Use	Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.			
Warranty, Limited Remedy, and Disclaimer	Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.			
Limitation of Liability	Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.			





This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2008 standards.