


Take the guesswork out of mixing chemicals.


Accuracy is more important than ever. Over-diluted chemicals can result in decreased efficacy, and with today's cleaning challenges you need to know your surfaces are clean. With the added complication of removing viruses from surfaces — including SARS-CoV-2 — you can't afford to guess.

3M™ Chemical Management Solutions control the flow of water by adjusting to changing water pressures, providing an accurate ready-to-use (RTU) solution.

3M outperforms the competition.

When six leading competitive dispensers were tested over a dynamic water pressure range of 20–120 psi, 3M had the lowest dilution error.





Competitor		
80 psi	30 psi	
20L — 22qt. 20qt. 15L — 16qt. 10L — 12qt. 8qt. 5L — 4qt.	20L — 22qt. 20qt. 15L — 16qt. 10L — 12qt. 8qt. 5L — 4qt.	

Potential Consequences of Inaccuracy.

Over-Dilution (too much water)		
	Decreased efficacy of over-diluted chemicals	
Ineffective disinfectant	Potential HAI and outbreak risk	
	Higher potential for increased infection/absentee rates	
	Non-compliance with EPA label	
Ineffective	Re-cleaning of surfaces	
cleaning	Increased labor to counter performance issues of incorrectly mixed concentrates, overall costs	
ability	Potential for harmful exposure due to manual dilution	

Under-Dilution (too much chemical)		
Increased	Over-budgeting/increased cost due to inconsistent chemical dispensing	
exposure	Potential for harmful exposure and worker safety hazards	
and costs	Surface degradation caused by overly acidic or basic chemical mixes, increasing replacement costs	
	Higher frequency of sticky floors/surfaces	
Excess	Re-cleaning of surfaces	
residue	Additional labor/effort, increasing labor and product costs	
	Potential for harmful exposure due to manual dilution	





Accuracy and sustainability go hand in hand.

You don't need to sacrifice your sustainability goals for effective cleaning and disinfection. The correct combination of chemical concentrate and water prevents excess depletion of valuable disinfectants to eliminate product waste and reduce water usage.



Improved dilution accuracy reduces waste and minimizes chemical use.



As many as seven 3M™ Cleaning Concentrates are Green Seal™ Certified, and all are concentrated to maximize value and cut packaging waste.



Many 3M Cleaning Concentrates are packaged in bottles made with 25% post-consumer recycled content.



Using 3M[™] Chemical Management Solutions can help contribute to LEED certification.

Fighting a new foe: SARS-CoV-2.

You and your staff have an even harder job to do with the arrival of SARS-CoV-2, the virus that causes COVID-19. The right disinfectant matched with best practices can help you keep your facility clean and protected without significant impact on your process, productivity or cost. Follow these best practices for proper disinfection:

Ensure accurate dilution. Accuracy is more important now than ever. Choose a chemical management solution that's proven to maximize accuracy.

Keep high-touch surfaces clean. Frequent disinfection of high-touch areas can help stop the spread of germs.¹

Adhere to dwell times. Without proper dwell times, you may leave germs on surfaces.

EPA registered for the SARS-CoV-2 efficacy claim with a 1 minute dwell time

3M[™] Quat Disinfectant Cleaner Concentrate (#5)

3M™ MBS Disinfectant Cleaner Fresh Scent Concentrate (#41)

3M™ Neutral Quat Disinfectant Cleaner (#23)

3M™ MBS Disinfectant Cleaner Concentrate (#42)

3M™ Disinfectant Cleaner RCT Concentrate (#40)

The right solution for your cleaning challenges.



3M™ Flow Control Wall Mount System.

Minimize worker interaction with chemicals and help ensure you have the right concentration of disinfectant to kill germs, including SARS-CoV-2, on surfaces. With its unique flow control technology, the 3M Flow Control Wall Mount System delivers accurate cleaning solutions directly into your containers.

Whether you're cleaning a hospital, classroom, office building or retail space, you know you're getting the right amount of chemicals to do the job.

- At least 55% more accurate dilution²
- 17-49% more compact³ while holding up to four half-gallon bottles
- Simple dispensing dial improves efficiency and productivity
- Three-point locking system limits chemical exposure and helps prevent theft
- Compatible with 25 different 3M[™] Cleaning Concentrates
- 3M Flow Control concentrate bottles are made with 25% post-consumer recycled content and are BPA-free
- Compact size measurements: 12.25" w x 22.5" h x 6.3" d

The 3M™ Flow Control Portable Dispensing System.

Reusable, portable dispensers are designed for durability, comfort and the same accuracy as the wall dispenser.



- Improved flexibility, convenience and staff productivity
- Designed for half-gallon bottles of 3M Cleaning Concentrates
- Foaming adapter sold separately

3M [™] Flow Control Systems Dispensing Reduction	Low End	High End
Estimated pounds/year reduced into drain	55%	96%
Quats	263	460
Detergents	197	345
Total estimated reduction of disinfectant/detergent substances	461	806

For context, the American Hospital directory lists 4,000 hospitals in the U.S., with a total of 810,000 beds. An average healthcare facility in highly populated states with a large number of hospitals (e.g., New York and Massachusetts) has 250–350 beds; the largest hospitals in these state have 1,000–2,500 beds. These estimates are based on sales data for three cleaning solution products at three hospital facilities, averaged to represent a 500-bed facility. and.com/state_statistics.html



3M™ Cleaning and Disinfecting Solutions are a component of the 3M™ Clean & Protect Certified Badge Program, which helps you demonstrate your commitment to a clean environment to your employees and guests. Contact a 3M representative for information on how to participate.

A simple twist mixes any chemical you need.

3M™ Twist 'n Fill™ Chemical Management System.

Using a single dispenser makes diluting solutions easier and more efficient. The 3M™ Twist 'n Fill™ System accurately dilutes and dispenses virtually any cleaning solution. Just pick a 3M™ Twist 'n Fill™ System chemical concentrate, insert your bottle, and twist and fill. Simple. Efficient. Accurate.

- Fits almost any cleaning closet
- One dispenser mixes over 30 chemicals
- Change out chemicals in seconds
- Air gap prevents backflow

With two flow rates, 3M™ Twist 'n Fill™ Chemical Management System can easily dilute solutions for mop bucket and spray bottles.



Get your customized wall chart.

Help your staff determine what chemicals to use. Choose from set templates and customize the information for your specific facility, or we can also help you create a completely custom wall chart for your team. For details, visit 3M.com/facility.

3M [™] Twist 'n Fill [™] Chemical Management System Reduction	Low End	High End
Estimated pounds/year reduced into drain	36%	96%
Quats	172	460
Detergents	130	345
Total estimated reduction of disinfectant/detergent substances	302	806

For context, the American Hospital directory lists 4,000 hospitals in the U.S., with a total of 810,000 beds. An average healthcare facility in highly populated states with a large number of hospitals (e.g., New York and Massachusetts) has 250–350 beds; the largest hospitals in these state have 1,000–2,500 beds. These estimates are based on sales data for three cleaning solution products at three hospital facilities, averaged to represent a 500-bed facility. ahd.com/state_statistics.html

Download the 3M™ COSMO App.



The 3M COmmercial Solutions MObile (COSMO) app gives you instant access to 3M Commercial Solutions product information.

- Quickly access and view 3M products and how-to videos.
- Download and save content to your device in custom folders so you can view it later without internet access.
- Easily share multiple pieces of literature and/or videos to multiple email addresses at one time.









General Areas

Most hard, non-porous surfaces, including windows, glass, mirrors, carpets, floors and walls.



















Restroom Areas

Bathroom mirrors, tile, bowls, urinals and fixtures.

















3M™ Cleaning Concentrates: A concentrated solution for many challenges, and different, hard, non-porous surfaces.



3M™ Glass Cleaner Concentrate

Non-streaking. For windows, glass and other mirrored surfaces, RTU color; Light blue/purple, TNF 30; FCS 35 gallons.





3M™ Food Service Degreaser Concentrate

Removes food and oily soils from hard surfaces such as walls, floors, tables and vinvl. RTU color: Light yellow. TNF 123; FCS 149 gallons.





3M™ Non-Acid Disinfectant Bathroom **Cleaner Concentrate**

Daily use. EPA-registered for bowls, urinals and other hard, non-porous surfaces. RTU color: Clear to light green. TNF 61; FCS 61 gallons.





3M™ Heavy Duty Multi-Surface Mark Remover Concentrate

Removes most spots, stains and grease from washable surfaces. RTU color: Light purple. TNF 7; FCS 7.25 gallons.



3M™ General Purpose Cleaner Concentrate

All-purpose, everyday cleaner. Use on floors, walls and other hard, non-porous surfaces. RTU color: Light pink, TNF 35; FCS 35 gallons.





3M™ Sanitizer Concentrate

EPA-registered sanitizer for walls, floors and other hard, non-porous surfaces. Safe for sanitizing food contact surfaces. RTU color: Clear. TNF 135; FCS 75 gallons.





3M™ Neutral Cleaner Concentrate

No-rinse, low-foaming formula. Use with mop or automatic scrubber. Fresh scent. RTU color: Light green/yellow. TNF 207; FCS 172 gallons.



Scotchgard™ Bonnet Cleaner Concentrate

For lightly soiled carpets. Helps maintain properties of carpets treated with Scotchgard™ Protector. Neutral pH is safe for cleaning nylon stain-resistant carpets, RTU color; Clear, TNF 26 gallons.



3M™ Glass Cleaner and Protector

Scotchgard™ Technology helps reduce fogging on windows and mirrors after repeated use. RTU color: Blue. TNF 42: FCS 40 gallons.





3M™ Bathroom Disinfectant Cleaner Concentrate EPA-registered disinfectant cleaner removes soap scum

and scale from bathroom surfaces. RTU color: Light forest green. TNF 27; FCS 26 gallons.



3M[™] Deodorizer — Country Day Scent Concentrate

Long-lasting deodorizer leaves a light, floral scent. RTU color: Pink. TNF 36 gallons.



3M™ Non-Acid Bathroom Cleaner Concentrate

Daily use. For bowls, urinals and other hard, non-porous surfaces, and soap scum. RTU color: Light green. TNF 26 gallons.





3M™ Quat Disinfectant Cleaner Concentrate

EPA-registered. Effective against SARS-CoV-2, HIV-1, MRSA, VRE, and other microorganisms. Rinse-free, fresh fragrance. RTU color: Light green. TNF 127; FCS 107 gallons.



3M™ Deodorizer — Fresh Scent Concentrate

Long-lasting deodorizer leaves a fresh, clean scent. RTU color: Blue. TNF 30; FCS 30 gallons.



3M™ Heavy Duty Glass Cleaner Concentrate

Non-streaking. For windows, glass and mirrors, and other mirrored surfaces. RTU color: Light blue/purple. TNF 12 gallons.





3M™ Speed Stripper Concentrate

Five-minute stripper. Removes sealers and floor finish buildup and finishes hardened by frequent burnishing. No unpleasant odor. RTU color: Light blue. TNF 8.2; FCS 10 gallons.



3M™ Deodorizer — Mountain Spice Concentrate

Long-lasting deodorizer leaves a fragrant, spiced scent. RTU color: Yellow-green. TNF 36 gallons.



3M™ Floor Stripper LO Concentrate

Low-odor, low-foaming, five-minute stripper for sealers, floor-finish buildup and finishes hardened by frequent burnishing. RTU color: Light green. TNF 11; FCS 11 gallons.







Carpet Areas

Prespray and extraction cleaning for colorfast and nylon stain-resistant carpets.







Hard Floor Maintenance

Cleaning and stripping for hard floors.











Food Service Area

Cleaning and degreasing walls, floors, tables, carpets and seating.















3M™ Neutral Quat Disinfectant Cleaner Concentrate

EPA-registered. Effective against SARS-CoV-2, HBV, HIV-1, MRSA, VRE, and other microorganisms. Rinse-free, low-foaming, neutral pH formula. RTU color: Light green. TNF 120; FCS 100 gallons.





Scotchgard™ Pretreatment Cleaner Concentrate

For heavily soiled areas of colorfast carpet. Use as a prespray prior to extraction or shampooing. RTU color: Clear. TNF 24; FCS 26 gallons.





3M™ MBS Disinfectant Cleaner Fresh Scent Concentrate

EPA-registered. Effective against SARS-CoV-2 (1 minute dwell), HIV-1, Norovirus, MRSA, VRE, Acinetobacter Baumanii and other microorganisms (5 minute dwell). Fresh fragrance, RTU color; green, TNF 123; FCS 110 gallons.





3M™ 3-in-1 Floor Cleaner Concentrate

Low-foaming. For use in automatic scrubbers. For scrubbing before recoating, cleaning before burnishing and daily cleaning, RTU color; Blue, TNF 137; FCS 132 gallons.



3M™ Neutral Cleaner LO Concentrate

Specially formulated for minimal residue. Low odor. RTU color: Light peach. TNF 207 gallons.





3M™ MBS Disinfectant Cleaner Concentrate

EPA-registered. Effective against SARS-CoV-2 (1 minute dwell), HIV-1, Norovirus, MRSA, VRE, Acinetobacter Baumanii and other microorganisms (5 minute dwell). Low odor and dve-free. RTU color: Clear. TNF 123; FCS 110 gallons.





3M™ HB Quat Disinfectant Cleaner Concentrate

EPA-registered. Effective against HIV-1, HBV, MRSA, VRE and other microorganisms. Rinse-free. RTU color: Clear to light yellow. TNF 180; FCS 155 gallons.



3M™ Peroxide Cleaner Concentrate

Daily use, no residue. For carpet and hard, non-porous surfaces such as floors, walls, tables, bathroom fixtures, tile, grout and more. Low odor. RTU color: Clear. TNF 53; FCS 50 gallons.





3M™ Bathroom Cleaner Concentrate

Removes soap scum and scale from bathroom surfaces. RTU color: Light forest green. TNF 27; FCS 26 gallons.





3M™ Industrial Degreaser Concentrate

Removes petroleum-based grease and oil, animal fats. and heavy dirt buildup. Can be used in industrial plants, schools, hospitals and other facilities. RTU color: Red. TNF 74; FCS 76 gallons.



3M™ Clean & Shine Daily Floor Enhancer

Daily use. Repairs fine scratches while providing superior cleaning efficiency, requiring less burnishing to maintain shine, thus extending life of protective floor coating. Usage of this product reduces frequency of required floor restoration.



3M™ Bathroom & Shower Cleaner Concentrate

For daily cleaning of surfaces such as ceramic tile, stainless steel, fixtures, floors and more. Can be used on shower walls, floors and fixtures. RTU color: Milky white. TNF 29; FCS 28 gallons.



Scotchgard™ Extraction Cleaner Concentrate

Low-foaming. For use on colorfast carpet. Neutral pH safe for nylon stain-resistant carpets. RTU color: Clear. TNF 53; FCS 55 gallons.







3M™ Disinfectant Cleaner RCT Concentrate

EPA-registered, Effective against SARS-CoV-2 and HIV-1 (1 minute dwell), HBV, MRSA, VRE, Acinetobacter Baumanii and other microorganisms (3 minute dwell). Rinse-free, fragrance-free and dye-free. RTU color: Clear TNF 123; FCS 116 gallons.



3M™ Tile, Grout & Bowl Cleaner Concentrate

For periodic cleaning, Removes both hard-water scale and soap scum. RTU color: Milky white. TNF 2.6 gallons.





The Carpet and Rug Institute (CRI) Seal of Approval addresses cleaning effectiveness by testing and certifying only those products that meet high performance standards.



specified for closed dilution systems.

Product No. 8, 34: Skin/eye damage met Products No. 24, 44: Acute toxicity and skin/eye requirements at the as-used dilution, as damage met requirements at the as-used dilution, as specified for closed dilution systems.

Products meet Green Seal™ Standard GS-37 based on effective performance. concentrated volume, minimized/recycled packaging and protective limits on: VOCs and human and environmental toxicity. Greenseal.org





Ordering Information

Prod	duct Description	3M [™] Twist 'n Fill [™] Gray Cap*	3M [™] Flow Control System
1	Glass Cleaner	23357 (L)	85843 (A)
2	HD Multi-Surface	19202 (L)	85827 (A)
3	Neutral Cleaner	20200 (H) 59167 (L)	85789 (A)
4	Bathroom Disinfectant	19204 (L)	85806 (A)
5	Quat Disinfectant	23219 (H) 23218 (L)	85926 (A)
6	Speed Stripper	19208 (H)	85872 (A)
7	Food Service Degreaser	23346 (H) 23347 (L)	85828 (A)
8	General Purpose Cleaner	19212 (H) 19211 (L)	85871 (A)
11	Scotchgard [™] Bonnet Cleaner	25981 (L)	n/a
12	Country Day Scent Deodorizer	20119 (L)	n/a
13	Fresh Scent Deodorizer	20121 (L)	85829 (A)
14	Mountain Spice Scent Deodorizer	20120 (L)	n/a
15	Non-Acid Disinfectant Bath†	20787 (L)	85830 (A)
16	Sanitizer	20112 (L)	85831 (A)
17	Glass Cleaner and Protector	59980 (L)	85790 (A)
19	Non-Acid Bath Cleaner	23207 (L)	n/a
20	HD Glass Cleaner	23360 (L)	n/a

Proc	duct Description	3M [™] Twist 'n Fill [™] Gray Cap	3M™ Flow Control System
22	Floor Stripper LO	23555 (H)	85833 (A)
23	Neutral Quat Disinfectant†	23552 (H) 26057 (L)	85927 (A)
24	3-in-1 Floor Cleaner	23553 (H)	85834 (A)
25	HB Quat Disinfectant	23550 (H) 23551 (L)	85791 (A)
26	Industrial Degreaser Cleaner	29664 (H) 29665 (L)	85835 (A)
27	Scotchgard [™] Extraction Cleaner	34857 (H)	85928 (A)
28	Scotchgard [™] Pretreatment Cleaner	34858 (H)	85995 (A)
33	Neutral Cleaner LO	59169 (H)	n/a
34	Peroxide Cleaner	59288 (H) 59749 (L)	85792 (A)
35	Clean & Shine Daily Floor Enhancer	84616 (H)	84615 (A)
40	Disinfectant Cleaner RCT	85783 (L)	85837 (A)
41	MBS Disinfectant Fresh Scent Cleaner†	86047 (H) 86045 (L)	86044 (A)
42	MBS Disinfectant Cleaner†	86049 (H) 86050 (L)	86046 (A)
44	Bathroom Cleaner	59164 (L)	85929 (A)
51	Bath & Shower Cleaner	26321 (L)	85930 (A)
52	Tile, Grout and Bowl Cleaner	26323 (L)	n/a

Dispensers	ЗМ UPC
3M™ Twist 'n Fill™ System	
3M™ Twist 'n Fill™ System Dispenser, Gray	23592
3M™ Twist 'n Fill™ System Dispenser, Pressure Relief Fitting Gray Cap	25932

3M™ Flow Control System	
3M [™] Flow Control Portable Dispenser	85849
3M™ Flow Control Chemical Dispenser, Action Gap	85850
3M™ Flow Control Chemical Dispenser, Action Gap, Pressure Relief Valve	85851
3M [™] Flow Control Chemical Dispenser, Air Gap	85852
3M™ Flow Control Chemical Dispenser, Air Gap, Pressure Relief Valve	85853
3M [™] Flow Control System Spray/Foam Applicator for Portable Dispenser	85882

- * (H) signifies TNF High-Flow Bottle; (L) signifies TNF Low-Flow Bottle.
- Effective against SARS-CoV-2 (the cause of COVID-19).
- † Meets the criteria defined in the U.S. EPA Emerging Pathogen Policy.

IMPORTANT NOTICE: Always refer to chemical product label prior to use. To learn more about SARS-CoV-2, please refer to the 3M Technical Talk "Coronavirus Disease 2019 (COVID-19) Tech Talk."



Commercial Solutions 3M Center, Building 220-12E-04 St. Paul, MN 55144-1000 USA

Phone 1-800-852-9722 Web 3M.com/accuracy 3M, Scotchgard and Twist 'n Fill are trademarks of 3M Company, Used under license in Canada. Green Seal and the Green Seal Certified mark are trademarks of Green Seal, Inc. The Carpet and Rug Institute's Seal of Approval logo is a trademark of the Carpet and Rug Institute. LEED and related logo is a trademark owned by U.S. Green Building Council and is used by permission.

© 3M 2021. All rights reserved. Printed in USA. Please recycle. 78-8134-0831-3 June 2021

- 1. Reopening Guidance for Cleaning and Disinfecting Public Spaces, Workplaces, Businesses, Schools, and Homes. Centers for Disease Control (CDC). Accessed online 10/21/2020. https://www.cdc.gov/coronavirus/2019-ncov/community/reopen-guidance.html.
- 2. The 3M° Flow Control System (FCS) is 55% more accurate on average at diluting chemical concentrates than the nearest competitive system when used under laboratory conditions at water pressures ranging from 20 to 120 psi.
- 3. The 3MT Flow Control System is 17–49% smaller in cabinet size volume than the four competitive four-bottle dispenser systems tested.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solled presponsible for evaluating the product and determining the results of the property and the product and performance and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to property evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M whisps the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTON, OR USAGE OF TRADE. If AN product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, varranty, contract, negligence, or strict liability.