


# 3M™ Thinsulate™ Acoustic Insulation TAI2099S

## Technical Data Sheet



Magnified image of Thinsulate™ Acoustic Insulation showing fine PP and larger PET fibres.



Thinsulate™ Acoustic Insulation  
TAI2099S material

### General Description

This non-woven mat has excellent sound absorbing properties useful in many automotive applications, for example inside door panels, instrument panels, pillar trim, package trays, wheelarch liner etc. It is compressible, non-linting, lightweight, and can be easily die-cut. A white polyolefin scrim on one side protects the fibres. It also has a surface embossing treatment on both sides to provide better attachment of the scrim and better abrasion resistance of the material.

### General Construction

TAI2099S is made of a web and a white scrim on one side. The web is composed of 20% polyester staple fibres, and 80% polypropylene fibres. The polypropylene fibres are extremely fine, producing the high-energy absorption characteristic with the low weight. The polyester fibres are added to strengthen the web. The white scrim is a 100% polypropylene non-woven fabric.

### Special Characteristics


Suitable for applications in vehicle cabin, headliners, trim panels, luggage compartment interiors and exterior applications like bumpers and wheelarch liners. Attaching to trim panels is recommended, preferably using ultrasonic or heat spot welding, but adhesives (double sided pressure sensitive tapes or hot melt) may also be used. It can be processed by conventional techniques such as die-cutting and heat sealing. As the fibres are hydrophobic, this material will not absorb water. Therefore the risk of mildew and odours developing are minimal allowing this product to be used in humid or moist conditions. Not recommended for applications where temperatures will be continuously above 120° C.

## Properties

General properties		(typical values)
Composition web	80% polypropylene, 20% polyester	
Composition scrim	100% polypropylene	
Construction and colour	White web with single white scrim, both sides embossed	
Material Thickness	8 mm (tested after 6 weeks on roll according SAE J1355 @ 0,002 psi (14 N/m <sup>2</sup> ))	
Surface weight	217 g/m <sup>2</sup> (web and scrim; tested on 315 x 315 mm samples)	
Density	27 kg/m <sup>3</sup>	
Flammability	Self-Extinguishing (SE) as per SAE J369 (FMVSS 302, ISO 3795, DIN75200)	
Temperature resistance	120° C (tested for 2,000 hours)	
Storage	Rolls need to be stored upright	
Availability	Die cuts as per customer requirement - plain cut, hot trim edge or sealed edge - available with adhesive	


## Acoustical Properties – Alpha Cabin

Alpha Cabin Measurement with 1.2 m<sup>2</sup> sample measuring Random Incidence Sound.  
 Result is average of 30 samples, tested after 6 weeks on roll (24 hrs conditioning @ RT), scrim facing noise and 10 mm frame used (acc. 3M TMAE 017 (Rieter standard Alpha Cabin test) at 3M Germany in Neuss)



## Acoustical Properties – Impedance Tube

Dual Microphone Impedance Tube Method that measures Normal Incidence Sound.  
Combined result average of min 5 samples (100 mm & 29 mm tube), on nominal weight samples and thickness set at nominal 6 weeks thickness. (acc. 3M TMAE 016 (based on ASTM E-1050))



**Additional Information:** This data sheet contains typical information specific to the product. This information should not be used to determine a product specification. Samples and further information on the use of the product are available separately.

**Important notice to purchaser:** All statements, technical information, and recommendations herein are based on tests we believe to be reliable, but the accuracy or completeness thereof is not guaranteed. Please ensure before using our product that it is suitable for your intended use. All questions of liability relating to this product are governed by the Terms of Sale subject, where applicable, to the prevailing law.



**3M Deutschland GmbH**  
**Automotive Laboratory**  
Carl-Schurz-Strasse-1, D-41453 Neuss, Germany

Phone +49-2131-14-3580  
Fax +49-2131-14-3849

TAI2099S\_05  
Issue Date: 06/2017

3M and Thinsulate are trademarks of 3M  
Company © 3M 2017 All rights reserved.