



Repulpable Nose Tabs 9030

Technical Data

October, 2006

Product Description 3M™ Repulpable Nose Tabs 9030 is a light-weight tissue coated on both sides with blue repulpable adhesive for quick grab to newsprint and are furnished on an easy-release extended paper liner.

Product Construction	Adhesive	Liner	Color	Size
	High tack, repulpable	Silicone coated, semi-bleached kraft paper	Blue	2 ¹ / ₄ in. x 3 in. (57 mm x 76 mm)

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Repulpability:	Tape – Completely* Liner – Completely*
Tape Thickness:	3 mils (0.075 mm) without liner
Bonding Strength:	Delaminates most papers
Heat Resistance:	Excellent to 400°F (204°C) web temperature

*Repulpability judged according to TAPPI UM-213, Procedure A. It is important to follow the weight and quantity measurements for the fiber, splicing tape and water. Non-representative results can occur if test guidelines are not followed.

Features

- Practically eliminates the “human element” from flying paper operations. Unlike glue, there are no “drying times,” “correct mixtures,” “too soft,” “too wet,” etc. which can depend on operator performance or judgements.
- Packing in small wrapped packages helps assure moisture content of unused Nose Tabs.
- Water solubility and alkali dispersability are excellent and eliminate danger of contaminating the paper mill “broke” with non-repulpable materials. Poor quality paper and plugged Fourdrinier screens often can be caused by typical rubber-base splicing mediums.
- Help prevent costly and wasteful downtime and at the same time, provide a more consistent flying paster pattern.

Application Techniques

For optimum results, firm, even rub down pressure must be applied to the taped area to create the best possible adhesion between the tape and paper surface. A plastic squeegee or similar tool can help achieve the proper uniform pressure.

3M™ Repulpable Nose Tabs

9030

Storage Store under normal conditions of 70°F (21°C) and 50% R.H. in the sealed plastic bags until ready for immediate use.

Shelf Life To obtain best performance, use this product within 18 months from date of manufacture.

Product Use All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

Warranty and Limited Remedy Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.

Limitation of Liability Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2000

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



**Industrial Business
Industrial Adhesives and Tapes Division**

3M Center, Building 21-1W-10, 900 Bush Avenue
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (fax)
www.3M.com/industrial



*Recycled Paper
40% pre-consumer
10% post-consumer*

3M is a trademark of 3M Company.
Printed in U.S.A.
©3M 2006 70-0703-2719-5 (10/06)