



# Vinyl Seal Tape 1510R

Technical Data

April, 2015

**Product Description** 3M™ Vinyl Seal Tape 1510R is a vinyl seal tape coated with an aggressive rubber pressure.

Product Construction	Backing	Adhesive	Color	Standard Roll Length
	Vinyl	Rubber	White	33 yds (30 m)

- Features**
- Resistant to moisture, acids, alkalis, oils and other chemicals
  - Performs well over a wide range of environmental conditions
  - Conforms well to corners and irregular surfaces
  - Color matched specifically for PVC

**Typical Physical Properties**

**Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.**

Test	Typical Value	Typical Value (Metric)	Test Method
Product Thickness	10.0 mils	(0.25 mm)	PSTC-133
Peel Adhesion	29 oz/in	(8.1 N/25 mm)	PSTC-101
Shear Adhesion	>24 hrs @ 2.2 psi	(>24 hrs @ 15.2 kPa)	PSTC-107
Tensile Strength	31 lb/in	(140.1 N/25 mm)	PSTC-131
Elongation	150%	(150%)	PSTC-131
Service Temperature	0° to 175°F	(-18° to 79°C)	

- Application Ideas**
- Ideal for use on PVC jacketing and fittings
  - For interior use

# 3M™ Vinyl Seal Tape 1510R

---

**Storage** Store in a clean, dry place. Temperature of 40-80°F (4-26°C) and 40 to 50% relative humidity are recommended.

---

**Shelf Life** To obtain best performance, use this product within 12 months from date of manufacture

---

**Technical Information** The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

---

**Product Use** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

---

**Warranty, Limited Remedy, and Disclaimer** Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

---

**Limitation of Liability** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

---

**ISO 9001**

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.



## Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06  
St. Paul, MN 55144-1000  
800-362-3550 • 877-369-2923 (Fax)  
www.3M.com/construction



*Recycled Paper*  
40% pre-consumer  
10% post-consumer

3M is a trademark of 3M Company.  
Printed in U.S.A.  
©3M 2015 All rights reserved.  
E 70-0709-4178-9