

8518 Gloss Overlamine

8519 Luster Overlamine

8520 Matte Overlamine

8915 Ultra-Matte Overlamine

8528 Gloss Overlamine

Product Description

- **8518, 8519, 8520:** resists fuel vapors, highly conformable
- **8518:** optically clear, provides a wet paint look
- **8915:** Ultra-matte, reduces glare
- **8528:** Excellent UV protection, longer term vertical durability, horizontal warranty
- **8518, 8519, 8520, 8915:** Expected performance life of eight years (unwarranted period applied to a flat, vertical, outdoor surfaces)
- **8528:** Expected performance life of nine years (unwarranted period applied to a flat, vertical, outdoor surfaces)
- **8520** is UL Classified for slip resistance in accordance with UL 410 (File SA11595).

Recommended Types of Graphics and End Uses

- **8518, 8519, 8520:** Fleet/vehicle, vehicle wraps, watercraft, transit, labels, thermoformable graphics, smooth walls
- **8518:** Windows, glass, and applications requiring optical clarity
- **8915:** Fleet/vehicle, vehicle wraps, watercraft, transit, signage, smooth walls
- **8528:** Fleet/vehicle, vehicle wraps, transit, smooth walls, windows, and glass
- Floor graphics (**8520 only**)

Characteristics

These are the typical values for unprocessed product. Processing may change the values.

Performance Characteristics

Characteristic	Value
Material	Cast vinyl
Thickness	2 mils
Gloss (60° gloss angle)	8518, 8528: Gloss >80 8519: Luster >70 8520: Matte <30 8915: Ultra-matte <10
Liner	8518, 8528: Polyester 8519, 8520, 8915: Kraft paper
Lamination Temperature	60°F to 100°F (16°C to 38°C)
In Use Temperature Range	-65°F to 200°F (-54°C to 93°C)
Chemical Resistance	• Resists mild alkalis, mild acids, and salt • Excellent resistance to water (<i>does not include immersion</i>) • Resists occasional fuel spills
Flammability	ASTM E84 reports: 8518 , 8519 , 8520 , and 8528 , or go to the online product catalog at 3Mgraphics.com . For all other test reports call 1-800-328-3908.

Factors Affecting Graphic Performance Life

The actual performance life of a graphic is affected by:

- Selection and preparation of the substrate
- Application methods
- Cleaning or maintenance methods
- Exposure conditions
- Cabinet design and maintenance
- Lamp selection and intensity

Graphics Manufacturing



CAUTION

Before using any equipment, always read the manufacturer's instructions for safe operation.

Completely Dry Graphics

NOTE

Incomplete drying or curing can result in graphic failure including curling, increased shrinkage, and adhesion failure, which are not covered under any 3M Graphics warranty.

See the ink's 3M product and instruction bulletins for more details.

Application Tapes

There are two types of application tapes. See [3M Instruction Bulletin Application: 3M™ Application Tapes for Graphic Films](#) to determine what application tape is recommended for your 3M Graphics Products. Finished graphics eligible for any 3M warranty must be constructed using approved 3M Graphics Products. See the [3M Graphics Warranty Bulletin](#) for more details.

Premasking Tape

Premasking tape increases stiffness during application while preventing stretching and damage. Use when little or no liner is exposed. See [3M Instruction Bulletin Application: 3M™ Application Tapes for Graphic Films](#) for complete details.

Prespacing Tape

Prespacing tape holds cut and weeded letters or graphics in place during application and after removal of the film liner, while preventing stretching and damage. Use when large amounts of liner are exposed. See [3M Instruction Bulletin Application: 3M™ Application Tapes for Graphic Films](#) for complete details.

Maintenance and Cleaning

Use a cleaner designed for high-quality painted surfaces. The cleaner must be wet, non-abrasive, without solvents, and have a pH value between 3 and 11 (neither strongly acidic nor strongly alkaline). See [3M Instruction Bulletin Maintenance](#) for details.

Shelf Life, Storage, and Shipping

Shelf Life

The shelf life is **never more than three years** from the date of manufacture on the original box.

Processing the film changes its shelf life to **one year** from the processing date, but no more than three years from the manufacturing date.

Storage Conditions

- 40°F to 100°F (4°C to 38°C)
- Out of sunlight
- Clean, dry area
- Original container
- Bring the film to room temperature before use

Shipping Finished Graphics

Flat, or rolled printed side out on a 6 in. (15 cm) or larger core. This helps prevent the application tape, if used, from popping off.

3M Related Literature

In addition to other 3M bulletins specified in this document, the following bulletins provide details users may need to successfully apply a graphic.

- [3M Instruction Bulletin Production: Lamination](#)
- [3M Instruction Bulletin Application: Backlit Signage](#)

Health and Safety

Chemicals

When handling any chemical products, read the manufacturers' container labels and the safety data sheets (SDS) for important health, safety, and environmental information.

[Follow this link to obtain SDS sheets for 3M products.](#)

[Follow this link to obtain information about substances of very high concern \(SVHC\) for EU products.](#)

Tools and Equipment Usage

When using any equipment, always follow the manufacturer's instructions for safe operation.

Air Quality Regulations

Country, state, or regional volatile organic compound (VOC) regulations may prohibit the use of certain chemicals with VOCs in graphic arts coatings and printing operations. Check with local environmental authorities to determine whether use of this product may be restricted or prohibited.

Warranty Information

Warranty Coverage Overview

The warranty coverage for eligible graphics is based on the user both reading and following all applicable and current 3M Graphics product and instruction bulletins. The warranty period for eligible graphics is as stated in the 3M Graphics Warranties Matrices at the time the film was purchased. Information found at [3M.com/graphicswarranties](https://www.3m.com/graphicswarranties) includes:

- [3M Graphics Warranties Bulletin](#)
 - This bulletin contains information on limitations, exceptions, and warranty period reductions for 3M Graphics warranties. The warranty period may be reduced and stipulations may apply for certain constructions, applications, and graphic exposures as covered in this bulletin.
- [3M Graphics Warranties Selector](#)
 - Use this selector to search for your warranty coverage by 3M Graphics Product(s), Inks, Printer, Application(s), and Exposure.
- [3M™ Global Geographical Zones](#)
 - Use this map to identify your warranty zone and determine if you are subject to reduced warranted durabilities.

Technical Information

Technical information, guidance, and other statements provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license to any intellectual property rights is granted or implied with respect to this technical information.

Product Selection and Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment, reviewing all applicable regulations and standards, and reviewing the product label and use instructions. Failure to properly evaluate, select, and use a 3M product in accordance with instructions or to meet all applicable safety regulations may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer

Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Commercial Branding and Transportation

3M Center, Building 223-3N-30
St. Paul, MN 55144

1-800-328-3908
[3M.com/Graphics](https://www.3m.com/Graphics)

© 3M 2026. All rights reserved.
3M and Scotchcal are trademarks of 3M.
Used under license in Canada.
All other trademarks are property of their respective owners.
Revision F, September 2026 Please recycle.

