

# Cable Cleaning/Degreasing Wipes

## Data Sheet

---

### Product Description

Cable Cleaning/Degreasing Wipes are designed specifically to remove contaminants such as grease, oil, sealants and cable jelly from switchgear and cables. The product will remove even heavy or old deposits without hazard to substrates or insulation materials.

### Typical Applications

- Cable cleaning prior to jointing
- Removal of protective greases and jelly from switchgear
- Sub-station cleaning and maintenance
- PCB cleaning
- Degreasing overhead power lines – rail

### Application Methods

Wipe over surface to be cleaned.

Recommend gloves should be worn for skin protection, please refer to the product MSDS for further details.

### Advantages

- High dielectric strength
- Will not harm circuit boards or connectors
- No deleterious effects on cable insulation
- For all heavy duty applications

### Key Features

- Safe to use on all electrical equipment and cables
- Effective on both general grease/oil and protective coatings

#### Important Notice

Technical information provided by 3M is based on experience and/or tests believed to be reliable, but their accuracy is not guaranteed and the results may not be relevant to every user's application. For this reason 3M does not accept responsibility or liability, direct or consequential, arising from reliance upon any information provided and the user should determine the suitability of the products for their intended use. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence. All questions of liability relating to 3M products are governed by the seller's terms of sale subject where applicable to the prevailing law. If any goods supplied or processed by or on behalf of 3M prove on inspection to be defective in material or workmanship, 3M will (at its option) replace the same or refund to the Buyer the price paid for the goods or services. Except as set out above, all warranties and conditions, whether express or implied, statutory or otherwise are excluded to the fullest extent permissible at law.

3M is a trademark of the 3M Company. Printed in the UK.

© 3M United Kingdom PLC, 2014. Issue 2

---

#### Electrical Markets Division

##### 3M United Kingdom PLC

##### Sales Office

PO Box 393

Bedford MK41 0YE

Telephone: 0870 609 4639

Fax: 01234 229 433

##### 3M Ireland Ltd

##### Sales Office

The Iveagh Building, The Park,

Carrickmines, Dublin 18, Ireland

Telephone: (01) 800 812 732

Fax: 353 1 280 3509

##### 3M United Kingdom PLC

##### Head Office

3M Centre, Cain Road

Bracknell, Berkshire RG12 8HT

Telephone: 01344 858 000

Fax: 01344 858 758