



Science.
Applied to Life.™



**Anti-fog technology.
Applied to help workers
see clearly, longer.**



Scotchgard™ Anti-Fog Coating Technology brings higher performance to safety eyewear.



Clearly better anti-fog performance.

A fogged lens can be frustrating and dangerous. Removing eyewear to wipe away fog can expose eyes to potentially dangerous workplace impact hazards and debris. The Scotchgard™ Anti-Fog Coating resists fogging longer than traditional anti-fog coatings, even after washing multiple times.

Help workers see clearly, longer.

Scotchgard™ Anti-Fog Coating is designed for working in challenging situations such as:

- Hot & humid conditions
- Indoor & outdoor work
- Physically demanding tasks
- Climate-controlled areas

See what you've been missing with our fog-resistant eyewear.

Try the Solus™ 1000 Series safety eyewear and Goggle Gear 500 Series splash goggle with Scotchgard™ Anti-Fog Coating and see clearly, longer.*


Scotchgard™ Anti-Fog Coating is now available on Solus™ 1000 Series safety eyewear in a range of lens colors (clear, grey or amber). Other features include removable temples, soft nose bridge, optional elastic strap, padded temples for added comfort, and vented, removable foam gasket to help reduce eye exposure.

Scotchgard™ Anti-Fog Coating is also available on 3M™ Goggle Gear 500 Series splash goggle with a low-profile design, adjustable strap and optional prescription insert. All come with polycarbonate lenses, which absorb 99.9% of UV rays.

* Based on 3M internal testing per EN168 test method when compared with traditional anti-fog coatings.



The science behind Scotchgard™ Anti-Fog Technology.



The facts are clear:

- Scotchgard™ Anti-Fog Coating **lasts longer** than traditional anti-fog coatings,* helping to increase eyewear performance in wet and steamy environments
- Workers may enjoy reliable, clearer sight longer, because the coating, with its active ingredient, is bonded to the lens
- The coating **retains its effectiveness** for at least 25 washings, allowing workers to wear their eyewear longer
- The coating **can be disinfected** with diluted bleach soaking or alcohol wipes without losing its anti-fog performance
- Workers can **feel confident** wearing Scotchgard™ Anti-Fog coated eyewear because it meets the requirements of ANSI Z87.1 and CSA Z94.3

* Based on 3M internal testing per EN168 test method when compared with traditional anti-fog coatings.



Get out of the fog with a new family of eyewear.

Solus™ 1000 Series Eyewear

Kit: Blue/Black/Clear Lens



Kit: Green/Black/Clear Lens



Alternate Lens Options

Grey

Amber



Goggle Gear 500 Series Goggle

Clear

Prescription Insert



Replacements

Foam Gasket/Strap



Product No.	UPC	Product Description	Per Case
➤ S1101SGAF-KT	50051131271895	KIT: 3M™ Solus™ 1000 Series, Blue/Black Eyewear with Clear Scotchgard™ Anti-Fog Lens and foam gasket and strap	20
➤ S1101SGAF	50051131271864	3M™ Solus™ 1000 Series, Blue/Black Eyewear with Clear Scotchgard™ Anti-Fog Lens	20
➤ S1102SGAF	50051131271871	3M™ Solus™ 1000 Series, Blue/Black Eyewear with Grey Scotchgard™ Anti-Fog Lens	20
➤ S1103SGAF	50051131271888	3M™ Solus™ 1000 Series, Blue/Black Eyewear with Amber Scotchgard™ Anti-Fog Lens	20

Product No.	UPC	Product Description	Per Case
➤ S1201SGAF-KT	50051131271857	KIT: 3M™ Solus™ 1000 Series, Green/Black Eyewear with Clear Scotchgard™ Anti-Fog Lens and foam gasket and strap	20
➤ S1201SGAF	50051131271826	3M™ Solus™ 1000 Series, Green/Black Eyewear with Clear Scotchgard™ Anti-Fog Lens	20
➤ S1202SGAF	50051131271833	3M™ Solus™ 1000 Series, Green/Black Eyewear with Grey Scotchgard™ Anti-Fog Lens	20
➤ S1203SGAF	50051131271840	3M™ Solus™ 1000 Series, Green/Black Eyewear with Amber Scotchgard™ Anti-Fog Lens	20

Product No.	UPC	Product Description	Per Case
➤ Solus-foam	50051131271901	3M™ Solus™ Accessories Foam Gasket	10
➤ Solus-strap	50051131271918	3M™ Solus™ Accessories Strap	10

Product No.	UPC	Product Description	Per Case
➤ GG501SGAF	50051131274551	3M™ Goggle Gear, 500 Series Clear Scotchgard™ Anti-Fog Lens	10
➤ GG500-PI	50051131274568	3M™ Goggle Gear, 500 Series Anti-Fog Lens Prescription Insert	10

How to

Attach strap to Eyewear



Attach temple to Eyewear



Attach strap to Goggle Gear



Foam gasket has small vents to help reduce fogging



⚠ WARNING

These eye and face protection products help provide limited eye and face protection. **Misuse or failure to follow warnings and User Instructions may result in serious potential injury, including blindness or death.** For proper use, selection and applications against flying particles, optical radiation and/or splash, see supervisor, read *User Instructions* and warnings on the package or call 3M PSD Technical Service in the USA at 800-243-4630. In Canada, call Technical Service at 800-267-4114.



Personal Safety Division
3M Center, Building 235-2W-70
St. Paul, MN 55144-1000

For more information
Technical Service: 1-800-243-4630
Customer Service: 1-800-328-1667
3M.com/PPESafety

© 3M 2015. All rights reserved.
3M and Scotchgard are trademarks of 3M Company.

70-0716-7161-7