

3M Personal Safety

# Approved combinations of Earmuffs and Helmets

The following combinations meet the requirements for the CE certification according to EN 352:3.



## 3M Peltor X series

Helmet model	X1	X2	X3	X4	X5	Adapter
3M G500 Headgear	SML	SML	SML	SML	SML	E
3M G22	SML	SML	ML	SML	L	E
3M G2000	SML	SML	SML	SML	ML	K
3M G3000	SML	SML	SML	SML	ML	E
3M H700	SML	L	L	SML	L	E
3M Versaflor M-106 and 107	ML	ML	ML	ML	ML	AF
3M Versaflor M-306 and M-307	SML	ML	ML	SML	L	AF
Auboueix/Seybol, Kara	SML	SML	SML	SML	ML	E
Auboueix Iris 2	ML	ML	ML	ML	L	E
Arco Champion	L	L	L	L	L	H
Arco Champion Plus	L	L	L	L	L	H
Centurion 1100 (H fitting)	L	L	L	L	L	H
Centurion 1125 (H fitting)	L	L	L	L	L	H
Centurion Concept (E fitting)	L	L	L	L	L	E
Centurion Concept (H fitting)	L	L	L	L	L	H
Centurion Vulcan	L	L	L	L	L	H
Delta Plus Zircon	SML	L	L	SML	L	E
Grolls, Balance AC	L	L	L	L	L	E
MSA V-Gard 500	SML	SML	SML	SML	SML	E
PETZL, Vertex Best, Vent and ST	ML	ML	ML	ML	L	E
Protector/Scott Style 300	ML	ML	ML	ML	ML	E
Protector/Scott Style 600	SML	SML	SML	SML	ML	E
Shubert EuroGard	SML	L	L	SML	L	E

# Optime and H31

Helmet model	H31	Optime I	Optime II	Optime III	Adapter
3M Airstream AH1, AH4	ML	ML	ML	L	AE
3M Airstream AH7	ML	ML	ML	L	AE
3M Airstream HT-701, HT-702, HT-705	ML	ML	ML	L	AE
3M Airstream HT-707	ML	ML	ML	L	AE
3M G500 Headgear	SML	SML	SML	SML	E
3M Versaflo M-106, M-107	ML	ML	ML	ML	AF
3M Versaflo M-306, M307	ML	ML	ML	ML	AF
3M Peltor G2000	SML	SML	SML	SML	K, E
3M Peltor G22 Basic set	SML	SML	SML	SML	E
3M Peltor G3000	SML	SML	SML	SML	E
3M H700	SML	ML	SML	L	E
Auboueix Brennus	SML	SML	SML	SML	F
Auboueix Fondelec	SML	SML	SML	SML	F
Auboueix Iris	ML	ML	ML	ML	E
Auboueix Iris 2	ML	ML	ML	ML	E
Auboueix KARA	SML	SML	SML	ML	E
Berendsen Safety Balance	ML	ML	ML	ML	E
Berendsen Safety Balance AC/3M 1465	ML	ML	ML	ML	E
Berendsen Safety Balance HD	SML	SML	SML	SML	N
Centurion Safety Robust	SML	SML	SML	SML	E
Centurion 1100/Arco type 2	SML	SML	SML	ML	H
Centruion 1125/ARCO plus	SML	SML	SML	SML	H
Centurion 1540/ARCO	ML	ML	ML	ML	A
Centurion Concept	SML	SML	SML	SML	E
JSP EVOLITE	L	ML	ML	L	E
JSP MK6R/MK7R	L	SML	SML	L	E
JSP MK8	L	L	ML	L	E
Kemira Top Cap	SML	SML	SML	SML	A

Helmet model	H31	Optime I	Optime II	Optime III	Adapter
LAS LP2002, LP2006	SML	SML	SML	SML	E
MSA Super V-Gard II	SML	SML	SML	SML	E
MSA V-Gard	SML	SML	SML	SML	E
Petzl Vertex	SML	SML	SML	SML	E
Protector Style 300	SML	SML	SML	SML	E
Protector Style 600	SML	SML	SML	SML	E
Protector Tuffmaster II	ML	ML	ML	ML	E, G
Römer Bravo 2 Nomaz	SML	SML	SML	SML	B
Römer Marus Top 2 Atlas Nomaz	SML	SML	SML	SML	B
Römer N2 Atlas Nomaz	SML	SML	SML	SML	BB
Römer Profi Expo	SML	SML	SML	SML	E
Römer Profi Nomaz	SML	SML	SML	SML	E
Römer Top Expo Atlas	SML	SML	SML	SML	B
Schuberth BEN	SML	SML	SML	SML	BB
Schuberth BER S	SML	SML	SML	SML	E
Schuberth BER80/WPC80	SML	SML	SML	SML	EA
Schuberth BOP R	SML	SML	SML	SML	B
Schuberth Pionier	SML	SML	SML	SML	B
Schuberth SH 91/WPL 91	SML	SML	SML	SML	EB
Schuberth SW1	ML	ML	ML	ML	EB
Sofop Taliaplast Oceanic	ML	ML	ML	ML	E
Sofop Taliaplast Opus	ML	ML	ML	ML	E
UVEX Airwing	SML	SML	SML	SML	E
Voss Inap 88	SML	SML	SML	SML	E
Voss Inap Master	ML	ML	ML	ML	E
Voss Inap PCG	ML	ML	ML	ML	G
Voss Inap Star	ML	ML	ML	ML	E