



WATER RESISTANT


3M

THINSULATE™
Insulation

3M™ Thinsulate™ Water Resistant Insulation

3M™ Thinsulate™ Water-Resistant Insulation for footwear helps keep your feet high and dry without unnecessary bulk. This insulation is pre-compressed, so whether you're trekking to your tree stand or strolling down frosty city streets, it helps keep your feet warm and comfortable.

- Pre-compressed insulation designed expressly for footwear
- Our most water resistant insulation for warmth, even when wet
- The original thin insulation for footwear



“My lined boots are the reason I’m able to survive winter. Staying inside is not an option for me. When Thinsulate is keeping me warm, I can focus on enjoying my time outdoors.”

-KURT S. | MINNESOTA

Consumer received free product.
Actual consumer not shown in photo.





WATER RESISTANT
B100, B200, B400, B600



TECHNOLOGY				ORIGINAL		FOOTWEAR	
Warm (80g or less) FX40 FX70 FX100 XT-S40				Warm (Up to 80g) U40 M60		Warm (Up to 300g) B0400 B100 B200	
Warmer (80g-140g) XT-S80 XT-S80 XT-S100 FR120 J60 J80 J100 R70 R100 R150 FL600				Warmer (80g-140g) C70 C100 C150 U70 U100 M80 M100 M150 KL100 G60 G80		Warmer (300g-600g) B2200 B2400 B2500 B0600 B400	
Warmest (140g and above) XT-S150 FR150 FR200 J150 J150 J200 J250 R200 FL700				Warmest (140g-250g) C200 C250 C300 U150 U200 KL150 KL200 KL250 TYPE O M200 G100 G120 G150 G200		Warmest (600g-1000g) B600	
Fill Power Warmth (350-500)				Fill Power Warmth (500-650)		Fill Power Warmth (850-900)	

IMPORTANT NOTICE

WARRANTY, LIMITED REMEDY AND DISCLAIMER: 3M warrants that 3M™ Thinsulate™ Insulation that is stored, maintained and used in accordance with 3M's written instructions will meet the applicable 3M product specifications. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If any Thinsulate insulation does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

LIMITATION OF LIABILITY: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract or strict liability.

PRODUCT USE: Because of the variety of factors that can affect the use and performance of Thinsulate insulation, user is solely responsible for evaluating the product and determining whether it is fit for a particular purpose and suitable for user's method of application. 3M may change the product, specification and availability of the product as improvements are made; therefore, user should contact 3M for latest information before specifying the product.

All Thinsulate insulation rolls are made within strict dimensional tolerance specifications. However, length and/or width dimensions may shift, shrink, or otherwise change up to a maximum of ±4% during handling or shipment. Please allow 24 hours after vacuum pack is removed.



Home Care Division

3M Center, Building 223-4NE-13
St. Paul, MN 55144-1000

651-575-6694
thinsulate.com

3M and Thinsulate are trademarks of 3M, used under license in Canada.

Please recycle. Printed in U.S.A.
© 3M 2015. All rights reserved.
70-0717-0897-1