



200
microlayers
reflect heat,
not signals

Multilayer optical technology. Applied to keeping drivers calm, cool and connected.

3M Ultra-Clear Solar Film keeps the heat out, but not the signals.

Because of its non-metallic construction, 3M Ultra-Clear Solar Film won't interfere with electronic device signals or alter the appearance of glass. But it will interfere with infrared heat from the sun. Cooler automotive interiors mean less AC usage, which can lead to better fuel efficiency, decreased emissions and increased comfort.



Non-metallized —
no signal interference


3M™ Ultra-Clear Solar Film

Using multilayer optical film technology, over 200 microlayers reflect infrared heat while allowing visible light to pass through. 3M Ultra-Clear Solar Film can be used in laminated windshields, sunroofs, sidelights and backlights to create comfortable automotive interiors. Its non-metallic construction means it won't interfere with electronic signals or corrode.

- ▶ Reflects infrared heat for improved comfort
- ▶ Non-metallic — won't interfere with electronic signals
- ▶ Neutral color to maintain glass aesthetics
- ▶ Conformable for bent glass processing


How is it used?

3M Ultra-Clear Solar Film is easily laminated between sheets of PVB. It's conformable for bent glass applications and works with different glass and PVB combinations.



Solar performance of laminated automotive glass

	Tvis	Rvis	Tsol	Rsol	Asol	Tts
Clear glass/Solar green glass	81.9%	8.4%	55.3%	6.5%	38.2%	0.668
with UCSF	79.7%	10.6%	47.1%	22.6%	30.3%	0.562
with UCSF and IR absorbing PVB	78.8%	10.0%	40.1%	21.3%	38.7%	0.518



Get connected at 3M.com/Glass.

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.