

3M™ Floor Care



Consistent
Performance
Long Lasting Shine



Floor Finishes and Protectors

Protection that Pays

Scotchgard™ Hard Floor Protection Systems give you the right floor finish to help protect your investment and stand up to each area's specific challenges while enhancing the appearance of your facility.

3M flooring solutions help reduce maintenance requirements while enhancing the appearance of your facility. For more information visit us at www.3M.com/building



HARD FLOOR PROTECTION SYSTEM

Scotchgard™ Systems



3M Scotchgard™ Stone Floor Protector is a high-performance floor surface hardener and protective clear finish for concrete, marble, terrazzo and other porous stone surfaces.

3M Scotchgard™ Vinyl Floor Protector is a high-performance floor finish that utilizes nano-sized, inorganic particles that, upon curing, produce a floor finish that is up to six times more resistant to abrasion than traditional acrylic floor finishes. The hardness of the coating results in a surface that is resistant to soiling and Scotchgard™ Vinyl Floor Protector never needs to be stripped. It is designed for vinyl, vinyl composition, rubber, linoleum and asphalt tile floors.

Both Scotchgard™ Protectors are applied with the 3M™ Easy Shine Applicator System and require only two coats to provide stain, scuff and scratch resistance. Reduced maintenance requirements help reduce labour hours and costs typically associated with traditional acrylic floor finishes and can result in savings of up to 55 percent on maintenance and labour costs annually. When scratches occur on a finished floor surface, the floor can easily be repaired by burnishing with Scotch-Brite™ Purple Diamond Floor Pad Plus.

Primary Features/Advantages/Benefits:

- Helps protect against stains, scuffs and scratches for long-lasting finish.
- Easy to reapply – no stripping or deep scrubbing required.
- Reduces floor downtime – finish applies in one to two coats, with each coat drying in 20 to 30 minutes, so rooms are functional more quickly.
- Helps reduce labour and material costs associated with traditional acrylic floor finishes up to 35 percent in the first year and up to 60 percent per year in subsequent years.
- Environmentally preferable cleaning system* – System meets the Executive Order 13101 definition of 'environmentally preferable.'
- Helps reduce the need for finishes, strippers and crystallization products, and the labour intensive work associated with applying these chemical products.

*'Environmentally preferable,' according to Executive Order 13101, means products or services that have a lesser or reduced effect on human health and the environment when compared with competing products or services that serve the same purpose. This comparison may consider raw materials acquisition, production, manufacturing, packaging, distribution, reuse, operation, maintenance, or disposal of the product or service.

Scotchgard™ Stone and Vinyl Floor Protectors

Scotchgard™ Stone Floor Protector

High performance floor surface hardener and protective clear coat for concrete, marble, terrazzo, and other porous stone surfaces. Produces a glossy, hard, dust repellent, chemical-resistant and water-resistant surface. For use with the 3M™ Easy Shine Applicator System.



Scotchgard™ Vinyl Floor Protector

High performance floor protector that utilizes nano-sized inorganic particles. Applied with the 3M™ Easy Shine Applicator and has excellent stain, scuff and scratch resistance.



Scotchgard™ Floor Protector Applicator Pad

Applicator pads for application of Scotchgard™ Stone Floor Protector and Scotchgard™ Vinyl Floor Protector products. Designed for use with the 3M™ Easy Shine Applicator. Two 18" pads per pack.



Stone Floor Care Products

3M™ Trizact™ Diamond HX Discs Red

Diamond disc system for refurbishing and initial finishing of worn and damaged stone floors using low-speed rotary or automatic equipment.



3M™ Trizact™ Diamond HX Discs Blue

Diamond disc system for intermediate finishing and pre-polishing stone floors using low-speed rotary or automatic equipment.



3M™ Trizact™ Diamond HX Discs Gold

Diamond disc system for more aggressive refurbishing of stone floors with apparent wear or danger from scratching or pitting caused by ice melting chemicals or wear from pallets, heavy traffic or other mechanical damage.



Scotch-Brite™ Purple Diamond Floor Pad Plus

Diamond-coated floor pads for cleaning and polishing marble, terrazzo, slate and polished concrete flooring. Helps eliminate floor finish and helps reduce labour costs. Generally used after the Scotch-Brite™ Sienna Diamond Floor Pad Plus.



Scotch-Brite™ Sienna Diamond Floor Pad Plus

Diamond-coated floor pads for cleaning and conditioning worn and dull marble, terrazzo, slate and polished concrete flooring. When floor appearance reaches a medium shine, the Scotch-Brite™ Sienna Diamond Floor Pad Plus can be used to further enhance the floor appearance.



Beautiful Floors Made Easy

3M offers a full line of floor finishes to meet your facility's unique and varied hard-floor needs. With excellent shine and durability, the floor finishes in the Scotchgard™ Classic Floor Finish System are easy to apply and easy to repair, giving you the high gloss and scratch resistance you want. And they're formulated to be easier on the environment. That's beautiful floors made easy.

Scotchgard™ Classic Floor Finish System

Scotchgard™ Low Maintenance 18 Floor Finish

Low maintenance, economical floor finish. Quick-drying formula is responsive to spray buffing and burnishing. Use on most hard floors maintained with machines of any speed.



Scotchgard™ UHS 25 Floor Finish

Quick-drying, easily repaired coating gives you the deepest "wet look" for high-frequency burnishing programs. For use on resilient tile and terrazzo floors with ultra high speed machines (1,500 rpm and higher).



Scotchgard™ Low Maintenance 25 Floor Finish

Exceptionally tough and durable, low maintenance, 25% solids floor finish provides a "wet-look" gloss with less burnishing. Dries fast for outstanding image and film clarity. Use on resilient tile and terrazzo floors.



3M™ Floor Finishes and Sealers

3M™ Cornerstone™ Floor Sealer/Finish

Seals and beautifies stone floors in one step. Adheres securely and provides gloss on hard-to-maintain stone surfaces such as terrazzo, concrete, quarry tile, brick and unglazed ceramic. Works with equipment of any speed.



The background is a vibrant teal color with a dynamic pattern of water droplets and splashes. A white rectangular box is positioned in the center, containing text. The text is in a clean, sans-serif font. The overall aesthetic is clean and modern, emphasizing purity and freshness.

Cleaning Chemicals

For clearly beautiful floors, day after day, 3M has a full line of floor maintenance chemicals to meet the needs of your particular building.

For years, 3M™ Twist 'n Fill™ Cleaning Chemical Management System has been an industry leader in providing automated dispensing and mixing, along with top-performing cleaning chemicals.

For more information visit us at
www.3M.com/building

3M™ Chemical Management Systems

Whether you're looking to clean hard floors or tackle your toughest rest-room challenges, 3M has a variety of products to fit your every need.

The 3M™ Twist 'n Fill™ Cleaning Chemical Management System

Features a single dispenser that is designed to accurately dilute and dispense a wide range of cleaning solutions. You pick and choose only the chemicals you need for your cleaning task – and dispense them all through the same dispenser.

- Dispense chemicals with one compact dispenser
- Unique bottle and cap design lets you interchange chemicals in seconds
- Very compact – fits in closets
- Easy to use – just insert bottle, twist and fill
- Integral air gap prevents chemical backflow
- Flexible – mount on wall or, for portability, on cart or cleaning equipment
- Accurate dispensing technology helps ensure consistent, effective chemical performance
- Automatic 3-gallon-per-minute dispense rate for bucket applications; 1-gallon-per-minute for trigger spray bottle applications
- Automatic shut-off attachment also available
- Tamper-resistant packaging helps control chemical mixing away from the dispenser



The 3M™ Twist 'n Fill™ Cleaning Chemical Management System features a single dispenser that is designed to accurately dilute and dispense a wide range of cleaning solutions.

3M™ Twist 'n Fill™ Cleaning Chemical Management System Dispensers and Accessories

3M™ Twist 'n Fill™ System Dispenser

A unique, compact, versatile chemical dispenser that dilutes chemical concentrates with water to create ready-to-use cleaning products.



3M™ Twist 'n Fill™ System Dispenser (with Back Pressure-Relief Fitting)

A unique, compact, versatile chemical dispenser with pressure-relief fitting that dilutes chemical concentrates with water to create ready-to-use cleaning products.



3M™ Chemical Concentrates for use with the 3M™ Twist 'n Fill™ Cleaning Chemical Management System

3M™ Neutral Cleaner Concentrate 3H (Makes 207 Ready-to-Use Gallons)

Green Seal™ Certified. No-rinse, low-foaming formula won't harm washable hard floors or leave soapy residue that can dull or soften floor finish. Use with mop or automatic scrubber. Fresh scent

Available in high flow for use in filling buckets.



3M™ General Purpose Cleaner Concentrate 8H and 8L (Makes 35 Ready-to-Use Gallons)

Green Seal™ Certified. High-performance, all-purpose cleaner. First choice for your everyday cleaning needs. Use on floors, walls and other nonporous surfaces.

Available in both low flow for use in filling bottles and high flow for use in filling buckets.



3M™ Non-Acid Bathroom Cleaner Concentrate 19L (Makes 26 Ready-to-Use Gallons)

Daily-use bathroom cleaner for toilets, urinals and other hard surfaces. Excellent soap scum remover. Low flow for use in filling bottles.



3M™ 3-in-1 Floor Cleaner Concentrate 24H (Makes 137 Ready-to-Use Gallons)

Green Seal™ Certified. Versatile, low-foaming cleaner for use in automatic scrubbers or in mop-on applications. Formulated for scrubbing before recoating as well as cleaning before burnishing and daily cleaning.

High flow for use in filling buckets.



3M™ Neutral Quat Disinfectant Cleaner Concentrate 23H and 23L (Makes 120 Ready-to-Use Gallons)

For use in hospitals. EPA-registered disinfectant cleaner kills HIV-1, MRSA, VRE, herpes simplex I and II, and other pathogens. Rinse-free, low-foaming, neutral pH formula.

Available in both low flow for use in filling bottles and high flow for use in filling buckets.



3M™ Non-Acid Disinfectant Bathroom Cleaner Concentrate 15L (Makes 61 Ready-to-Use Gallons)

Daily-use, EPA-registered, disinfectant bathroom cleaner for bowls, urinals, and other hard surfaces including ceramic tile, plastic, stainless steel, fiberglass and marble. Low flow for use in filling bottles.



3M™ Floor and Baseboard Strippers

3M™ Floor Stripper

Easy-rinsing, non-ammoniated formula aggressively attacks even heavily-burnished finishes and buildup fast and with no offensive odor. Dilution rate: 1:4



3M™ Troubleshooter™ Liquid Finish Remover

Sprayable foam formula removes soil and finish buildup. Use on baseboards, floor edges, corners, stairways and ceramic tile. Ready-to-use quarts.



3M™ Rinse-Free Floor Stripper

Non-ammoniated formula strips floors without lengthy downtime. No rinsing or neutralizing needed. Dilution rate: 1:4



3M™ Troubleshooter™ Baseboard Stripper

Non-ammoniated formula strips floors without lengthy downtime. No rinsing or neutralizing needed. Dilution rate: 1:4



3M™ Specialty Floor Cleaners

3M™ TopLine Pre-Burnish Floor Conditioner

No-rinse neutral conditioner will not dull or damage floor finish. Pre-burnish floor conditioner recommended for use with the Scotch-Brite™ Diamond Pad System. Dilution rate: 1:128



3M™ All Purpose Cleaner Concentrate

For daily cleaning of medium-soiled floors. Also applicable for cleaning walls, counters, desks and painted surfaces. Dilution rate: 1:5 – 1:100



3M™ Neutral Floor Cleaner

No-rinse, low-foaming formula will not harm floors or leave soapy residue that can dull or soften floor finish. Use with mop or automatic scrubber. Fresh scent. Dilution rate: 1:64



3M™ Sharpshooter™ Extra Strength No-Rinse Mark Remover

No-rinse formula cleaner for quick, easy removal of soil and grease. This powerful cleaner penetrates and loosens buildup quickly. Convenient and effective.



3M™ Disinfectant Cleaners

3M™ Neutral Quat Disinfectant Cleaner Concentrate

Rinse-free, EPA-registered, hospital-grade quaternary disinfectant cleaner kills HBV, HIV-1, MRSA, VRE, herpes simplex I and II, and other pathogens. Low-foaming, neutral pH formula. Dilution rate: 1:256.



3M™ TB Quat Disinfectant Ready-to-Use Cleaner

Rinse-free, EPA-registered disinfectant formula disinfects and cleans hard, nonporous surfaces. Effective against TB, HBV, HIV-1, MRSA, VRE and other pathogens. Complies with OSHA's Bloodborne Pathogen Standard for disinfecting surfaces soiled with blood or other potentially infectious body fluids. Pleasant lemon fragrance; extended 1-year shelf life.



3M™ Rest-room Cleaners

3M™ Creme Cleanser Ready-to-Use

Cleans away hard water scale, rust stains, soap scum and heavy soil from stainless steel surfaces, bathroom fixtures and ceramic surfaces. Extra thick formula contains very fine grade abrasive particles for extra scrubbing power.



3M™ Heavy Duty Degreaser Concentrate

Powerful degreaser developed for extremely tough jobs. Ideal for cleaning machinery, engines, factory floors, tools, trucks and metal parts. Quickly penetrates grease, oil and a variety of soils.



*Dispensers tested over a range of 20–120 psi.



The Carpet and Rug Institute (CRI) Seal of Approval addresses cleaning effectiveness by testing and certifying only those products that meet high performance standards.



To help customers meet their sustainability goals and initiatives, or to aid in complying with government and state regulations, 3M has completed certification on twelve of its products from Green Seal™, a nationally recognized not-for-profit environmental organization.

Scotchgard™ Tile & Grout Protector and Applicator Kit

Protects grout from dirt and soils to help make routine cleaning easier. Kit contains: one 3M™ Doodlebug™ Pad Holder 6472 and four 3M™ Doodlebug™ Micro Cloths.





3M™ Easy Clean System

Fits You, Fits the Job, Fits the Budget

For cleaning, dusting, scrubbing, stripping and buffing floors, nothing beats the variety and performance of 3M Hard Floor Solutions.

For more information visit us at
www.3M.com/building

Easy Clean

Our specially designed 3M™ Easy Clean System is a more efficient way to dust, scrub and shine helping to: Reduce labour costs up to 70%, increase performance up to 6x, cut chemical waste by as much as 80%, reduce mop drag by up to 10x. The 3M™ Easy Clean System can help standardise cleaning procedures and help make it easier to meet the Joint Commission, OSHA and infection control guidelines.

3M™ Easy Scrub Flat Mop System

3M™ Easy Scrub Flat Mop Pad

Colour coded flat mops for 3M™ Easy Scrub Flat Mop System.



3M™ Easy Scrub Express Flat Mop Tool

Flat mop tool used for fast, efficient and lightweight cleaning. For use with flat mop pads.



3M™ Easy Scrub Express Caddy

Six caddies per case, each labeled and in bag.



3M™ Easy Scrub Express Bottles

Twelve empty bottles per bag, six bags per case. Squeezable bottle holds 11.5 oz. of solution.



3M™ Easy Scrub Plus Flat Mop (Shaggy)

3M™ Easy Scrub Plus Flat Mop for applying floor cleaner to ceramic tile, quarry tile or raised rubber flooring.



3M™ Easy Shine Applicator System

3M™ Easy Shine Applicator Kit

Floor finish mop applicator with special tubing to dispense floor finish from bag. Reusable applicator pads with backpack.



3M™ Easy Shine Applicator Pad

Dual fiber construction with easy glide stripes. For use with 3M™ Easy Shine Applicator Kit.



3M™ Easy Trap Duster System

3M™ Easy Trap Flip Holder

Holder works with standard threaded U.S. broom handle. Easy to flip holder clamps onto the 3M™ Easy Trap Duster and allows the customer to easily use both sides of the cloth without bending over. The 'A' shape allows the user to plow large debris without it tumbling over the holder.



3M™ Easy II Holder

Holder allows use of both sides of the duster without need to touch.



3M™ Easy Trap Duster

For dust, dirt and sand removal.












Hard Floor Maintenance

How to choose the right pad for the job. Moving left to right, select the appropriate maintenance operation, machine type and speed, then follow the color bar to the recommended 3M™ Floor Pads.

Maintenance Operation	Equipment	Speed	
	Speed		
Stripping To remove finish, sealer and contaminants from the floor surface. Done at the start of a maintenance program and at times when scrubbing will not achieve the desired results.	Rotary or Automatic		High Productivity 7300 Most aggressive stripping pad. Unique open construction resists loading and clogging. For fast removal of finish and proven consistent stripping.
	Low Speed 175–600 RPM		
Scrubbing Done prior to replacing worn finish; provides a fresh new surface to maintain.	Rotary or Automatic		Scotch-Brite™ Surface Prep Pad Heavy duty scrubbing for 2–4 coat removal prior to recoating.
	Low Speed 175–600 RPM		
Cleaning To remove light soil and other contaminants.	Rotary or Automatic		TopLine Autoscrubber 5000 Scrubs and cleans without dulling the finish. Open construction resists clogging. Ideal for use on an autoscrubber.
	Low Speed 175–600 RPM		
Buffing To remove scuffs and black heel marks and enhance floor appearance.	Rotary		Red Buffer 5100 Designed for spray buffing. Cleans when damp; buffs when dry. Use to light scrub without dulling the finish.
	Low Speed 175–600 RPM		
Burnishing To repair finish and improve gloss and image clarity of floor surface.	Electric Battery Propane		Eraser Burnish 3600 Removes black marks and returns gloss in fewer passes than other pads while producing less dust. Ideal for harder finishes & high traffic areas. Excellent durability and minimal finish removal.
	Ultra High Speed 1500 RPM & Above		
Scuff & Mark Removal	Electric Battery Propane		TopLine Speed Burnish 3200 Optimizes UHS burnishing on a wide variety of finishes. Combines black mark removal and gloss generation in one pad.
	Ultra High Speed 1500 RPM & Above		
Best Gloss	Electric Battery Propane		Aqua Burnish 3100 Produces brilliant gloss. Exceptional durability and life. The soft finish problem solver.
	Ultra High Speed 1500 RPM & Above		
Soft Finish	Electric Battery Propane		Scotch-Brite™ Sienna Diamond Floor Pad Plus Diamond coated floor pads for cleaning and conditioning worn and dull marble, terrazzo, slate, and polished concrete flooring.
	Ultra High Speed 1500 RPM & Above		
Diamond-Coated Floor Pads Use to clean and condition worn and dull stone floors.	Rotary or Automatic		Scotch-Brite™ Purple Diamond Floor Pad Plus Diamond coated floor pads for cleaning and polishing marble, terrazzo, slate and polished concrete flooring.
	Low Speed 175–600 RPM		
Diamond-Coated Floor Pads Use to clean and polish stone floors.	Rotary or Automatic		Scotch-Brite™ Purple Diamond Floor Pad Plus Diamond coated floor pads for cleaning and polishing marble, terrazzo, slate and polished concrete flooring.
	Low Speed 175–600 RPM <small>Variable Low & Ultra High Speed</small>		

Consistent Performance, Long Lasting Shine. Every 3M™ Floor Pad is made to high quality standards. Ongoing innovation and advancements in technology make 3M™ Floor Pads more effective than ever. 3M™ Floor Pads help: Remove black marks up to 6x faster, increase soil removal by up to 60%, maintain aggressiveness over the life of the pad by up to 10x, extend pad life by up to 25x's. For more information visit us at www.3M.com/building

Alternate Choices		System Procedures*
 <p>Black Stripper 7200 Standard of the industry. Consistent proven performance. Long pad life.</p>	 <p>Brown Stripper 7100 Conformable stripping pad for uneven floors. Strips prior to refinishing. Super heavy duty scrubbing for 2–4 coat removal prior to recoating.</p>	<ol style="list-style-type: none"> 1. Dust mop 2. Mask off delicate surface 3. Apply properly diluted stripping solution 4. Let solution dwell 5 minutes 5. Strip with floor machine and pad 6. Pick up dirty solution 7. Detail damp mop 8. Let dry and dust mop prior to applying finish
 <p>Blue Cleaner 5300 Heavy duty scrubbing for 1–2 coat removal prior to recoating.</p>		<ol style="list-style-type: none"> 1. Dust mop 2. Apply properly diluted scrubbing solution 3. Scrub with floor machine and pad 4. Pick up dirty solution 5. Detail damp mop 6. Let dry, dust mop prior to buffing or applying finish
 <p>Red Buffer 5100 Designed for spray buffing. Cleans when damp; buffs when dry. Use to light scrub without dulling the finish.</p>	 <p>White Super Polish 4100 Spray buff or dry buff on soft finishes. Use for polishing on wood floors.</p>	<ol style="list-style-type: none"> 1. Dust mop 2. Apply properly diluted cleaning solution 3. Clean with floor machine and pad 4. Pick up dirty solution 5. Let dry prior to buffing
 <p>White Super Polish 4100 Spray buff or dry buff on soft finishes. Use for polishing on wood floors.</p>		<ol style="list-style-type: none"> 1. Dust mop 2. Buff only clean floors 3. Apply spray buff to floor 4. Buff to a high gloss using overlapping passes 5. Dust mop
 <p>Natural Blend Tan 3500 Blend of natural and synthetic fibers. For use on harder finishes and high traffic conditions. Removes marks and scuffs while polishing.</p>	 <p>Tan Burnish 3400 Produces brilliant gloss while removing scuffs and marks. Exceptional durability and life. For use on harder finishes and high traffic conditions.</p>	
 <p>Natural Blend White 3300 Blend of natural and synthetic fibers. Excellent results on a wide variety of finishes and traffic conditions. Provides consistent high gloss while minimizing swirl marks.</p>		<ol style="list-style-type: none"> 1. Dust mop 2. Burnish only clean floors 3. Burnish to a high gloss using overlapping passes 4. Dust mop
		<ol style="list-style-type: none"> 1. Dust mop 2. 6–12 passes with Scotch-Brite™ Sienna Diamond Floor Pad with automatic floor machine or burnisher 3. 6–12 passes with Scotch-Brite™ Purple Diamond Floor Pad Plus with automatic floor machine or burnisher 4. Use 3M™ TopLine Autoscrubber 5000 to maintain floor appearance 5. When shine level begins to fade, use Scotch-Brite™ Purple Diamond Floor Pad Plus again

*For details, please refer to 3M™ Floor Pads Technical Bulletin (78-8134-0152-4).

Hard Floor Maintenance

3M™ is committed to providing you with innovative, cost-effective cleaning solutions that help protect facilities and people, while creating clean, safe and comfortable environments throughout the world.

3M™ Doodlebug™ Products

3M™ Doodlebug™ Pad Holder 6472 (Bulk)

Durable swivel lets holder twist and turn to reach hard-to-get-at places. Orange plastic holder features special grippers that hold pads firmly in place and provide for easy attachment and changing of pads.



3M™ Doodlebug™ White Cleansing Pad 8440

For cleaning delicate surfaces. Fits 3M™ Doodlebug™ Pad Holder 6472 or 3M™ Doodlebug™ Handblock Pad Holder 6473.



Scotch-Brite™ Surface Preparation Pad Doodlebug™

Heavy duty scrubbing for 2-4 coat removal prior to recoating.



3M™ Doodlebug™ Brown Scrub'n Strip Pad 8541

Designed for tough jobs like removing finish and wax buildup from baseboards and floor edges. A great way to strip stairs. Fits 3M™ Doodlebug™ Pad Holder 6472 or 3M™ Doodlebug™ Handblock Pad Holder 6473.



3M™ Doodlebug™ Red – Medium Duty

For cleaning of floor edges, skirtings, stairways, floors, swimming pools and rest rooms.



3M™ Doodlebug™ Blue Pad 8242

For medium-duty cleaning and scrubbing. Fits 3M™ Doodlebug™ Pad Holder 6472 or 3M™ Doodlebug™ Handblock Pad Holder 6473.



3M™ Doodlebug™ Black – Heavy Duty

An ideal replacement to wire brushes, where you need aggressive stripping power.



3M™ Doodlebug™ Hi Pro Pad 8550

For extra heavy-duty cleaning and stripping. Fits 3M™ Doodlebug™ Pad Holder 6472 or 3M™ Doodlebug™ Handblock Pad Holder 6473.



3M™ Floor Sweeper 6000

Whisk away dirt and debris from virtually any type of floor surface including carpet, tile, linoleum, wood and entryway matting. Easy to handle and store.



Matting & Traction

3M™ has a complete range of Anti-fatigue & Slip resistant matting available that will provide the best solutions for productivity gains and work place improvements.

3M™ Safety Walk™ tape is a mineral coated self adhesive material designed to improve traction on slippery or wet surfaces. Conformable Rolls have a special aluminium backing which allows product to conform to irregular surfaces (ideal for checker plate applications).



3M™ Safety-Walk™ Wet Area Mat 3200

- Resilient vinyl construction without backing provides a comfortable cushion for barefoot traffic
- Open construction allows water to run through the mat, surface stays drier than surrounding area
- Resistant to fungus, mildew, body oils and chemicals commonly found in wet areas
- Excellent for locker rooms, around saunas, whirlpools, pools and shower areas to provide slip resistant footing.

3M™ Nomad™ Scraper Matting 8100 (Unbacked) and 8150 (Backed)

- Stands up to the heaviest use, designed for high traffic areas of more than 400,000 people per year
- Constructed of heavy vinyl loops
- Resistant to grease, oil and chemicals
- Excellent for pivot areas – stays in place, won't wear through
- Can be used in anti-fatigue applications.

3M™ Safety-Walk™ Cushion Matting 5100 (3M™ Safe-tigue™ Matting)

- Combination slip-resistant and anti-fatigue matting for safety and comfort
- Unbacked, open construction allows debris and liquids to pass through mat
- Excellent around function areas, commercial kitchens and bar areas
- Resistant to grease and a wide variety of chemicals and detergents.

3M™ Safety-Walk™ Tape

3M™ Safety-Walk™ General Purpose Tape

A highly durable mineral coated slip resistant surface, designed for use in light to heavy shoe-traffic areas. **Main applications:** stairs, ramps, entrances, walkways, loading docks, machinery, vehicles, etc.

3M™ Safety-Walk™ Conformable Tape

A highly durable mineral coated slip resistant surface, with an aluminium backing which allows the tape to conform to corners and irregular surfaces. Designed for use in light to heavy shoe-traffic areas. **Main applications:** Checker plate, steps, ladders, loading ramps and heavy equipment.

3M™ Safety-Walk™ Medium Grade Resilient Tape

A highly durable non-mineral, medium textured slip resistant surface, designed for use in barefoot or shoe-traffic areas. **Main applications:** Boats, recreational and exercise equipment, locker rooms, steps, around pools and spa's.

3M™ Safety-Walk™ Fine Grade Resilient Tape

A highly durable non-mineral, fine textured slip resistant surface, with a water resistant acrylic adhesive. This tape is designed specifically for use in wet traffic areas where contact is made with bare skin. **Main applications:** Showers.



3M™ Safety-Walk™ Cushion Matting 3270, 5270 and 5270E

- A durable medium profile mat with a solid textured top surface for work areas where people walk or stand; and want anti-fatigue and slip resistant properties.
- 3270: suitable for light industrial, retail or non-retail commercial businesses.
- 5270: suitable for light to medium industrial, retail or non retail commercial businesses.

Spill Management: Different Types of Sorbents

3M™ Oil & Petroleum Sorbents

For absorbing oil not water. Being hydrophobic (repel water) they are ideal for absorbing oil from areas where water may also be present.

3M™ Chemical Sorbents

An ideal solution for hazardous spill control. They provide very high absorption capacities and are suitable for absorbing a very wide range of liquids – even aggressive acids and alkalis.

3M™ Sorbents are available in a variety of configurations, so you can choose the format that meets your needs:

3M™ Sorbent Booms

Used to stop the spread of a spill, booms are the first line in spill containment. Once you have booms in place you can then use pads, rolls or pillows to recover the spilt liquids.

3M™ Sorbent Pads

Ideal for clean up and recovery of spilt liquids. Pads are used like a wipe and very versatile for getting at hard to reach areas. They may also be left on a spill area to soak up liquids.

3M™ Sorbents Rolls

Rolls provide the ability to use the exact amount of sorbents required. You can leave the amount of sorbent needed on the spill to soak up larger areas. They can also be used as matting in dirty areas or where contamination is an issue.

3M™ Sorbent Pillows

Ideal for reaching spilt liquids in hard to reach areas such as bilge pumps, drains, sumps and holding tanks.

3M™ Folded Sorbents

This versatile product is four formats rolled into one. Able to be used as a boom, sheet, pad or pillow, allowing one product to be stocked for almost any liquid spill. Perforations every 40cm permit the required length of sorbent to be selected so there is no waste. The handy dispenser allows easy onsite or off-site use and can be wall mounted.

3M™ Floorsweep

Floorsweep is made of biodegradable cellulose material which is presented in a finely divided granular form.

3M™ Spill Response Kits

3M Spill Kits give you the ability to have response materials close to any potential hazard area. Kits contain a combination of sorbents, respirators, protective equipment, contaminated waste bags, instructions and are stored in a bin or cab bag. 3M Spill Kits incorporate 3M™ Scotchlite™ Reflective Materials for high visibility in the workplace.

3M™ General Purpose Sorbents

Ideal for absorbing oil and other industrial fluids cleanly, safely and efficiently.

3M™ Floorsweep Sorbent

Is the newest addition to 3M's sorbent range and is Australian-made. It is ideal for indoor and outdoor liquid spills and on floors, roads and other hard surfaces.

Symbol Key

These symbols indicate which sorbents can and cannot be used with different fluids.



For use with petroleum-based products



For use with water-based products



For use with chemical-based products



Not for use with

Folded Sorbents Application Guide



Carry



Tear



Around corner



Unfold



Unopened



Open

Spill Management: General Purpose Sorbents

For leaks and drips of non aggressive fluids, 3M General Purpose sorbents (sometimes referred to as maintenance sorbents), are ideal for absorbing oil and other industrial fluids cleanly and efficiently. They are lightweight and very quick to deploy. They are long lasting and highly absorbent (up to 25 times their own weight) absorbing most fluids very quickly. 3M General Purpose Sorbents are not suitable for absorbing aggressive liquids.

General purpose sorbents by 3M are made from inert, synthetic fibres principally of polypropylene and polyester. They are available in several formats and are lightweight and dust free. They have a high absorption capacity which minimises the amount of waste for disposal.



Features and Benefits:

- Promotes a cleaner, safer working environment.
- Very easy to use and to retrieve.
- Reduces the risk of contamination of finished products.
- Reduces the risk of damage to valuable machinery.
- Significantly less waste to dispose of.

Applications:

- Industrial machinery leaks, drips, spills and splashes of non-aggressive fluids.
- Wiping down oily tools and equipment.
- Tabletops and under work surfaces.
- Indoor vehicle/equipment parking areas – fork trucks, compressors, and lift equipment.
- Areas where an oily mist is problematic.
- Under oily machined metal parts while they drip off prior to packing and shipping.

3M™ General Purpose Sorbents

3M™ General Purpose Folded Sorbent M-FL550DD

Able to be used as a boom, sheet, pad or pillow, it allows one product to be stocked for almost any fluid spill. Perforations every 40cm allow the required length to be torn off and used.



3M™ General Purpose Sorbent Pad M-PD1520DD

Suited for placing under and around machines to catch drips, these pads can be used to soak up spilt liquids. Can also be used as a highly absorbent wipe and are versatile for getting to hard to reach areas.



3M™ Sorbent Boom M-MB308

Because of their tube-like shape, these booms are typically used to encircle spills and to contain leaks. Also ideal for placing in, under and around machines to stop those annoying leaks.



Product Overview

Product	Product No	Dimensions	Capacity	Packaging
General Purpose Folded Sorbent	M-FL550DD	45cm x 15m	40L/box	3 boxes/case
General Purpose Sorbent Boom	M-MB308	2.4m x 7.5cm	7.5L/boom	6 booms/case
General Purpose Sorbent Pad	M-PD1520DD	40cm x 52cm	1.4L/pad	100 pads/case





**For further information call:
Australia: 136 136 OR New Zealand: 0800 252 627**

3M

3M Building and Commercial Services Division

3M Australia Ltd
Bldg A,
1 Rivett Road,
North Ryde NSW 2113
Call: 136 136
www.3m.com.au

3M NZ Ltd.
94 Apollo Drive
Rosedale
Auckland 0632
Call: 0800-252-627

Warranty and Limited Remedy. This product will be free from defects in material and manufacture for a period of ninety (90) days from date of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of application. If this 3M product is proved to be defective within the warranty period stated above, your exclusive remedy and 3M's sole obligation shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the product.

Limitation of Liability. Except where prohibited by law, 3M will not be liable for any loss or damages arising from the use of this 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

The following are Trademarks of 3M: 3M, Scotch-Brite, Scotchgard, Troubleshooter, Sharpshooter, Cornerstone, Trizact, Twist 'n Fill, Nomad, Safety Walk, Doodlebug, Safe-tigue.

Please recycle. Printed in Australia. © 3M 2012. All rights reserved. 3MKM0001