

Product Bulletin

Issued Oct 2005
 Supercedes Aug 2000
 Author: George Di Scala

Description:

The Scotch-Brite Red Floor Pad is a premium quality floor maintenance pad, made of high quality synthetic fibre, in an open textured non-woven construction. Polishing particles are dispersed throughout and bonded with a durable adhesive.

Each floor pad has a pre-cut centre hole.

Special Features:

- Designed for spray cleaning and autoscrubbing operations.
- Open web construction to collect soil from floors
- Fine fibre mix for effective removal of marks and fast polishing action on floors
- Flexible pad for easier washing after use
- Consistent performance
- Durable pad at work.
- Limited removal of floor finish

Where and When to Use:

RPM	150-500	1200
Strip		
Scrub	X	
Spray	XX	X
Buff	X	X

XX Designed for X suitable

Use under auto scrubbing machines with neutral detergent for routine cleaning of floors.

Use for routine spray cleaning with standard or high-speed floor machines (150 - 500 RPM).

Use with Spray Buff cleaner

Use on floors protected with a floor finish.

Directions for Use:

1. Install a clean floor pad under the machine pad holder
2. Dust mop the area.
3. Wet clean the area using auto scrubber or dry spray buff using spray cleaning chemical
4. Remove pad and wash after use.

Maintenance of pad:

1. Remove pad from machine after each use
2. Scrub with a nylon brush under tap water or spray hose both sides of pad till clean
3. Hang up for drying.

Performance Advantages:

Produces up to 30% more shine on protected floors (Test 3M/SC)

Removes more black marks

Lasts up to 2 times longer (Test 3M/BT)

Durability : 7 000 to 10 000 sqm at 150 RPM in standard use with appropriate maintenance.

Disposal Informations:

Discard into appropriate container, for incineration, if available.

Packaging material: recyclable



Product Specifications:

Scotch-Brite Red Floor Pads consist of polyester fibre and synthetic adhesive. They are not significantly affected by water, detergents and cleaners normally used for floor maintenance.

Product Characteristics:

Colour: red

Marking: 3M Red 5100

Thickness: 28.0mm

Centre hole: pre-cut at 85 mm

Weight: 1450 g/m²

Fibre type: polyester, mixture of sizes.


Mineral: 24 % , natural type

Aggressiveness (Schiefer Value):

(Test Method 3M/ST)

Expected value for spray cleaning operation: 0 to .25 g.

3M value: 0.1 grams



Packaging and labeling:

5 pads per box

Bar code on each label.

Standard Sizes:

Standard Outside Diameters:

30, 33, 35, 40, 43, 45, 50cm

others available depending on demand

Origin:

Made in USA, ISO 9002 certified plant .