

### Product Bulletin

Issued Dec 2008

Aug 2000

Author: George Di Scala

#### Description :

**3M #230 Scourer** is a non woven abrasive hand pad.

It is made of polyester fibres that are intertangled and bonded together with a urethane resin that also contains an abrasive mineral. (Aluminium oxide)

#### Product Positioning :


The # 230 & 150 is a very economical pad designed for use in a wide variety of applications such as;

- commercial kitchens
- food preparation plants
- building maintenance
- industrial work shops

#### Special Features :

- Very economical
- Consistent performance
- Very conformable
- Good mineral distribution throughout the cross section
- Green colour
- Flexible web, very conformable
- Open construction reduces heat build up, loading up.
- Wear resistant

#### Scotch-Brite Component



#### Product Specifications

The # 230 scourer is an highly engineered product that has to meet 3M performance specifications before it is released The following areas are tested.

- Tensile strength
- Abrasive cut
- Durability
- Elmendorf tear strength
- Chemical resistance
- Dimensional tolerance
- Mineral weight

**Thickness** avg 9 mm

**Abrasive cut** 0.4 grams

**Tensile** 6wt nominal

5g/100sq cm

#### Carton

L 310 x W 280 x H 240mm

Cube 0.021sqm

1 pad 18g

50 pads = 900g

Carton 600g

Gross 1500g

#### Precautions for use :

This product contains abrasive mineral and will scratch or polish surfaces.

Not to be used on delicate surfaces, use 3M #449 white scourer

#### Size :

- #230 = 230 x 150 mm
- #150 = 150 x 100 mm
- also in 300 x 300 mm

#### Packaging and Marking :

- 50 Pads per carton
- 48 Cartons per pallet
- #150 = 100 per carton

Each carton is marked with product name, size, quantity and manufacturer's trade name and address. Batch number

#### Product Origin:

3M Korea

#### Source of supply :

3M Australia