

3M Science.
Applied to Life.™

3M Industrial Adhesives and Tapes

Specialty Six

3M™ Specialty Tape Solutions
meeting application challenges
for appliances, aerospace,
automotive, construction,
MRO, electronics, commercial
transport, marine and more...



Specialty Six



3M™ Aluminum Foil Tape 425

Key Characteristics


- High thermal conductivity enhances heating or cooling efficiency
- High heat reflectivity and flame resistance protects temperature-sensitive materials against heat and flame damage and hot spots
- Reflect light
- Seal and protect against moisture, solvents and dust
- Resist outdoor weathering and UV degradation for long term performance

Use For

- Heat shielding of delicate parts
- Aircraft chemical paint strip masking
- Refrigerator and freezer copper coil attachment
- Reflective layer for lighting
- Sealing out air and moisture

Technical Parameters

Adhesive	Acrylic (transparent)
Backing	Aluminum (dead soft)
Backing Thickness	2.8 mils (0.07mm)
Total Thickness	4.6 mils (0.12mm)
Temperature Use Range	-65°F to 300°F (-54°C to 149°C)



3M™ Vinyl Tape 471*

Key Characteristics

- “Color throughout” resists scrapes, wear and weathering
- Clean removal
- Extreme conformability and dead stretch means tape stays locked in place
- Chemical resistant
- Wide color variety

Use For

- Durable marking of aisles and corridors in factories, warehouses, hospitals and retail spaces
- Marking of safety hazards on walls, stairs and pipes
- Fine line paint masking
- Sealing
- High visibility splicing
- Decorative trim
- Surface protection



Technical Parameters

Adhesive	Synthetic rubber
Backing	Vinyl
Backing Thickness	4.1 mils (0.10mm)
Total Thickness	5.2 mils (0.13mm)
Temperature Use Range	40°F to 170°F (4°C to 77°C)



3M™ Glass Cloth Tape 361

Key Characteristics

- High temperature resistance
- Very high tensile strength
- Protects surfaces against abrasion
- Protect against high temperature to pass FAA flame resistance regulations
- Meets F.A.R. 25.853 specification


Use For

- Splicing of fabrics and textured surfaces
- Aerospace panel sealing
- Welding backup
- Wire harness protection

Technical Parameters

Adhesive	Silicone
Backing	Glass Cloth
Backing Thickness	5.4 mils (0.14mm)
Total Thickness	7.5 mils (0.19mm)
Temperature Use Range	-65°F to 450°F (-54°C to 232°C)

Bringing better ideas to the surface with a wide variety of tape solutions.



3M™ Polyester Tape 850

Key Characteristics

- Thin caliper, high tensile strength and elongation at break for reliable butt and other splices
- Seal, protect and reinforce
- Color code or decorate with long term holding
- Maintains color after long term aging
- Transparent option for virtually invisible splices


Use For

- Film splicing
- Defect marking
- Edge reinforcement
- Sealing
- Color coding



Technical Parameters

Adhesive	Acrylic
Backing	Polyester
Backing Thickness	0.9 mils (0.02mm)
Total Thickness	1.9 mils (0.05mm)
Temperature Use Range	-60°F to 300°F (-50°C to 150°C)



3M™ PTFE Film Tape 5490

Key Characteristics


- Slippery, low energy surface for smoother material movement
- High temperature resistance
- Chemical resistant
- Conformable
- Protects surfaces
- Non-stick backing

Use For

- Wrapping web rollers to reduce friction
- Covering web former edges to minimize friction during folding
- Noise reduction of parts where surfaces rub together
- Increasing wear life of parts
- Providing excellent mold release in composite bonding

Technical Parameters

Adhesive	Silicone
Backing	PTFE
Backing Thickness	2.0 mils (0.05mm)
Total Thickness	3.7 mils (0.09mm)
Temperature Use Range	-65°F to 500°F (-54°C to 260°C)



3M™ UHMW-PE Tape 5423

Key Characteristics

- Excellent abrasion resistance provides long wear life
- Low coefficient of friction
- Effective solution for noise and vibration problems
- Chemical resistant backing
- Anti-stick/release properties

Use For

- Reducing squeaks and rattles in automotive and transportation assemblies
- Lining of conveyors, chutes, blades, slides and guide rails
- Noise reduction in escalators and elevators
- Separating dissimilar parts to reduce noise and friction

Technical Parameters

Adhesive	Rubber
Backing	UHMW-PE
Backing Thickness	10.0 mils (0.25mm)
Total Thickness	11.7 mils (0.30mm)
Temperature Use Range	-30°F to 225°F (-34°C to 107°C)

For more information, call 1-800-362-3550 or visit 3M.com/IATD

SCALE

Specialty Solutions Custom Accelerated Line Extension



3M has one of the most comprehensive sets of technologies for tape and adhesive products on the planet.

The SCALE program was developed to generate customized solutions by allowing for the mixing and matching of 3M adhesives, backings and liners from our vast tape portfolio. We can use this world-class capability to design a unique single coated tape solution for your specialized needs.

Adhesives + Backings + Liners = Custom Solution

- Acrylics
- Rubber and rubber blends
- Silicones
- Metal foils
- Glass cloth
- PTFE/UHMW
- Vinyl
- Polyester
- Polyethylene
- Polypropylene
- Paper
- Foam
- Films: Polyester and HDPE
- Papers: DK and PCK

Here's how this fast-track process works:

Customer request identified

Something not currently offered in 3M line

3M Rep inputs request into SCALE product request database

Generates request to St. Paul, MN

Tech Service, Marketing, Sales discuss opportunity for clarification

Capability, timing, pricing established and samples delivered

Trial order placed and production run begins

To see if the SCALE program can help you, contact your local 3M sales representative.



3M Industrial Adhesives and Tapes Division
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
Phone 800-362-3550
Fax 877-369-2923
Web 3M.com/IATD

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. **Warranty, Limited Remedy and Disclaimer:** Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

3M is a trademark of 3M. © 3M 2016. All rights reserved. Please recycle. Printed in USA. 70-0709-5364-4 Rev0416