


# 3M-Matic™ Side Belt Case Sealer 8000a/8000a3

## Consistent. Reliable. Tough.

Today, companies need to be fast and flexible in every phase of their operations—and that includes end-of-line packaging. The 3M-Matic™ Side Belt Case Sealer 8000a/8000a3 gives manufacturers and distributors from every industry the packaging flexibility and speed to stay one step ahead of the competition.

Narrow width cases have met their match in this state-of-the-art case sealer from 3M. Engineered for maximum throughput and stability for almost any case height and width, the 3M-Matic™ Side Belt Case Sealer 8000a/8000a3 is the high volume solution for box sealing productivity.



### **Operating Rate**

Seals up to 40 same-sized cases per minute

### **Box Capacities**

**Length:** 6.0" to unlimited

**Width:** 4.5" to 21.5" (8000a)  
5.5" to 21.5" (8000a3)

**Height\*:** 3.75" to 27.25" (low)  
4.25" to 28.25" (standard)  
13.375" to 36.75" (high)

\*Height range is dependent upon Tape Leg Length (Standard or Short).



# 3M-Matic™ Side Belt Case Sealer 8000a/8000a3


## Innovative Features

- 3M™ AccuGlide™ 3 Taping Heads ensure reliable application of tape without box damage
- Interchangeable 2- or 3-inch taping heads maximize production flexibility
- Easily accessible side handle and reference ruler make height adjustments a snap for a wide variety of case heights from 3.75–36.75 inches
- Rugged, dual-extruded columns allow for smooth incremental adjustments to case heights

## Standard Features

- Spring-loaded side belt drive
- Top flap compression rollers
- Centrally located emergency stop
- Spring-loaded upper drive assembly
- Dual masts and dual lead screws

**Options:** Infeed and exit conveyors, locking casters, low tape indicator, tape application monitor, box hold-down attachment, 3-flap folder



## Box Capacities

Machine	Length		Width		Height	
	Minimum in. (mm)	Maximum in. (mm)	Minimum in. (mm)	Maximum in. (mm)	Minimum* in. (mm)	Maximum* in. (mm)
8000a	6.0 (152)	N/L	4.5 (114)	21.5 (546)	4.25 (108)	28.25 (711)
8000a3	6.0 (152)	N/L	5.5 (140)	21.5 (546)	4.25 (108)	28.25 (711)

\*Minimum case height of 3.75" can be obtained by moving columns and upper assembly to lowest position and using the short 2-inch tape leg.

\*\*Maximum case height of 36.75" can be obtained by moving columns and upper assembly to highest position. Minimum will be 13.375".

Contact your 3M representative for special modifications that may be available for sizes not listed.

**Note:** This technical information and data should be considered representative or typical only and should not be used for specification purposes.

## Visit [3M.com/packaging](http://3M.com/packaging) for more information



3M Industrial Adhesives and Tapes Division  
3M Center, Building 225-3S-06  
St. Paul, MN 55144-1000

Phone 800-362-3550  
Web [3M.com/packaging](http://3M.com/packaging)

**Product Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. **Warranty, Limited Remedy, and Disclaimer:** Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

3M, "3M Science. Applied to Life.", 3M-Matic and AccuGlide are trademarks of 3M Company.

Please recycle. Printed in USA. © 3M 2015. All rights reserved. 70-0710-0431-4