

3M™ Wrap Film Series 1380

**All what current Wrap Film Series 1080 does, plus:**

**Features**

**Advantages**

**Benefits**

Low relaxation force of the film

- Warranted lifting resistance
- Conformability without cutting

- Peace of mind
- Quality of application
- Speed of application

Special low tack adhesive formulation associated with Controltac™ film technology

- Optimized initial tack

- High slideability and repositionability property makes application easier and more efficient when an installer is working alone

Micro Comply™ adhesive technology

- Impressive film appearance

3M Non-Visible Air Release Channels result in a very uniform final appearance on the vehicle

