

3M Science.
Applied to Life.™

**A bundle of savings on
everyday working tapes.**

Masking made simple.

Now it's easy to choose the best tape to get industrial jobs done right. This simplified 5-tape system is built on increasing levels of performance, plus they're color-coded for easy identification.



3M™ Value Masking Tape

101+

The basic tape for basic jobs
Marking, temporary holding, wrapping and sealing.

3M™ General Use Masking Tape

201+

The tough tape for everyday jobs
Bundling, labeling and identifying.

3M™ Performance Yellow Masking Tape

301+

The dependable choice for industrial performance
Paint masking, marking, color coding and sealing.

3M™ High Performance Green Masking Tape

401+

Industrial strength with clean removal
Ideal for two-tone paint applications on vehicles.

3M™ Specialty High Temperature Purple Masking Tape

501+

The highest degree of industrial performance
Super-sharp paint lines for high temperature masking jobs.

Quick sticks and tight holds. Where you need it most.

3M™ High Performance Flatback Tape 2519

A high performance tape for splicing liner boards, bundling, holding, packaging applications, reinforcing, wrapping and protecting. High strength paper backing offers surface protection when applying thick-coat paint or caulk.

Go-to pricing you'll get stuck on.



Increasing the hold... 3M™ DT Series Duct Tapes

This duct tape trio can handle the full range of strengths you need. Individually wrapped tape rolls are color-coded by performance level, bi-lingual, and hand tearable for ease of use. Now that's easy-to-grasp packaging.



3M™ All Purpose Duct Tape DT8 *Conformable with instant bond* 8 mil

Holds to smooth metal, glass, plastic, sealed concrete and more.


Color: Silver, black



3M™ Heavy Duty Duct Tape DT11 *Versatility with holding power* 11 mil

The go-to tape for holding, seaming, sealing, repairing and packaging. Ideal for sticking to plastic.

Color: Silver, black



3M™ Super Duty Duct Tape DT17 *Super thick for super tough jobs* 17 mil

Super thick for super tough jobs including repairing, seaming, and protecting metal parts and surfaces.

Color: Black

Be equipped for the day. Save on these 3M Go To Tapes.

Purchase Quantity	Discount %
5 cases (same tape)	5% Off
48+ cases (assorted at case level)	10% Off
2 pallets (assorted at pallet level)	20% Off

	Eligible Tapes	Performance Level	Description
Masking Made Simple	3M™ Value Masking Tape 101+, 5.1 mil	*	The basic tape for basic jobs: marking, temporary holding, wrapping and sealing. A cost-effective solution for indoor, light-duty applications.
	3M™ General Use Masking Tape 201+, 4.4 mil	**	The tough tape for everyday jobs: bundling, labeling and identifying. Sticks and holds to a variety of surfaces such as paper, fiberboard, glass, rubber, plastic and metal.
	3M™ Performance Yellow Masking Tape 301+, 6.3 mil	***	The dependable choice for industrial performance: paint masking, marking, color coding and sealing. Clean removal up to 5 days.
	3M™ High Performance Green Masking Tape 401+, 6.7 mil	****	Industrial strength with clean removal. Ideal for two tone paint applications on vehicles. Withstands surface temperatures up to 250°F (121°C) for 30 minutes. Clean removal.
	3M™ Specialty High Temperature Masking Tape 501+, 7.2 mil	*****	The highest degree of industrial performance. Super-sharp paint lines for high temperature masking jobs. Withstands surface temperatures up to 300°F (149°C) for 30 minutes. Withstands multiple paint cycles. Clean removal.
Flatback	3M™ High Performance Flatback Tape 2519, 7.3 mil	****	Its high performance, proprietary high-tack adhesive is designed for splicing liner boards, bundling, holding, packaging applications, reinforcing, wrapping and protecting. Smooth and consistent unwind.
Duct Tape Trio	3M™ All Purpose Duct Tape DT8, 8 mil	**	Holds to smooth metal, glass, plastic, sealed concrete and more. (Excludes 22.9m rolls.)
	3M™ Heavy Duty Duct Tape DT11, 11 mil	***	The go-to tape for holding, seaming, sealing, repairing and packaging. Ideal for sticking to plastic. (Excludes 22.9m rolls.)
	3M™ Super Duty Duct Tape DT17, 17 mil	****	Super thick for super tough jobs including repairing, seaming, and protecting metal parts and surfaces. (Excludes 22.9m rolls.)

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Closure and Masking Systems Division

Building 225-3S-06
St. Paul, MN 55144-1000
Phone 1-800-362-3550
Fax 1-877-369-2923
Web www.3M.com/tape

**Discount will apply to distributor's low net price upon order.
This offer is open to all U.S. 3M Distributor Partners.
Review bCom for discount eligibility at SKU level.**

3M is a trademark of 3M Company. © 3M 2019 All rights reserved. 70-0710-0471-0 Rev. 5/19 (Janz)