

Bold colors. Unlimited possibilities.

Opaque Graphic Film Color Card Reference Guide



Make a powerful impression with colors that get noticed.

If you're looking to turn an ordinary surface into an extraordinary brand experience, you've come to the right place. As the world's leading innovator of film and adhesive technology, we have the durable, cost-effective opaque films for just about any surface and application. So whether it's a storefront window, an interior wall, a delivery vehicle — or an entire fleet — you're sure to create exactly the brand image you're looking for. And customers are sure to notice.




































Vehicle colors shown are Atomic Red and Black.

Opaque Colored Films




	Number				
	180mC	7725	7725SE	7125	50
	Product				
	3M™ Controltac™ Graphic Film with Comply™ Adhesive Series 180mC	3M™ Scotchcal™ ElectroCut™ Graphic Film Series 7725	3M™ Scotchcal™ ElectroCut™ Graphic Film Series 7725SE	3M™ Scotchcal™ ElectroCut™ Graphic Film Series 7125	3M™ Scotchcal™ Graphic Film Series 50
	Description				
	Designed for long-term fleet applications where non-visible air release channels are needed along with sliding capabilities, snap-up and removability.	Designed for electronic cutting and is thermal transfer printable. Cuts and weeds down to 1/4". Moisture-resistant synthetic liner lays flat and won't split. Also permits easy multi-color lay-up.	Fluorescent colors designed to be electronically cut for graphics needing high visibility and attention value.	Designed for electronic cutting and is thermal transfer printable. Cuts and weeds down to 3/8". Blue paper liner on white film helps improve speed and ease of weeding.	Reliable, value-priced 3M solution for electronically cut letters and graphics. Cuts and weeds down to 3/8" and is thermal transfer printable. Also features removable adhesive and blue liner on white films for ease of weeding.
	Applications				
Fleet (commercial trailer, truck, tractor)	✓	✓		✓	✓
Transit (bus, passenger train)	✓	✓		✓	
Railroad	✓	✓			
OEM graphics	✓				
Label (warning, information)	✓	✓	✓	✓	✓
Signage — non-backlit	✓	✓	✓	✓	✓
Cut letters/shapes	✓	✓	✓	✓	✓
Window graphics	✓	✓		✓	✓
	Durability and warranties				
Expected performance life, unprinted (years)*	10	8	1	8	5
3M™ MCS™ Warranty	✓	✓	✓	✓	
	Application process				
Flat, simple curves	✓	✓	✓	✓	✓
Flat with rivets	✓	✓	✓	✓	
Corrugated	✓				
Compound curves	✓				
	Film characteristics				
Number of standard colors	84	84	5	84	28
Screen printable (SP), thermal transfer (TT)	SP	SP, TT	SP	SP, TT	TT
Cast or non-cast	Cast vinyl	Cast vinyl	Cast vinyl	Cast vinyl	Non-cast vinyl
Film thickness (mils)	2	2	2–3.8	2	3
	Adhesive characteristics				
Permanent		✓	✓	✓	
Removable	✓				✓
Pressure-activated	✓				
Non-visible air release channels	✓				

*unwarranted

3M™ Scotchcal™ ElectroCut™ Graphic Film Series 7125 and 7725
3M™ Controltac™ Graphic Film with Comply™ Adhesive Series 180mC

	Transparent 114		Dove Gray 91		Beige 49
	White <i>Only available in 180mC-10</i>		Dark Gray 41		Fawn 99
	White <i>Only available in 7725-10 and 7125-10</i>		Nimbus Gray 101		Magenta 103 PANTONE® 205 C
	Matte White 20		Duranodic 69		Process Magenta 273 PANTONE® 214 C
	Antique White 90		Black 12 PANTONE® Process Black C		Perfect Match Red 263 PANTONE® 186 C
	Pearl Gray 11 PANTONE® Cool Gray 2 C		Matte Black 22 PANTONE® Black C		Tomato Red 13 PANTONE® 1795 C
	Light Gray 121		Deep Mahogany Brown 19 PANTONE® 4625 C		Atomic Red 293
	Stone Gray 81		Russet Brown 29 PANTONE® 175 C		Geranium 63
	Medium Gray 31 PANTONE® Cool Gray 7 C		Tan 39		Cardinal Red 53
	Mid Gray 61 PANTONE® Cool Gray 8 C		Putty 59		Imperial Red 93
	Traffic Gray 151*		Sandstone 89		Deep Red 23

3M™ Scotchcal™ ElectroCut™ Graphic Film Series 7125 and 7725
3M™ Controltac™ Graphic Film with Comply™ Adhesive Series 180mC

	Burgundy 58		Lime Green 136		Dark Aqua 307
	Terra Cotta 24		Apple Green 196		Robin Egg Blue 86
	Red Orange 74		Kelly Green 46		Peacock Blue 77 PANTONE® 298 C
	Bright Orange 14 PANTONE® Orange 021 C		Bright Green 186 PANTONE® 348 C		Soft Blue 97
	Apricot 64		Dark Green 56 PANTONE® 3425 C		Light Blue 107
	Light Orange 54		Bottle Green 276		Olympic Blue 57 PANTONE® 7461 C
	Harvest Gold 105 PANTONE® 7510 C		Khaki Green 16		Persian Blue 117
	Sunflower 25 PANTONE® 1235 C		Forest Green 66 PANTONE® 3302 C		Intense Blue 47 PANTONE® 301 C
	Bright Yellow 15 PANTONE® 109 C		Bermuda Blue 357 PANTONE® 323 C		Vivid Blue 17
	Light Lemon Yellow 65		Teal 96 PANTONE® 322 C		Sapphire Blue 37 PANTONE® 2747 C

Some of these products are a simulation of the closest PANTONE®-identified color standard. Consult current PANTONE® publications for accurate color. PANTONE and other Pantone trademarks are the property of Pantone LLC. © Pantone LLC, 2019. All rights reserved.

Note that the elements used in sign construction, including sources of illumination, adhesives and substrates, can affect color. In most instances, color variation is slight, but certain elements will have a more noticeable effect, particularly on shades of white. PANTONE® color numbers are based on reflective light measurements of product samples applied to a standard white substrate.

3M™ Scotchcal™ ElectroCut™ Graphic Film Series 7125 and 7725
3M™ Controltac™ Graphic Film with Comply™ Adhesive Series 180mC

Metallic Graphic Film

Fluorescent Graphic Film 7725SE


Not available in other film lines.



Dark Blue 397



Dark Blue Metallic 217



Yellow Orange 404



Wedgewood Blue 187



Bright Blue Metallic 227



Red Orange 414



Shadow Blue 177



Petroleum Blue Metallic 247



Fuchsia 413



Light Navy 197
PANTONE® 289 C



Satin Aluminum 120
PANTONE® 877 C



Yellow 405



Indigo 27
PANTONE® 2767 C



Slate Metallic 201



Green 406



Boat Blue 127



Charcoal Metallic 211



Royal Purple 38



Chocolate Brown Metallic 239



Purple 48



Champagne Metallic 249



Plum 78
PANTONE® 525 C



Satin Gold 131
PANTONE® 872 C



Dark Violet 98



Gold Metallic 241



Copper Metallic 229



Steampunk Red Metallic 243

3M™ Scotchcal™ Graphic Film Series 50

	Transparent 11		Gold 54 PANTONE® 872 C		Grass Green 73
	White 10		Beige 914		Bright Green 745 PANTONE® 355 C
	Matte White 100		Pink 64 PANTONE® 214 C		Medium Green 76 PANTONE® 3415 C
	Light Gray 94		Light Red 44 PANTONE® 485 C		Dark Green 78 PANTONE® 7484 C
	Nimbus Gray 97 PANTONE® 7540 C		Dark Red 483		Teal 79 PANTONE® 321 C
	Silver 58 PANTONE® 877 2C		Burgundy 49 PANTONE® 209 C		Light Blue 82
	Black 12 PANTONE® Black C		Bright Orange 34 PANTONE® 1655 C		Azure Blue 84 PANTONE® 2935 C
	Matte Black 120		Sunflower 27 PANTONE® 7549 C		Sapphire Blue 88 PANTONE® 287 C
	Brown 92		Lemon Yellow 24 PANTONE® 106 C		Deep Navy Blue 90 PANTONE® 655 C
					Purple 66

Can't find your color?


Get the highest quality film in the color you want with our three-day, no charge color match service.

Can't find your color? No problem — we can custom match colors for you. Contact your local 3M distributor or sales representative to find out how easy it is to get the perfect film for your needs in the perfect color for your brand.

Custom colors available in 180mC and 7725 only.

To learn more visit 3M.com/graphics.


Color matching steps:



Contact your 3M sales representative.



Provide Pantone®, RAL, or NCS color, or a physical sample.



Receive A4 sample of the matched color in about one week! Once the color is approved, 3M will begin to make the color shortly after ordering.

*Minimum order quantities as low as 250 yards. Minimum quantities vary based on product and dimension



Authorized PANTONE Partner

Take command at 3M.com/opaquefilms.



Commercial Solutions
3M Center, Building 220-12E-04
St. Paul, MN 55144 USA

Phone 1-800-328-3908
Web 3M.com/graphics

Gerber High Performance Series 220 and 225 Premium Films are manufactured by 3M and sold exclusively by Gerber. Every effort has been made to ensure the accuracy and completeness of the information in this brochure. 3M, however, assumes no liability as a result of any errors or inaccuracies which may exist.

Warranty and Limitations. The following is made in lieu of all other express or implied warranties, including any implied warranty of merchantability or fitness for a particular purpose. All 3M products are warranted to be free of defects in materials and manufacture at the time of shipment and to meet the specifications stated in the film or media's Product Bulletin. Also see the 3M Graphics Warranties Bulletin, which gives the terms, additional limitations of the warranty, if any, and limitations of liability.

© 3M 2021. All rights reserved. 3M, Comply, Controltac, ElectroCut, MCS and Scotchcal are trademarks of 3M. PANTONE is a registered trademark of PANTONE Inc. Please recycle. Printed in USA. 75-5100-2618-2

