



Vapor Permeable Air Barrier 3015VP

Technical Data

October 2019

Product Description	3M™ Vapor Permeable Air Barrier 3015VP is a water vapor permeable, air and water impermeable membrane with an aggressive, high-tack acrylic adhesive that does not require the use of a primer on most construction surfaces.
---------------------	---

Product Construction	Backing	Adhesive	Colors	Liner
	Elastomeric Coated Nonwoven	Acrylic Pattern Coated	White	Polyester

Typical Physical Properties	Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.
-----------------------------	---

		ASTM Test Method
Liner Thickness:	3 mils (0.078 mm)	ASTM D3652
Total Thickness (coated membrane):	15 mils (0.50 mm)	ASTM D3652
Tensile Strength (coated membrane):	1177 psi (8.1 MPa)	ASTM D882
Elongation at Break:	40%	ASTM D882
Lap Adhesion (Stainless Steel):	50 oz./in (0.44 N/mm)	ASTM D3330

Water Vapor Transmission per ASTM E96, US perms

Dry Cup 12
Wet Cup 17

Nail Sealability

127 mm (5 inches) water head after 3 days Dry / Pass ASTM D1970-14, Section 7.9

3M™ Vapor Permeable Air Barrier 3015VP

Features

- Meets the requirements of ASTM E2178 and CAN/ULC S741-8.
- Passes NFPA 285 as part of various exterior wall constructions.
- Service temperature from -40° to 300°F (-40° to 150°C).
- Can be applied to substrates from 0° to 150°F (-18° to 66°C).
- Permeable to water vapor, impermeable to air and water.
- Resists UV exposure for up to 12 months.
- Compatible with many building sealants: No adverse reaction with synthetic rubber, butyl, polyurethane, silicone and silane terminated hybrid sealants.
- Excellent adhesion to concrete, concrete block, anodized aluminum, galvanized metal, plywood and most exterior grade fiberglass matt gypsum boards without the use of any primer. Contact your local 3M Sales Representative or refer to the Technical Bulletins for details.
- Adhesive provides a unique combination of both cold and hot temperature adhesion to most substrates, which can extend the construction season in many climates.
- Unique adhesive even adheres to damp surfaces that have not absorbed water, like metals, glass and plastics.
- Seals around nails and staples to prevent moisture intrusion.

Surface Preparation

- To obtain the best adhesion, 3M™ Vapor Permeable Air Barrier 3015VP should be installed when outdoor temperatures range from 0°F (-18°C) to 150°F (66°C).
- Surfaces should be clean, free from dirt and debris and have not absorbed water.
 - Surfaces should be free of any damaged, unsupported areas, sharp protrusions or voids.
 - Concrete must be cured a minimum of 7 days before application.
 - Block or brick walls should have mortar joints stuck flush.
 - While it can be applied as low as 0°F (-18°C), surfaces must be clear of snow, ice or frost.
 - Adheres to most common building materials. For difficult to stick to surfaces, test adhesion before application. If needed, apply 3M™ Hi-Strength 90 Spray Adhesive, 3M™ Hi-Strength 94 ET Spray Adhesive, 3M™ Holdfast 70 Spray Adhesive or 3M™ Fastbond™ Contact Adhesive 30NF to prime the substrate prior to applying the membrane. Products are available as either an aerosol or cylinder spray adhesive.

3M™ Vapor Permeable Air Barrier 3015VP

Application Instructions

Refer to 3M™ Vapor Permeable Air Barrier 3015VP Installation Guide for detailed application information.

- Remove outer protective film to expose adhesive surface.
- Must be lapped a minimum of 2" on sides and ends. Remove protective film cover before installing the next layer.
- No primer is needed on most construction surfaces.
- The adhesive is very aggressive and quickly bonds to substrates. Do not contaminate the adhesive area with dust or debris before applying it to the intended surface. Be careful when aligning product on the wall as repositioning may be challenging.
- Once aligned, set the membrane in place by rolling the product back against the exposed adhesive. Unwind the roll while maintaining pressure against the wall to tack the membrane in place. Wipe the membrane down with a feathering motion from the middle outward to obtain a smooth surface. For best air barrier membrane performance, roll the membrane with a rubber roller to ensure a tight seal against the wall and between overlapped edges.
- Remove film covering membrane.
- Detail work must be carefully executed to ensure a continuously sealed building envelope.
- Rough openings may be flashed with detail widths of 3M™ Air and Vapor Barrier 3015.

3M™ Vapor Permeable Air Barrier 3015VP

Storage	Optimum storage conditions are 60° to 80°F (16° to 27°C) and 40 to 60% relative humidity in the original packaging material.
Shelf Life	To obtain best performance, use this product within 24 months from date of manufacture.
Technical Information	The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.
Product Selection and Use	Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.
Warranty, Limited Remedy, and Disclaimer	Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.
Limitation of Liability	Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

ISO 9001

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.



Industrial Adhesives and Tapes Division
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (Fax)
www.3M.com/industrial

3M is a trademark of 3M Company.
©3M 2019 (10/19)