



# Scotchâ Tape 8915

## Performance Filament Tape

**Manufactured in an ISO 9002 certified facility**

Updated : June 2000  
Supersedes : February 1999

<b>Product Description</b>	A high performance transparent tape reinforced along its length with continuous glass yarn filaments which give the tape high tensile strength.	The transparent ScotchPro™ backing provides stiffness and excellent abrasion, moisture and scuff resistance. The pressure sensitive adhesive is specifically formulated to provide high adhesion, clean removability and stain resistance on most finishes.
----------------------------	---	---

### Physical Properties

Not for specification purposes

<b>Adhesive Type</b>	Pressure sensitive hot melt solvent free (synthetic rubber resin)	
<b>Backing</b>	ScotchPro™ polypropylene film	
<b>Reinforcement</b>	Glass Yarn	
<b>Thickness</b>	150 microns (0.15 mm)	ASTM D-3652
<b>Colour</b>	Transparent; blue	
<b>Available Widths</b>	Contact your local sales office	<b>Available Lengths</b> Contact your local sales office
<b>Core Size (ID)</b>	76 mm (3")	
<b>Storage Conditions</b>	Store behind present stock, in a clean dry place. Temperature of 40 - 80°F (4-26°C) & 40-50 % Relative Humidity are recommended. Rotate your stock.	

### Performance Characteristics

Not for specification purposes

<b>Adhesion to Stainless Steel</b>	6.5 N/cm	ASTM D-3330
<b>Tensile Strength</b>	298 N/cm	ASTM D-3759
<b>Elongation at Break</b>	3 %	ASTM D-3759

Date : June 2000  
8915 Performance  
Filament Tape

3M, Scotch and ScotchPro are trademarks of the 3M Company.

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations.



**Packaging Systems Division**

3M ITALIA S.p.A.  
Packaging Systems Customer Service  
Via S. Bovio 3 - Milano S. Felice  
20090 SEGRATE MI  
ITALY

Tel. + 39 02 7035 3174/3173  
Fax. + 39 02 7035 2104/3124

© 3M United Kingdom PLC 2000