




Science.
Applied to Life.™



3M Commercial Solutions

3M™ MCS™ Warranty

Qualified printers



3M™ MCS™ Warranty

3M™ MCS™ | Qualified Printers Overview

Printer Manufacturer	Printer Model	Ink Name	Ink System
Durst	Rho 160R, Rho 351	3M™ Piezo Inkjet Ink Series 2700UV	UV
Durst	Rho 312R, 512R, P10 320R	Durst Rho Roll 3M™ Premium UV Inks	UV
EFI	Quantum® 3 and 5/	EFI™ 3M™ SuperRange Ink	UV
EFI	EFI™ VUTEk 3r and 5r Printers	EFI™ 3M™ SuperRange Ink	UV
EFI	EFI™ Pro 16h LED Printer	EFI™ Pro 16h-3M Ink	UV
EFI	EFI™ VUTEk® H1625 LED	EFI™ H1625 LED Series 3M™ Inks	UV
EFI	EFI™ VUTEk® GS3250/5250/5500LX (incl. Pro/UD Series)	EFI™ 3M™ SuperRange Ink	UV
EFI	EFI™ VUTEk® GS3250/5250/5500LXr (incl. Pro/UD Series)	EFI™ VUTEk® GSLXr 3M™ SuperFlex UV Ink	UV
EFI	EFI™ VUTEk® GS2000LX/ 3250LX (incl. Pro/UD Series)	EFI™ VUTEk® GSLX 3M™ SuperFlex UV Ink	UV
EFI	EFI™ VUTEk® GS2000/3200/3250 (incl. Pro Series)	EFI™ VUTEk® GS 3M™ Premium UV ink	UV
EFI	EFI™ VUTEk® GS3250r/5000r	EFI™ VUTEk® GSr 3M™ Premium UV ink	UV
EFI	EFI™ R3225	EFI™ R3225 3M™ UV Inks	UV
EFI	PV 200	3M™ Piezo Inkjet Ink Series 2200UV	UV
EFI	EFI™ VUTEk® UltraVU® 150/X300/X360	3M™ Piezo Inkjet Ink Series 1500v2	Solvent
Epson	Sure Color® SC-40600/SC-60600/SC80600	Epson® - 3M™ UltraChrome® GS3 Ink (with red)	Solvent
HP	Latex 310/315/330/335/360/365/370/375	HP831 Latex Inks, a 3M™ MCS™ warranty component	Latex
HP	Latex 560/570	HP831 Latex Inks, a 3M™ MCS™ warranty component	Latex
HP	Latex 370/375/570	HP871 Latex Inks, a 3M™ MCS™ warranty component	Latex
HP	Designjet L26100/26500/28500	HP792, a 3M MCS warranty component	Latex
HP	Latex 210/260/280	HP792, a 3M MCS warranty component	Latex
HP	Latex 1500/3000/3100	HP881 Latex Inks, a 3M™ MCS™ warranty component	Latex
HP	Designjet L65500	HP 3M LX-600 Latex Specialty Inks	Latex
HP	Latex 820, 850; LX820, 850; Scitex LX600, 800	HP 3M LX-600 Latex Specialty Inks	Latex
HP	Latex 3500/3600	HP 3M 891 Latex Ink	Latex
HP	Scitex TJ 8300/8350	3M™ Piezo Inkjet Ink Series 4800	Solvent
Mimaki	UJV-160, JFX-1631, JFX-1615R	MIMAKI UV Piezo Inkjet Ink Series LF-200 <i>Manufactured by 3M</i>	UV
Mimaki	UJV500-160	MIMAKI UV Piezo Inkjet Ink Series LUS-200 <i>Manufactured by 3M</i>	UV
Mutoh	Blizzard 65 / 90	3M™ Piezo Inkjet Ink Series 6900	Solvent
Mutoh	Spitfire Extreme 65 / 90 / 100	3M™ Piezo Inkjet Ink Series 6900	Solvent
Mutoh	ValueJet 1638X, 2638	Mutoh + 3M Universal Mild Solvent Inks	Solvent
OKI Data Infotech	ColorPainter™ E-64s Printer	3M™ SX Ink from OKI	Solvent
OKI Data Infotech	ColorPainter™ H3-104s Printer	3M™ SX Ink from OKI	Solvent
OKI Data Infotech	ColorPainter™ H-74s, H-104s, H2-74s, H2-104s	3M™ GX Ink from OKI	Solvent
OKI Data Infotech	ColorPainter™ M-64s Printer	3M™ SX Ink from OKI	Solvent
OKI Data Infotech	ColorPainter™ W-54s, W-64s	3M™ GX Ink from OKI	Solvent
WP Digital	3M 2500UV	3M™ Piezo Inkjet Ink Series 2700UV	UV